

NEW

EASIEST TO PROGRAM, CONNECT & OPERATE **EZ Series™** PLC TOUCHPANELS



*EZ Series
PLC Touchpanels
Start at*
\$399

**TESTED AND PROVEN BY
20,000+ ENGINEERS**

- Easy to Learn, Intuitive Software
- Easy to Operate 3D Objects
- Easy to Connect to Most PLCs
- Easy to Maintain Hardware
- Easy on the Budget
- 8 Display Sizes to Choose From
- Exclusive Online Programming, No Downtime
- NEMA 4x Indoor, FDA Compliant

**EZ Series Touchpanels
are Easy to Operate**



- Efficient 3D Graphical Objects
- 4000 Symbols to Choose From
- Multiple Languages
- Easy to Understand Trend Graphs
- Easy Insightful PID Faceplates
- Multi-State Indicators
- Alarm Reporting
- Recipe Button w/ On-Screen Edit
- Scale Objects w/o Distortion
- Pop Up Thumbwheel Entry
- Pop Up Alpha-Numeric Keypad
- 8 Levels of Password Security
- Dynamic/Multi-state Bitmaps
- Bitmap Buttons

**EZ Series Touchpanels
have Drivers for Over
90% of PLCs/Networks**

Serial Drivers

- Allen-Bradley DF1 Half and Full Duplex (PLC-5, SLC 500, MicroLogix 1000, 1200 and 1500)
- DH485/AIC/AIC+ for MicroLogix 1000, 1200, 1500, SLC500, 5/01, /02, /03
- Aromat Mewtocol COM
- Control Techniques - Unidrive 2-wire, 4-wire (binary)
- CTC Binary
- GE Fanuc SNPX (90/30, 90/70)
- Idec Computer Link
- Omron Host Link (C200 and C500)
- All Mitsubishi FX Series
- Modicon MODBUS® RTU
- Siemens S7 MPI Adapter series
- Square D Symax
- Texas Instruments - T15x5 Series

Ethernet Drivers

- Allen-Bradley Ethernet I/P for ControlLogix
- Allen-Bradley DF1 over Ethernet for MicroLogix & SLC 500 PLC's
- GE SRTP over Ethernet
- Modbus TCP/IP Ethernet

Hardware Drivers

- DH+ / Remote I/O
- Modbus Plus
- Profibus
- DeviceNet

**EZ Series Touchpanels
have Enhanced Data
Acquisition & Ethernet
Connectivity Options**

EZDac (EZ's Data Acquisition \$99 Utility Option) uses the RS232 programming port to a PC or Ethernet for communicating with multiple panels allowing data acquisition in a PC remote from the panel. The user specifies tags and schedules for data acquisition. Data files are organized in a convenient, user selectable format (tab delimited or CSV) and can be opened in Excel or in any text editor. EZDac Software installed on your PC can select any tag you want to monitor on the PLC / Panel, watch the data coming in real time (as compared to receiving only a snapshot when certain event occurs) and plot it into an Excel sheet automatically. Time intervals on event triggers can be selected from a wide range of options.

PROGRAM THIS SCREEN IN LESS THAN 10 MINUTES

Programming Software
\$108

NEW

EZ Series Touchpanels have Earned their Name!

We named them “EZ Series” for a reason! We made an easy to use, simple operator interface that will save you a lot of engineering hours and design time due to its simplicity and ease of use. You don’t need prior programming knowledge to design a screen. You do not need to attend any classes to learn how to program them.

It is Intuitive, it is Simple!


ONLY ASSUMPTIONS:

- Familiar with Windows®-Based Environments
- Good Understanding of Your PLC Memory’s Address Formats




STEP 1 - Select an Object

- Click on “Objects” on the main menu bar
- Select the object you wish to create. In this example, we’ll click on “Switches”.
- You may also select an object from the tool bar below the main menu



STEP 2 - Fill in the Dialog Box

- A** Click the style of switch you wish to use.
- B** Select “Label Text”. This will allow you to name and customize the object.
- C** Select or create a PLC bit address tag that the “Switch” will activate.
- D** If you need password protection, click on the “Protection” tab at the top of the dialog box.
- E** If you wish to keep this object invisible until a PLC tag is triggered, click on the “Visibility/Details” tab.



STEP 3 - Place the Object

- Click on the screen and stretch the object to your desired size.
- If you want to edit the object again, simply double click to bring up the dialog box.
- You can even “Simulate” the object to see how it interacts in real time.



UNIQUE ONLINE PROGRAMMING: SAVES TIME FOR SCREEN DESIGN & MACHINE DEBUG

OTHERS:

- Create a screen - 20 minutes
- Compile and Download to panel (minimum 5 minutes)
- Check it out on the panel
- Change colors, fonts, object sizes... an average of 4x, 5 minutes each

TIME TO DEVELOP AND FINALIZE ONE SCREEN - 60 MINUTES

COMPILE... DOWNLOAD... COMPILE... DOWNLOAD
COMPILE... DOWNLOAD... COMPILE... DOWNLOAD



60 MINUTES

OURS:

- Create a couple of objects
- Click Save (transfers instantaneously) to see how they look
- Add more objects, click save again

**NO Compilation or Download... NO Machine Down Time...
JUST CLICK and Save to Panel**

NO COMPILATION OR DOWNLOAD



10 MINUTES

**TIME TO DEVELOP AND FINALIZE ONE
SCREEN - 10 MINUTES**

DEDICATED NON-WINDOWS OPERATING SYSTEM FOR SUPER-FAST RESPONSE & SCREEN UPDATE TIME



Switch between
screens in less
than a second!



**TYPICAL 0.75
SECONDS**



and not 2-3 seconds like others



Fastest Response to Touch Input

Because of the use of vector based graphics and a proprietary OS, EZ Series Touchpanels are universally recognized as having the fastest response to touch inputs, typically less than 3/4 of a second even with complex screens. This means no waiting and also less wear on a panel from operators pounding an object on a screen waiting for a response.



SPECIFICATIONS

Enclosure: NEMA 4/4X Indoor, FDA Compliant

CPU Type: Motorola Coldfire 32 bit 40MHz

OS: Dedicated (non-Windows)

Service Power: 24 Vdc (20 to 30 Vdc) 10 to 20 W depending on model

Agency Approval: UL, CUL, CE

Op. Temp.:

STN: 0 to 45° C

TFT: 0 to 55° C

Storage Temp.: -20 to 65° C

Humidity: 10 to 95% RH, non-condensing

Withstand Voltage: 1000 Vdc 1 min

Vibration: 5 to 55Hz, 2G for 2 hours

Shock: 10G up to 20 milliseconds

Electrical Noise: NEMA ICS 2-230 Showering Arc

No. of Screens: Up to 999

Limited by Memory only

Real Time Clock: Built-in

Screen Saver: Built-in

Mounting: DIN

MODEL SPECIFIC SPECIFICATIONS

Screen Pixels:

6": 320x240

8, 10 & 15": 640x480

Display Type & Touch Cells:

6" W.O.B.: 5.7", 4 Shades of Blue 140 Nits, 40K Hrs, 48 tch cells

6" Mono: 5.7", 16 Shades of Gray, 140 Nits, 40K Hrs, 192 cells

6" STN Color: 5.7", 128 Colors, 200 Nits, 40K Hrs, 192 touch cells

6" TFT Color: 5.7", 128 Colors, 470 Nits, 75K Hrs, 192 touch cells

8" STN Color: 8.2", 128 Colors, 140 Nits, 40K Hrs, 192 touch cells

8" TFT Color: 8.2", 128 Colors, 370 Nits, 50K Hrs, 192 touch cells

10" TFT Color: 10.4", 128 Colors, 400 Nits, 50K Hrs, 192 tch cells

15" TFT Color: 15", 128 Colors, 250 Nits, 55K Hrs, 192 tch cells

PRODUCT DIMENSIONS (EXTERNAL):

6": 6.2 x 8.1 x 2.5"

8": 8.8 x 10.9 x 2.3"

10": 10.6 x 13.6 x 2.9"

15": 13 x 16.8 x 4.7"

To Order (Specify Model Number)

MOST POPULAR MODELS HIGHLIGHTED!

MODEL	PRICE	DESCRIPTION
EZP-S6W-RS	\$399	5.7" White on Blue EZ Series Touchpanel
EZP-S6M-FS	499	5.7" Monochrome EZ Series Touchpanel
EZP-S6C-FS	699	5.7" STN Color EZ Series Touchpanel
EZP-T6C-FS	844	5.7" TFT Color EZ Series Touchpanel
EZP-S8C-FS	944	8.4" STN Color EZ Series Touchpanel
EZP-T8C-F	1049	7.7" TFT Color EZ Series Touchpanel
EZP-T10C-F	1599	10.4" TFT Color EZ Series Touchpanel
EZP-T15C-FS	2399	15" TFT Color EZ Series Touchpanel
SOFTWARE		
EZP-PANELEDIT	\$108	Programming Software
EZ-DAQ-SOFT	108	Data Acquisition Software for EZ Series Panels
MEMORY AND ACCESSORIES		
EZP-RAM-2	\$99	1 MB Expansion RAM card for EZ Series panels
EZP-FLASH-1	49	512K Flash memory card for EZ Series panels
EZP-FLASH-2	59	1MB Flash memory card for EZ Series panels
EZP-FLASH-3	89	2MB Flash memory card for EZ Series panels
EZP-ETHERPLUS	249	Modbus TCP/IP Ethernet Interface Card
EZP-BAT	20	Replacement 3.6V Battery for EZ Series panels
EZP-BRK-1	56	Optional DIN rail clips for 5.7" models (set of 2)
DISPLAY SHEILDS		
EZP-COV6	\$20	Pack of 3 protective shields for 6 EZ
EZP-COV8	34	Pack of 3 protective shields for 8 EZ
EZP-COV10	38	Pack of 3 protective shields for 10 EZ
EZP-COV15	56	Pack of 3 protective shields for 15 EZ
CABLES		
EZP-CBL	\$22	10' RS232C shielded cable for EZPLC
EZP-2CBL	22	10' RS232C shielded cable for DL series PLC
EZP-MLOGIX-CBL	30	6' shielded cable for AB Micrologix PLC
EZP-SLC-232-CBL	22	10' shielded cable for AB SLC series PLC
EZP-DH485-CBL	25	10' shielded cable for AB DH485 network
EZP-90-30-CBL	22	10' shielded cable for GE 9030 or 9070 SNPX
EZP-MITSU-CBL	22	10' RS422 shielded cable for FX, 15D to 25D
EZP-MITSU-CBL-1	22	10' RS422 shielded cable for FX, 15D to 8 Din
EZP-S7MPI-CBL	22	10' shielded cable for Siemens S7
EZP-OMRON-CBL	22	10' shielded cable for Omron C200 or C500
EZP-ARCOL-CBL	22	10' shielded cable for Aromat PLC
EZP-CTRUNI-CBL	22	10' RS422 shielded cable, 4 wire Unidrive
EZP-CTRUNI-CBL-1	22	10' RS485 shielded cable, 2 wire Unidrive
EZP-CTCBI-CBL	22	10' RS232C shielded cable for CTC PLC
EZP-IDECM-CBL	22	10' RS485 shielded cable for IDEC Micro 3 PLC
EZP-MODUNI-CBL	22	10' RS485 shielded cable for Modicon Unitelway
EZP-MODRTU-CBL	22	10' RS232C cable Modbus RTU, 15D to 9D
EZP-S7200-CBL	22	10' RS485 shielded cable for Siemens S7-200
EZP-IDECS-CBL	22	10' RS232C shielded cable for IDEC Microsmart
EZP-MODRJ-CBL	22	10' RS232C shielded cable for Modicon Micro
EZP-PGMCBL	25	RS232 Programming cable

Ordering Examples: EZP-S6W-RS, 5.7" white on blue EZ series touchpanel, EZP-PANELEDIT, programming software, EZP-CBL, programming cable, \$399 + 108 + 22 = \$529. EZP-S6C-FS, 5.7" STN color EZ series touchpanel, EZP-PANELEDIT, programming software, EZP-CBL, programming cable, \$699 + 108 + 22 = \$829.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters