



DRA-ACT-4 DIN Rail Mount AC Voltage/Current Signal Conditioners

4-Wire AC Powered Design



\$220
Basic Unit



DRA-ACT-4I Series AC Current Input

DRA-ACT-4V Series AC Voltage Input

- ✓ ± 0.1% Accuracy
- ✓ Isolated
- ✓ 4-20 mA Output
- ✓ Low Profile Enclosure

The DRA-ACT-4I AND DRA-ACT-4V Series are isolated 4-wire ac current and ac voltage input DIN rail mount signal conditioners that convert the measured input into a proportional, linear and highly accurate 4-20 mA output current. The DRA-ACT-4I Series of ac current input models includes models for 0-1 Aac and 0-5 Aac inputs with a 4-20 mA output. The DRA-ACT-4V Series of ac voltage input models includes models for 0-150 Vac, 0-250 Vac and 0-400 Vac inputs again with a 4-20 mA output. Standard instrument power is 115 Vac, 50/60 Hz. Units can also be configured for optional 230 Vac, 50/60 Hz power.

For complete safety, an internal transformer isolates the signal conditioner input from the output thus enabling these units to withstand large momentary inputs. Complete input to output isolation, high surge current capacity and high output signal-to-noise ratio make these signal conditioners highly immune to ground loop signals and RFI. Zero and span trimmers accessible from the front panel of these units facilitate fine tuning.

Specifications

GENERAL

Accuracy: ±0.1% of span typical (2-100% of span) for pure sinusoidal input

Temperature Stability: 0.02%/1°C

CMR: 122 dB typical; 117 dB min

Response Time: 220 msec (0-98%)

Power Supply: 115 Vac ± 15%, 50/60 Hz standard; 230 Vac ± 15%, 50/60 Hz optional

Power Consumption: 1.9 VA

Loop Resistance: 750 Ohms @ nominal ac supply; 600 Ohms

@ minimum ac supply
Supply and Load Variation Effect: < 0.03% for full change

Output Ripple: better than 0.1% of span RMS

Frequency: 40-500 Hz

Output: 4-20 mA

Zero Adjust: ±35% min

Span Adjust: ±25% min

Operating Ambient: 32 to 158°F (0 to 70°C); 5 to 95% RH, noncondensing

Storage Temperature: -13 to 185°F (-25 to 85°C)

Enclosure: polycarbonate

Mounting: standard 35 mm DIN rail or wall mount

Dimensions: 2.87" H x 1.77" W x 4.69" D (73 x 45 x 119 mm)

Weight: 0.9 lb (0.4 kg)

DRA-ACT-4I SERIES (AC CURRENT INPUT)

Input: 0-1 Aac, 0-5 Aac

Input Power

Consumption: 0.26 VA at 5 Aac input

Isolation: Current Input: 2.5 KV RMS/1 min; Power Input: 4 KV RMS/1 min

Inrush Current: 40 Aac RMS max for 8 sec every 10 min; 75 Aac RMS max for 1 sec every 10 min

DRA-ACT-4V (AC VOLTAGE INPUT)

Input: 0-150 Vac, 0-250 Vac,

0-400 Vac

Input Power Consumption: 0.3 VA at 120 Vac input; 1.4 VA at 230 Vac input

Isolation: 4 KV RMS/1 minute



To Order (Specify Model Number)

DRA-ACT-4I ac current input models*

Model No.	Price	Description
DRA-ACT-4I-1	\$220	0 to 1 A ac input, 4 to 20 mA output
DRA-ACT-4I-2	220	0 to 5 A ac input, 4 to 20 mA output

DRA-ACT-4V ac voltage input models*

DRA-ACT-4V-1	220	0 to 150 Vac input, 4 to 20 mA output
DRA-ACT-4V-2	220	0 to 250 Vac input, 4 to 20 mA output
DRA-ACT-4V-3	220	0 to 400 Vac input, 4 to 20 mA output

* Standard power is 115 Vac, 50/60 Hz. To order unit configured for 230 Vac, 50/60 Hz power, add suffix "-230" to model no., no additional charge.

Comes with complete operators manual.

Ordering Example: DRA-ACT-4V-2, ac voltage signal conditioner, 0 to 250 Vac input, 4 to 20 mA output, \$220.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters