





DRA-CSM-1 Current Multiplexer

\$630



- ✓ **Multiplexes Sixteen 4-20 mA Inputs Into One 4-20 mA Output**
- ✓ **± 0.01% Accuracy**
- ✓ **Channel Selection Controlled by 4 Discrete Inputs**
- ✓ **Solid-State Technology**
- ✓ **Economical PLC Upgrade**

The DRA-CSM-1 Current Multiplexer is a solid state multiplexer capable of transferring the selected 4-20 mA input current signal to the output terminals in less than 10 microseconds at an accuracy better than 0.01%. The DRA-CSM-1 is typically controlled by a PLC thereby obtaining full data synchronization.

The DRA-CSM-1 is provided with a unit enable/disable control line which enables the parallel connection of several multiplexers to the same controller input. The period during which the unit is disabled is used for self-testing according to a self-test procedure which checks the unit's hardware.

Model DRA-CSM-1 is powered by an external DC power supply. Each two-wire 4-20 mA transmitter is connected to the input terminals. Each channel provides a current limited voltage supply for the

connected two-wire transmitter. The channel selected by the multiplexer is directed to the control device's (e.g., PLC's) analog inputs. Power is maintained by the multiplexer to the unselected channels thereby maintaining uninterrupted transmitter current flow. Each 4-20 mA input channel on the multiplexer has its own red LED status light which illuminates on presence of current in the loop.

Specifications

- Analog Inputs:** 16, 4-20 mA current loops
- Digital Inputs:** 4 address, 1 enable/self-test
- Logic:** true low (user selectable)
- Digital Levels:** "0" < 0.4V, 5V < "1" < 60V
- Analog Output:** selected, 4-20 mA current loop
- Accuracy:** ±0.01% of span (for full temp range)
- Switching Time:** 10 microseconds (resistive load)

Current Leakage: unmeasurable when disabled

Addition to Loop Resistance: 350 ohm max

Transmitter Current Limitation: 40 ±2mA

Indicators: 16 red LEDs for current inputs, one yellow power on LED

Supply Voltage: 15-40 Vdc

Operating Current Consumption: 12 mA max (not including transmitter currents)

Self-Test Current Consumption: 120 mA peak (not including transmitter currents)

Mounting: standard 35mm DIN rail or wall mount

Operating Ambient: 32 to 158°F (0 to 70°C), 5 to 95% RH noncondensing

Storage Temperature: -25 to 85°C (-13 to 185°F)

Weight: 0.6 kg (1.3 lb)

Dimensions: 73 H x 200 W x 121 mm D (2.88" x 7.88" x 4.76")

To Order (Specify Model Number)

Model No.	Price	Description
DRA-CSM-1	\$630	Current multiplexer
DRN-PS-1000	150	Power supply, 95-240 Vac input, 24 Vdc @ 1A output

Comes with complete operator's manual.

Ordering Example: DRA-CSM-1 current multiplexer with DRN-PS-1000 power supply, \$630 + 150 = **\$780**.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters