

LDM30 Series

General Purpose Limited Distance Modem



\$133
Basic Unit

- ✓ DC to 57,600 Baud
- ✓ Optical Isolation
- ✓ Surge Protectors
- ✓ LED Diagnostic Indicators
- ✓ Operation to 3 Miles (5 KM) at 9600 Baud, 1 Mile (1.7 KM) at 19,200, 0.5 Miles (0.8 KM) at 57,600
- ✓ Four-Wire Full Duplex, Two-Wire Simplex
- ✓ Self-Powered or Host-Powered
- ✓ Selection of Connectors
- ✓ Wide Operating Temperature Range, 0 to 70°C

The LDM30 Series of products is designed to allow video display terminals (VDTs) and other RS-232 devices to be connected over distances sufficient to cover any industrial or institutional complex of buildings. These modems feature a rugged aluminum enclosure small enough to mount on the back panel


of VDT units, saving valuable desk and floor space.

The LDM30 Series is designed for full-duplex, asynchronous operation over two, DC-continuity, on-loaded, twisted-wire pairs. Through special high-speed optically-coupled circuits they may communicate at data rates up to 57,600 baud.

Specifications

Model	LDM30						
Baud Rate Range	0 – 57.6K						
Baud Rate	57.6K	38.4K	19.2K	9.6K	4.8K	2.4K	1.2K – 0
Distance (miles)	0.5	0.75	1.0	3	5	7	12
Distance (km)	0.8	1.25	1.7	5	8.3	11.7	20
Common Mode Isolation	500V Surge, 300V Continuous						
Differential Mode Surge Protection (3 devices)	ANSI/IEEE C37.90.1-1989						
Channel Lines ⁽¹⁾	TD, RD						
Control Lines ⁽¹⁾	RTS, CTS, DTR, DSR, RLSD						
Modes	Asynchronous 4-wire full duplex, 2-wire simplex						

Notes: (1) TD = Transmit Data, RD = Receive Data, RTS = Request To Send, CTS = Clear To Send, DTR = Data Terminal Ready, DSR = Data Set Ready, RLSD = Received Line Signal Detect.



A self-powered model and a host-powered model are available. The self-powered unit uses 12 Vac from a wall-mounted transformer while the host-powered unit takes \pm DC power from pins 9 and 10 of the RS-232 connector. The modem circuits—and, consequently, the host device—are protected from electrical transients due to lightning strikes or operation of heavy industrial equipment.

Each device features a convenient Data-Communication Equipment (DCE) to Data-Terminal Equipment (DTE) switch which reverses pins 2 and 3 of the RS-232 connector. For installation and troubleshooting, each unit has diagnostic Light-Emitting Diodes (LEDs) on the transmit and receive lines.

The RS-232 connector may be ordered as a male or female 25-pin connector. Field connection is made through a modern, solderless, screw-termination assembly. Alternatively, a convenient four-wire modular phone jack is available.

Model	LDM30
Power: AC operation ⁽²⁾ DC operation	12 Vac at 92 mA \pm 9 Vdc to \pm 15 Vdc, 35 mA
Operating Environment	0 to 70°C, 0 to 95% relative humidity, noncondensing
Dimensions	3.6 x 2.1 x 1" (91.4 x 53.3 x 25.4 mm)
Weight AC Transformer	100 g (3.5 oz) max 311.8 g (11.0 oz) max
MTBF⁽³⁾	>150,000 hrs

Notes: (2) 120 Vac and 220 Vac power transformers are available. (3) Ground-benign environmental conditions (no salt atmosphere, <50°C ambient temperature).

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)				
Model Number	Price	RS232 Connector	Field Connector	Power Source
LDM30-P	\$133	25 Pin male	Screw termination	Host-powered
LDM30-S	133	25 Pin female	Screw termination	Host-powered
LDM30-PT	149	25 Pin male	Screw termination	Transformer
LDM30-ST	149	25 Pin female	Screw termination	Transformer

Includes operator's manual.
Transformer powered units also include 120 Vac wall mount transformer.

Ordering Example: LDM30-ST converter: \$149.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters