

# LDM80 Signal Powered Fiber Optic Modem

**\$195**

Basic Unit



- ✓ Data Rates to 19.2K Baud at 2.2 Miles (3.5KM)
- ✓ 17dB Optical Link Power Budget
- ✓ Powered by RS-232 Host Port Signals
- ✓ Full Duplex Asynchronous Operation
- ✓ Indicating LEDs
- ✓ DCE/DTE Switch
- ✓ Designed for FCC Class A Requirements
- ✓ Complies with FCC Class A Requirements
- ✓ Pinned or Socketed RS-232 Connectors

LDM80-P-025, \$195, Shown smaller than actual size

The RS-232 connection is through male or female EIA 25-pin connectors. The fiber optic connection is through ST connectors. The LDM80 is equivalent to a 3-wire, full duplex, RS-232 circuit. Handshake signals are locally connected as in Figure 1.

Indicating LEDs come on during a "SPACE" on transmit or receive data. A TD/RD reversing DIP switch is provided for connection to DTE (Data Terminal Equipment) or DCE (Data Communication Equipment) ports.

### Recommended Cables


The LDM80 optical transmitter may be used with a wide range of fiber sizes. Specifications are for 100/140µm. Other fiber sizes may be used with a resulting different cable loss budget.

The LDM80 is a small, inexpensive fiber optic transmitter/receiver completely powered by the host RS-232 port. The enclosure for the LDM80 is a conductive shell which greatly reduces RF radiation and susceptibility. The rugged metal enclosure is small enough to mount on the back panel of typical computer equipment saving valuable desk and floor space. A pair of these units allows most RS-232C cable links to be replaced and extended with a duplex fiber optic cable. The normal 50-foot RS-232 limit may be extended to 2.2 miles (3.5 km). Fiber optic data communications provide complete EMI/RFI rejection, isolation, elimination of ground loops, and reduced error rates. Data security is enhanced by almost nonexistent electromagnetic emissions.

### Specifications

Model	LDM80		
Baud Rate Range	0 – 19.2K		
<b>Distance: Over Baud Rate Range</b>			
<b>Fiber Core Diameter (µm)</b>	<b>Max. Cable Length (km)</b>	<b>Loss Budget (dB)</b>	
100 (glass)	3.5	17	
50 (glass)	2.5	9	
62.5 (glass)	2.0	11	
85 (glass)	3.5	16	
200 (glass)	3.5	23	
1000 (plastic)	30 meters	32	
<b>Channel Lines<sup>(1)</sup></b>	TD, RD		
<b>Control Lines<sup>(1)</sup></b>	RTS, CTS, DSR, DTR, RLSD		
<b>Modes</b>	Asynchronous 2-fiber full duplex, 1-fiber simplex		
<b>Optical Transmitter</b>	850 nm wavelength		
<b>Output from 1 m cable</b>	-26dB typ, -27dB min, -18dB max		
<b>Optical Receiver Power Input for 4 µs Pulse Distortion</b>	-44dB min		
<b>Optical Connectors</b>	ST		

Notes: (1) TD = Transmit Data, RD = Receive Data, RTS = Request To Send, CTS = Clear To Send, DTR = Data Terminal Ready, DSR = Data Set Ready, RLSD = Received Line Signal Detect.



Model	LDM80
RS-232 Output Voltage	+5V logic 0, -5V logic 1 with 3kW Load
DCE/DTE Switch	One
Diagnostic LEDs	Two
Power: Port Power and/or DC operation	+5.0 to +8.5VDC, no current limit, 5mA >+8.5 VDC, 10mA current limit
Operating Environment	-20 to +70°C, 0 to 95% relative humidity, non-condensing
Dimensions	3.51" x 1.88" x 0.729" (89.2 x 47.8 x 18.5 mm)
Weight	8.1 oz (230 g) max
MTBF <sup>(1)</sup>	>100,000 hrs

Notes: (1) Ground-benign environmental conditions (no salt atmosphere, <50°C ambient temperature).

**AVAILABLE FOR FAST DELIVERY!**

To Order (Specify Model Number)			
Model No.	Price	RS232 Connector	Field Connector
LDM80-P-025	195	25 Pin male	ST fiber optic connector
LDM80-S-025	195	25 Pin female	ST fiber optic connector

Includes operator's manual.

OMEGACARE<sup>SM</sup> extended warranty is available for models shown on this page.

Ask your sales representative for full details when placing order.

Ordering Example: LDM80-P-025 converter, OMEGACARE<sup>SM</sup> 1year warranty for LDM80-P-025 (adds 1 year to standard 1 year warranty), \$195 + 28 = \$223.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters