

Portable Data Loggers with Display Part of the NOMAD® Family

OM-73, temperature/relative humidity data logger, \$159.

OM-71, temperature data logger, \$129.

OM-74, thermocouple data logger, \$179.

OM-72, temperature data logger with remote sensor, \$139.

OM-70 Series Starts at **\$129**

MADE IN USA 1 YEAR WARRANTY NIST CE

Optional †

FREE Thermocouple Included!
Model OM-74 Includes a free 1 m (40") Type K insulated beaded wire thermocouple with subminiature connector and wire spool caddy. Order a Spare! Model No. SC-GG-K-30-36, \$15.

- ✓ LCD Real Time Display of Temperature (°C or °F), Relative Humidity (% RH, Model OM-73 Only), Time, Date, Alarm Status, Recording Status and Battery Condition
- ✓ User Selectable Stop on Memory Full or Memory Rollover for Continuous Recording
- ✓ PC Delayed Start or Push-Button Recording Control
- ✓ Read Recorded Data on Logger Display
- ✓ Displays Alarm Icon for High/Low Alarm Conditions
- ✓ Nonvolatile EEPROM Memory Retains Data Even if Battery Fails
- ✓ USB Interface for Fast Data Transfer
- ✓ Compact, Light Weight, Easy-to-Use

The OM-70 Series of portable temperature and temperature/humidity data loggers are easy-to-use, versatile devices which can be used for a wide range of logging applications including coolers, freezers, greenhouses, museums,

laboratories, shipping containers, warehouses, environmental monitoring and food storage. These data loggers are capable of sampling as fast as once per second or as slow as every 18 hours. Models OM-71 and OM-72 can store a total of 43,344 temperature measurements in memory.

Model OM-73 can store a total of 43,344 measurement points for temperature only or 21,672 points of temperature, humidity and dew point. The model OM-74 thermocouple data logger can store 32,638 temperature samples. Easy-to-use Windows software is included with each data logger.

The software is a full-featured program that allows you to set up all data logger functions including sampling rate, logging duration, start mode, logging mode, and high and low temperature alarm values. Once data has been logged, the program then allows you to download data from the logger, plot the data and export the data to an ASCII text or Excel file format for further analysis.

Software Features Include:

- Data summary to read statistics and alarm information in a simplified report format
- Data listing for tabular view of detailed dates, times and values of recorded data
- Graph function displays data in clear graphical format.
- Zoom magnifies data with powerful zoom and autoscale functions.
- Autoscale function fits data to the screen or allows user to manually enter their own values.
- Graphical Cursor displays exact data of any point in the graphical display.
- Export data in text or Excel format.
- Print graph or text data with print preview and setup options
- Logger configuration allows easy set up and launch of data loggers with immediate or delayed start, preferred sample rate, alarm setup, and custom ID
- Password protected calibration function automatically stores with parameters in device or restores factory defaults.

† Refer to next page for NIST calibration ordering information.

A calibration Window is provided in the software to simplify the calibration procedure.

- Status windows display unique ID of logger, battery voltage, memory used, sample rate, duration, alarm condition and logging status.
- Menu Bar along the top of the screen provides one click access to software functions.

Specifications

OM-71, OM-72, OM-73

Ambient Temperature

Measurement Range (Models OM-71, OM-73):

-20 to 70°C (-4 to 160°F)

External Sensor Temperature Measurement Range

(Model OM-72):

-40 to 70°C (-40 to 160°F)

Storage Temperature:

-40 to 77°C (-40 to 170°F)

Temperature Accuracy:

±0.5°C (±1°F), from -17 to 50°C (1 to 122°F)

Temperature Resolution:

0.1°C (0.05°F)

Relative Humidity Range

(Model OM-73): 0 to 99% RH non-condensing

Relative Humidity Accuracy

(Model OM-73):

±2% RH from 10 to 90% RH

Relative Humidity Resolution

(Model OM-73): 0.05% RH

OM-74

Display Temperature Resolution:

0.1°C (0.2°F) up to 199.9 °C or °F, 1°C (1°F) above 200 °C or °F

Logged Temperature Resolution:

0.1°C (0.2°F)

Thermocouple Impedance:

50 Ω max for specified accuracy

Cold Junction Temperature

Accuracy: ± 0.3°C (±0.5°F)

Operating Temperature:

-18 to 55°C (0 to 131°F)

Storage Temperature:

-30 to 80°C (-20 to 175°F)



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

Thermocouple Temperature Range and Accuracy (OM-74)

Thermocouple	Accuracy ¹	Logger Supported Range ²
K	±0.7°C (1.3°F)	-250 to 1300°C (-418 to 2372°F)
J	±0.6°C (1.0°F)	-170 to 1000°C (-274 to 1832°F)
E	±0.4°C (0.8°F)	-200 to 820°C (-328 to 1508°F)
N	±0.8°C (1.5°F)	-200 to 1300°C (-328 to 2372°F)
T	±0.7°C (1.3°F)	-200 to 400°C (-328 to 752°F)
S	±2.8°C (5.0°F)	-50 to 1760°C (-58 to 3200°F)
R	±2.8°C (5.0°F)	-50 to 1760°C (-58 to 3200°F)
B	±3.3°C (6.0°F)	20 to 1820°C (68 to 3308°F)
C	±1.7°C (3.0°F)	0 to 2320°C (32 to 4208°F)

¹ The accuracy given is for the OM-74 unit only. Errors may increase depending on the thermocouple wire grade used. ² The logger supported range is for stored temperature. The logger can only display temperatures up to 1999°F or 1999°C

GENERAL

Sample Rate: 1 second to 18 hours user selectable

Alarm Settings:

Over/under alarm with visual indication

LCD Display:

Displays temperature, date, time, alarm condition recording status and battery condition

Time Accuracy:

±100 ppm @ 24°C (75°F)

Measurement Capacity:

OM-71, OM-72, OM-73:

Non-volatile memory; 43,344 samples for temperature only, or 21,672 samples for temperature, humidity and dew point (Model OM-73); OM-74; 32,638 temperature samples

Recording Control: Start on button press, immediate after setup, or at a user specified date and time


Recording Mode: Stop on memory full, or continuous recording with memory rollover

Minimum System Requirements:

8MB of RAM, 2MB of disk space, 800 x 600 resolution, 1 free USB port

Software Compatibility:

Windows XP/VISTA/7



Windows software displays data in graphical or tabular format.

Interface:

USB 2.0

Power: OM-71, OM-72, OM-73:

3V CR2032 lithium battery (included);

OM-74: 3 AAA batteries (alkaline or lithium (included))

Battery Life: 3 years (average)

Dimensions:

OM-71, OM-72, OM-73:

6 H x 5.7 W x 1.3 cm D (2.36 x 2.24 x 0.51")

OM-74: 5.7 H x 5.5 W x 3.0 cm D

(2.25 x 2.15 x 1.2")

Weight: OM-71, OM-72, OM-73:

91 g (3.2 oz)

OM-74: 62 g (2.2 oz)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
OM-71	\$129	Temperature data logger with display
OM-72	139	Temperature data logger with display and remote temperature sensor
OM-73	159	Temperature/humidity data logger with display
OM-74	179	Thermocouple data logger with display
OM-40-BATT-6	15	Replacement 3V lithium battery (box of 6), for OM-71, OM-72 and OM73
CAL-3-HU†	125	NIST traceable calibration certificate for OM-73

Comes complete with Windows software, operator's manual on CD, USB interface cable and battery.

Ordering Example: OM-73, temperature/humidity data logger with display and OMEGACARE 1 year extended warranty for OM-73 (adds 1 years to standard 1 year extended warranty), \$159 + 25 = \$184.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters