

Digital I/O to Computer Interfaces

RS-232 or RS-485 Compatible

H1700 Series
\$275
 Basic Unit



IBM PC



SERIAL I/O



D/I/O



H1770, \$350, shown connected to SSS-PC16-B

H1750, \$275, shown connected to SSS-PC-24V

- ✓ Digital Inputs/Outputs via RS-232 or RS-485
- ✓ Connect to Solid State I/O Modules to Sense/Control ac/dc Voltages
- ✓ Configure Each Bit Individually as Input/Output
- ✓ Control Digital I/O Singly or All at Once
- ✓ 24 and 64-Bit Versions
- ✓ Up to 24 Boards/7936 Channels on a Single RS-485 Line

Specifications

Channels: H1750, 24 channels; H1770, 64 channels; user can define individual channels as either input or output
Input Voltage Level: 0 to 10 V without damage
Input Switching Levels: 3.5 V min high; 1.0 V max low
Power Requirements: +5 Vdc ± 0.25 V @ 30 mA max (not including I/O module requirements)
Baud Rates: 300, 600, 1200, 2400, 4800, 9600, 19.2k, 38.4k
Multidrop Capability: Up to 124 interfaces

Outputs: 0 to 10 V, 15 mA max load
Communications: ASCII format via RS-232/485 ports; 7 data bits, odd, even or none parity; all communications setups stored in nonvolatile memory using EEPROM
Dimensions: 102 H x 117 mm W (4.0" x 4.6"), H1750; 127 H x 254 mm W (5.0" x 10.0"), H1770
Operating Ambient: -25 to 70°C (-13 to 158°F); 0 to 95% RH, non-condensing
Storage Ambient: -25 to 85°C (-13 to 185°F)

The H1700 Series provides easy access to digital input and output signals through an RS-232 or RS-485 communications link. The H1750 provides 24 channels of digital I/O, while the H1770 has 64 channels. For interfacing to real-world signals, the H1700 Series is designed to work directly with OMEGA solid state I/O modules. Modules are available to sense ac or dc voltages, or to control ac or dc power lines.

The H1750 mounts directly to the OMEGA SSS-PC-24V, which accepts up to 24 I/O modules, while the H1770 connects to up to four SSS-PC16-B 16-channel backplanes.

MOST POPULAR MODELS HIGHLIGHTED

To Order (Specify Model Number)		
Model No.	Price	Description
H1750	\$275	24-channel digital I/O to RS-232/485 interface; mounts directly to SSS-PC-24V backplane
H1770	350	64-channel digital I/O to RS-232/485 interface; connect to up to four SSS-PC16-B backplanes; requires H1700-CA-1 cable
H1770-CA-1	100	Four cables to attach H1770 to four SSS-PC16-B backplanes
SSS-PC16-B*	100	16-channel digital I/O module backplane, for use with H1770; requires H1770-CA-1 cable
SSS-PC-24V*	160	24-channel digital I/O module backplane, for use with H1750

*Backplanes require solid state I/O modules.

Each unit supplied with complete operator's manual.

Ordering Example: H1770 64-channel digital I/O interface, H1770-CA-1 cable assembly and SSS-PC16-B digital I/O module backplane, \$350 + 100 + 100 = \$550.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters