

## Thermocouple Temperature and Pressure Data Logger

OM-CP-PRTC210 Series

**\$649**

All Models



- ✓ Up to 2 Years Battery Life
- ✓ Wide Temperature Range
- ✓ Accepts Thermocouple Types J, K, T, E, R, S, B and N
- ✓ High Speed Download
- ✓ Real-Time Operation
- ✓ Programmable Start Time
- ✓ Miniature Size

The OM-CP-PRTC210 is a pressure and thermocouple temperature data logger, ideal for use in factory settings. This device is available from 2 to 345 bar (30 to 5000 psi) and features a 1/8 MNPT fitting for quick connection.


The OM-CP-PRTC210 has a real-time clock and a battery life of up to 2 years. This all in one compact, portable, easy to use device has a high-speed download and can measure and record up to 21,844 readings per channel.

The storage medium is non-volatile solid state memory, providing maximum data security even if the battery becomes discharged.

The OM-CP-PRTC210 can be started and stopped directly from your computer and its small size allows it to fit almost anywhere.

The OM-CP-PRTC210 makes data retrieval quick and easy. Simply plug it into an available COM port and our user-friendly software does the rest.

The software converts a PC into a real-time strip chart recorder. Data can be printed in graphical and tabular format or exported to a text or Microsoft Excel® file.



OM-CP-PRTC210-30A, \$649, shown larger than actual size.

### Specifications

#### INTERNAL CHANNEL

**Temperature Range:** -20 to 80°C (-4 to 176°F)  
**Temperature Resolution:** 0.1°C  
**Calibrated Accuracy:** ±0.5°C

#### REMOTE CHANNEL

**Thermocouple Types:** J, K, T, E, R, S, B and N  
**Thermocouple Connection:** Female subminiature (SMP) connector  
**Cold Junction Compensation:** Automatic, based on internal channel  
**Maximum Thermocouple Resistance:** 1000Ω, <100Ω recommended  
**Pressure Sensor:** Semiconductor strain gauge

#### Pressure Specified Accuracy:

2% FSR, 0.25% @ 25°C Typical  
**Pressure Response Time:** 0.1 ms (10 to 90% FSR)

**Pressure Connection:** 1/8 MNPT  
**Start Modes:**

Software programmable immediate start or delay start up six months in advance

#### Real-Time Recording:

May be used with PC to monitor and record data in real time

**Memory:** 21,844 readings per channel for a total of 65,532 readings; software configurable memory wrap


**Reading Rate:** 2 seconds to 12 hours, selectable in software

**Calibration:** Digital calibration through software


**Calibration Date:** Automatically recorded within device

Thermocouple Type	Range	Resolution	Accuracy*
J	-210 to 760°C	0.1°C	±0.5°C
K	-260 to 1370°C	0.1°C	±0.5°C
T	-260 to 400°C	0.1°C	±0.5°C
E	-260 to 980°C	0.1°C	±0.5°C
R	-50 to 1760°C	0.5°C	±2.0°C
S	-50 to 1760°C	0.5°C	±2.0°C
B	60 to 1820°C	0.5°C	±2.0°C
N	-260 to 1300°C	0.1°C	±0.5°C
Voltage	-75 mV to 75 mV	5µV	±20µV

\* Accuracy specifications based on 3 m (9.8') 24 AWG thermocouple



5SRTC/5LRTC Series starts at \$48/5 pk, see [omega.com](http://omega.com) for details.



OM-CP-IFC200, \$129, Windows software displays data in graphical or tabular format.

Pressure Range	Resolution
0 to 30 psia	0.002 psia
0 to 30 psig	0.002 psig
0 to 100 psia	0.005 psia
0 to 100 psig	0.005 psig
0 to 300 psia	0.02 psia
0 to 300 psig	0.02 psig
0 to 500 psia	0.05 psia
0 to 500 psig	0.05 psig
0 to 1000 psia	0.05 psia
0 to 5000 psia	0.2 psia

**Battery Type:** 3.6 V lithium battery (included), user replaceable

**Battery Life:** Up to 2 years

**Data Format:** Date and time stamped °C, °F, K, °R, °C, °F, °K, °R, mV; inH<sub>2</sub>O, psig, inHg, bar, atm, Torr, Pa, kPa, and MPa

**Time Accuracy:**

±1 minute/month (at 20 to 30°C)

**Computer Interface:** PC serial or USB (interface cable required); 57,600 baud

**Software:** XP SP3/Vista and 7 (32-bit and 64-bit)

**Operating Environment:** -20 to 80°C (-4 to 176°F), 0 to 95% RH non-condensing

**Dimensions:** 55 H x 63 W x 22 mm D (2.2 x 2.5 x 0.9") plus NPT fitting

**Enclosure:** Delrin®

**Weight:** 119 g (4.2 oz)

**MOST POPULAR MODELS HIGHLIGHTED!**

To Order (Specify Model Number)		
Model No.	Price	Description
OM-CP-PRTC210-30A	\$649	Thermocouple temperature and pressure data logger, 0 to 30 psia
OM-CP-PRTC210-30G	649	Thermocouple temperature and pressure data logger, 0 to 30 psig
OM-CP-PRTC210-100A	649	Thermocouple temperature and pressure data logger, 0 to 100 psia
OM-CP-PRTC210-100G	649	Thermocouple temperature and pressure data logger, 0 to 100 psig
OM-CP-PRTC210-300A	649	Thermocouple temperature and pressure data logger, 0 to 300 psia
OM-CP-PRTC210-300G	649	Thermocouple temperature and pressure data logger, 0 to 300 psig
OM-CP-PRTC210-500A	649	Thermocouple temperature and pressure data logger, 0 to 500 psia
OM-CP-PRTC210-500G	649	Thermocouple temperature and pressure data logger, 0 to 500 psig
OM-CP-PRTC210-1000A	649	Thermocouple temperature and pressure data logger, 0 to 1000 psia
OM-CP-PRTC210-5000A	649	Thermocouple temperature and pressure data logger, 0 to 5000 psia
OM-CP-IFC200	129	Windows software and 3.7 m (12') USB interface cable
OM-CP-BAT105	15	Replacement 3.6 lithium battery

Comes complete with 3.6V lithium battery. Operator's manual and USB interface cable are included with the OM-CP-IFC200 windows software (required to operate the data logger and is sold separately).

To order data logger with NIST calibration certificate, add suffix "-CERT" to model number and add \$60 to price.

**Ordering Example:** OM-CP-PRTC210-30A-CERT, thermocouple temperature and pressure data logger with NIST calibration certificate, and OM-CP-IFC200, Windows software, \$709 + 129 = \$838.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters