

DATA LOGGERS

Portable Low Cost Temperature Data Logger Part of the NOMAD Family

OM-63
\$79




- ✓ Temperature Alarm With Visual Indication On Demand
- ✓ User Selectable Stop on Memory Full or Memory Rollover for Continuous Recording
- ✓ PC Delayed Start or Pushbutton Recording Control
- ✓ USB Interface
- ✓ Compact, Light Weight, Easy-to-Use

The OM-63 portable temperature data logger is an easy-to-use, versatile device which can be used for a wide range of logging applications. The OM-63 is capable of sampling as fast as once per second or as slow as every 18 hours. A total of 43,344 temperature measurements can be stored in the data logger memory.

Easy-to-use Windows software is included with the OM-63. The software is a full-featured program that allows you to set up all data logger functions including sampling rate, logging duration, start mode, logging mode, and high and low temperature alarm values. Once data has been logged, the program then allows you to download data from the logger, plot the data and export the data to an ASCII text or Excel file format for further analysis.


Specifications

- Temperature Measurement Range:** -40 to 85°C (-40 to 185°F)
- Temperature Sensor:** Internal digital sensor
- Temperature Accuracy:** ±0.5°C (±1°F)
- Temperature Resolution:** ±0.01°C (±0.01°F)
- Sampling Rate:** User selectable, 1 second to 18 hours
- Data Storage:** 43,344 temperature readings



OM-63, \$79, shown larger than actual size.

Windows software displays data in graphical or tabular format.



Temperature Alarms:

Programmable high and low alarm thresholds. After the data logger is started, alarm status can be checked by pressing the Start Check button. If an alarm has occurred, the status LED on the data logger will flash red.

Recording Mode: User selectable; stop on memory full or continuous recording with memory rollover

Recording Start: Push button, computer controlled, or up to 6 week delayed start

PC Interface: USB port (USB cable included)

Calibration: Single point offset calibration available through software for temperature

Operating System Compatibility: WIN 98/2000/XP/VISTA

Time Accuracy: ±100 ppm @ 75°F

Power: 3.0V lithium battery (included)

Battery Life: 6 years typical

Storage Temperature: -40 to 85°C (-40 to 185°F)

Dimensions: 76 Hx 40 W x 15 mm D (3.0 x 1.6 x 0.6")

Weight: 28 g (1 oz)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

| Model No. | Price | Description |
|-----------|-------|-------------------------|
| OM-63 | \$79 | Temperature data logger |

Comes with complete operator's manual, 3.0V lithium battery, Windows software on CD ROM and 1.8 m (6') USB interface cable.

Ordering Example: OM-63, temperature data logger, \$79.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters