



OM-CP-RFTEMP101A Wireless Temperature Transmitter Part of the NOMAD® Family

\$199

Basic Unit



- ✓ Multiple Transmitter Configurations
- ✓ Automatically Converts Your PC into a Strip Chart Recorder
- ✓ Real-Time Operation
- ✓ Memory Wrap Around
- ✓ Calibration Date Stored in Memory
- ✓ Programmable Alarm


The OM-CP-RFTEMP101A is a miniature, wireless, battery powered, stand-alone, temperature transmitter. This all-in-one compact, portable, easy to use device that will measure and transmit temperature measurements. When enabled, the wireless transmitter will transmit readings back to the host computer where the data can be analyzed in real time. These readings are also logged to the device's memory for added data security. The convenient slide switch allows the transmitter to be turned On or Off without affecting the operation of the device. The device can be started, stopped and configured directly from your computer. Its small size allows it to fit almost anywhere. In addition to the wireless communications, the OM-CP-RFTEMP101A makes data retrieval quick and easy. Simply plug the device into an available COM port and our user-friendly software will handle the rest. The OM-CP-RFTEMP101A is a major leap forward in both size and performance.

The Windows software converts your PC into a real time strip chart recorder. Data can be printed in graphical or tabular format and can also be exported to a text or Microsoft Excel file.

Specifications


Temperature Sensor:
Semiconductor

Temperature Range:
-30 to 70°C (-22 to 158°F)



- Temperature Resolution:** .01°C
- Temperature Accuracy:** ±0.5°C (0 to 50°C)
- Calibration:** Digital calibration through software
- Memory:** 8191 readings
- Reading Interval:** 1 reading every 30 seconds to 1 every 12 hours
- Data Format:** Date and time stamped, °C, °F, °K, °R
- Time Accuracy:** ±1 minute/month (at 20 to 30°C)
- Computer Interface:** PC serial or RS-232C COM or USB for receiver (interface cable required); 57600 baud
- RF Baud Rate:** 4800 baud
- RF Carrier Frequency:** 418 MHz
- Range:** 36 m (120') line of sight
- Power:** 3.6 V lithium battery (included)
- Battery Life:** 1 year typical (1 minute reading rate @ 25°C)
- Software:** XP SP3/Vista and 7 (32-bit and 64-bit)

OM-CP-RFTEMP101A, \$199, shown larger than actual size



- Operating Environment:** -30 to 70°C (-22 to 158°F)
5 to 95% RH non-condensing
- Communication Frequency:** 418 MHz
- Dimensions:** 20 H x 42 W x 59 mm D (0.8 x 1.7 x 2.3")
- Weight:** 60 g (2 oz)
- Enclosure:** ABS plastic

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
OM-CP-RFTEMP101A	\$199	Wireless temperature transmitter
OM-CP-RFTEMP101A-CERT	259	Wireless temperature transmitter with NIST calibration certificate
OM-CP-RFC101A	199	Receiver package includes RF receiver, 1.2 m (4') RS-232 cable with DB9F termination, Windows software and operator's manual
OM-CP-RFC200A	249	Receiver package includes RF receiver, 3.7 m (12') USB cable, Windows software and operator's manual
OM-CP-BAT105	12	Replacement 3.6 V lithium battery

Operator's manual, USB cable and receiving antenna are included with the OM-CP-RFC200A Windows software (software is required to operate the data logger and is sold separately).

Ordering Example: OM-CP-RFTEMP101A-CERT wireless temperature transmitter with NIST calibration certificate, OM-CP-RFC200A Windows software and USB cable with receiving antenna, \$259 + 249 = \$508.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters