

## OM-CP-SHOCK101 Tri-Axial Shock Data Logger Part of the NOMAD® Family

# \$600

Basic Unit



- ✓ Built-In Accelerometers
- ✓ Measures Dynamic and Static Acceleration
- ✓ Real-Time Operation
- ✓ Programmable Start Time
- ✓ Compact
- ✓ Reuseable

The OM-CP-ULTRASHOCK101 is a battery powered, stand alone temperature, pressure, humidity and 3-axis shock recorder.

The OM-CP-ULTRASHOCK101 measures and records temperature, pressure and humidity at the selected reading rates, while shock is recorded as the peak acceleration levels over the same interval.

The OM-CP-ULTRASHOCK101 is specifically designed for documenting dynamic environments such as moving vehicles, trucks, containers, ships, etc. The device is also valuable in characterizing environments such as production and assembly lines of delicate electronics, IC fabrication, communications and computer components. This compact, portable, easy to use device will measure and record up to 349,525 measurements per channel. The storage medium is non-volatile solid state memory, providing maximum data security even if the battery becomes discharged.


The OM-CP-ULTRASHOCK101 makes data retrieval quick and easy. Simply plug it into an empty COM or USB port and our user-friendly software does the rest.

The Windows software converts your PC into a real time strip chart recorder. Data can be printed in graphical or tabular format and can also be exported to a text or Microsoft Excel file.

### Specifications

**Acceleration Type:**  
MEMS semiconductor

Acceleration Range (g)	±5	±50	±100	±250
Calibrated Accuracy (g)	±0.2	±1	±2	±4
Acceleration Resolution (g)	0.01	0.05	0.1	0.2



OM-CP-SHOCK101-50, \$600, shown smaller than actual size



OM-CP-IFC200, \$129, Windows software displays data in graphical or tabular format

**Sampling Rate:** 1.953 ms/512 Hz (note: data is sampled at this rate, only peak values are written at the end of a recording interval)

**Frequency Response:** 0 Hz to approx. 400 Hz

**Memory:** 349,525 readings per channel (1,398,100 total memory)

**Recording Interval:** 64 Hz to 5 minutes for shock, selectable through software

**Real Time Recording:** May be used with PC to monitor and record instantaneous acceleration in real time (1 sec or slower reading rate)

**Start Modes:** Immediate or delay start

**Programmable Start Delay:** Up to 180 days from PC launch

**Password Protection:** An optional password may be programmed into the device to restrict access to configuration options. Data may be read out without the password

**Calibration:** Digital calibration through software

**Calibration Date:** Automatically recorded within device

**Power:** 9V lithium or alkaline battery (included)

**Battery Life:** 7 days typical with lithium battery

**Data Format:** Date and time stamped, G and mG

**Time Accuracy:** ±1 minute per month at 20 to 30°C

**Computer Interface:** USB or serial interface (cable required) 115,200 baud

**Software:** XP SP3/Vista and 7 (32-bit and 64-bit)

**Operating Environment:** -20 to 60°C (-4 to 140°F)

0 to 95% RH non-condensing

**Dimensions:** 89 H x 112 W x 26 mm D (3.5 x 4.4 x 1.0")

**Weight:** 340 g (12 oz)

**Material:** Anodized aluminum

**AVAILABLE FOR FAST DELIVERY!**

To Order (Specify Model Number)		
Model No.	Price	Description
OM-CP-SHOCK101-5	\$600	Tri-axial shock data logger, ±5 g range
OM-CP-SHOCK101-50	600	Tri-axial shock data logger, ±50 g range
OM-CP-SHOCK101-100	600	Tri-axial shock data logger, ±100 g range
OM-CP-SHOCK101-250	600	Tri-axial shock data logger, ±250 g range
OM-CP-IFC200	129	Windows software and 3.7 m (12') USB interface cable
OM-CP-BAT103	25	Replacement 9V lithium battery

Operator's manual and USB interface cable are included with the OM-CP-IFC200 Windows software and USB interface cable (required to operate the data logger and software sold separately).

**Ordering Example:** OM-CP-SHOCK101-5 tri-axial shock data logger and OM-CP-IFC200 Windows software and USB interface cable, \$600 + 129 = \$729.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters