

Tri-Axial Transient Shock Data Logger

OM-CP-TSR101
Basic Unit
\$600



- ✓ 3-Axis Shock Recorder
- ✓ Built-In Accelerometers
- ✓ Measures Dynamic and Static Acceleration
- ✓ Programmable Start Time
- ✓ Compact and Reusable
- ✓ Optional Password Protection
- ✓ High Speed Download (115,200 baud)

The OM-CP-TSR101 is a battery powered, stand alone 3-axis shock data logger. The OM-CP-TSR101 measures and records instantaneous shock levels when the user-selectable shock levels have been exceeded. There are 15 rates to choose from ranging from 1024 to 1 Hz.

The OM-CP-TSR101 is valuable in characterizing environments such as packaging and fragility assessment (drop testing), break and crash testing, and shipping validation. This is an all-in-one compact, portable, easy to use device that will measure and record approximately 349,000 measurements per axis.

The storage medium is non-volatile solid state memory, providing maximum data security even if the battery becomes discharged. The device can be started and stopped directly from your computer and its small size allows it to fit almost anywhere.


The OM-CP-TSR101 makes data retrieval quick and easy. Simply plug it into an empty COM or USB port and our user-friendly software does the rest.

Specifications


Channels: Shock (3-axis)

Acceleration Type: MEMS semiconductor

Acceleration Range (g)	±5	±50	±100
Calibrated Accuracy (g)	±0.2	±1	±2
Acceleration Resolution (g)	0.01	0.05	0.1g



OM-CP-IFC200, \$129. Windows software displays data in graphical or tabular format.



OM-CP-TSR101-50, \$600, shown smaller than actual size.

Reading Rate Range:

15 options from 0.976 ms/1024 Hz to 1 second, selectable in software

Trigger Specifics: User settable trigger levels on X, Y, and/or Z axis, and specifies # of samples after triggers

Pre-Trigger Specifics: Records a pre-trigger of up to 50 readings prior to the trigger point

Frequency Response: 0 Hz to approx. 400 Hz (50, 100 g) [0 to 512 Hz (5 g)]

Real Time Recording: May be used with PC to monitor and record instantaneous acceleration in real time (only at 1 second rate, not possible during logging)

Start Modes: Software programmable, immediate start or delay start up to 180 days in advance

Password Protection: An optional password may be programmed into the device to restrict access to configuration options. Data may be read out without the password

Calibration: Digital calibration through software

Calibration Date: Automatically recorded within device

Power: 9 V lithium or alkaline battery (included), user replaceable

Battery Life: 7 days typical with lithium battery, immediate start, 1024 Hz

Data Format: Date and time stamped, G and mG

Time Accuracy: ±1 minute per month at 20 to 30°C

Computer Interface: USB or serial interface (cable required) 115,200 baud

Software: XP SP3/Vista and 7 (32-bit and 64-bit)

Operating Environment: -20 to 60°C (-4 to 140°F)

0 to 95% RH non-condensing

Dimensions: 89 H x 112 W x 26 mm D (3.5 x 4.4 x 1.0")

Weight: 340 g (12 oz)

Material: Anodized aluminum

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
OM-CP-TSR101-5	\$600	Tri-axial shock data logger, ±5 g range
OM-CP-TSR101-50	600	Tri-axial shock data logger, ±50 g range
OM-CP-TSR101-100	600	Tri-axial shock data logger, ±100 g range
OM-CP-TSR101-250	600	Tri-axial shock data logger, ±250 g range
OM-CP-IFC200	129	Windows software and 3.7 m (12') USB interface cable
OM-CP-BAT103	25	Replacement 9V lithium battery

Comes with complete operator's manual and 9V lithium battery. The OM-CP-IFC200 Windows software includes UDB interface cable required to operate the data logger (software sold separately).

Ordering Example: OM-CP-TSR101-5, tri-axial shock data logger and OM-CP-IFC200, Windows software and USB interface cable, \$600 + 129 = \$729.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters