




Water Level and Temperature Data Logger Part of the NOMAD® Family



OM-CP-LEVEL101, \$649, data logger shown larger than actual size

\$649

Basic Unit



- Submersible
- Programmable Start Time
- User Calibration Through Software

The OM-CP-LEVEL101 is a battery powered, stand-alone submersible water level and temperature data logger.

This all-in-one compact, portable, easy to use device will measure and record up to 16,383 measurements per channel.

The storage medium is non-volatile solid state memory, providing maximum data security even if the battery becomes discharged.

The OM-CP-LEVEL101 can be started or stopped directly from your computer and its small size allows it to fit almost anywhere. Data retrieval is simple. Plug it into an empty COM port and the easy to use Windows software does the rest. The software converts your PC into a real time strip chart recorder. Data can be printed in graphical or tabular format and can be exported to a text or Microsoft Excel file.

Specifications

TEMPERATURE CHANNEL

Temperature Sensor:

Semiconductor

Temperature Range:

-40 to +80°C (-40 to 176°F)

Temperature Resolution: 0.1°C


Calibrated Accuracy: ±0.5°C

(0°C to 50°C)

Pressure Sensor: Semiconductor strain gage

Media Compatibility: Must be compatible with 303 stainless steel

Nominal Range: 0 to 30'
Measurement Range: 0 to 100'
Resolution: 0.05"
Calibrated Accuracy: Nominal range ±0.3% max at 25°C
Response Time: 90% change in 1ms
Repeatability: ±0.5% FSR; ±0.2% typical
Proof Pressure: 90 psia
Memory: 16,383 readings per channel; 32,766 total readings
Real Time Recording: May be used with PC to monitor and record data in real time
Reading Rate: 1 reading every 2 seconds to every 12 hours selectable in software
Start Modes: Software programmable immediate start or delay start up six months in advance
Calibration: Digital calibration through software
Calibration Date: Automatically recorded with device
Battery Type: 3.6 V lithium battery included; user replaceable
Battery Life: 1 year typical at 25°C
Data Format: Date and time stamped, °C, °F, °K, °R, PSI, inches, feet, millimeters, centimeters, meters (of water column)



Windows Software shows data in graphical format

Time Accuracy: ±1 minute/month (RS-232 cable not in use)
Computer Interface: PC serial or USB (interface cable required); 2400 baud
Software: XP SP3/Vista and 7 (32-bit and 64-bit)
Operating Environment: -40 to 80°C (-40 to 176°F), 0 to 100% RH non-condensing
Dimensions: 145 mm dia x 32 mm L (5.7 x 1.25")
Weight: 220 g (8 oz)
Material: 303 stainless steel

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
OM-CP-LEVEL101-SS	\$649	Water level and temperature data logger
OM-CP-LEVEL101-SS-CERT	709	Water level and temperature data logger and NIST calibration certificate
OM-CP-IFC200	129	Windows software and 3.7 M (12') USB interface cable
OM-CP-BAT102	12	Replacement 3.6 V lithium battery

Comes complete with 3.6V lithium battery. Operator's manual and interface cable are included with the OM-CP-IFC200 software/cable package (required for data logger operation, sold separately). NIST calibration for temperature only.

Ordering Example: OM-CP-LEVEL101-SS-CERT water level and temperature data logger with NIST calibration certificate and OM-CP-IFC200 Windows software and USB interface cable, \$709 + 129 = \$838.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters