

# Radio Frequency Extender Kit for OM-CP Series Data Loggers

## Part of the NOMAD® Family

OM-CP-RFEXT-KIT  
Starts at  
**\$999**



- ✓ No Wires or Installation Cost
- ✓ 1 Mile Transmission Distance
- ✓ Operating Temperature Range: 0 to 70°C (32 to 158°F)
- ✓ Automatically Convert PC into Strip Chart Recorder
- ✓ Downloads Data Logger Readings Remotely
- ✓ Monitor Moving Processes
- ✓ Simple and Transparent Operation
- ✓ High Reliability Spread Spectrum
- ✓ Operational in Minutes

The OM-CP-RFEXT-KIT will allow any OM-CP-Series data logger to be remotely mounted up to 1 mile away from a computer. The system will consist of one RF Transceiver module mounted at the computer and one Transceiver module mounted remotely. An OM-CP data logger may be connected to the RF Transceiver module through the OM-CP-IFC101 cable. Once a data logger is connected, all communication between the computer and the logger will be transparent to the user. In other words, the logger will act as though it was connected directly to our OM-CP-IFC101 interface cable to a computer. The wireless link can be used to log data in real time at the host PC or periodically download data from the remote device.

### Specifications

**Datalogger Compatibility:**  
Connects directly to most OM-CP Series data loggers for instant wireless data logging

#### Range:

**Indoor:** 183 to 457 m (600 to 1500') typical;  
**Outdoor:** 0.5 mi typical (1 mi line-of-sight)

**Communication:** 900 MHz  
**Transmitter Output Power:** 100 MW nominal

**Supported Baud Rates:** 2400, 9600, 19200, 38400, 57600 (600 and 28800 baud not supported)



OMEGACARE<sup>SM</sup> extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARE<sup>SM</sup> covers parts, labor and equivalent loaners.



OM-CP-RFEXT, \$599, shown smaller than actual size.

**Transceiver Type:** FM, frequency hopping spread spectrum (FHSS)  
**Power:** 7-18 Vdc @ 500 mA max (ac adaptor included)  
**Computer Interface:** PC serial or RS-232C COM or USB for receiver  
**Operating Environment:** 0 to 70°C (32 to 158°F)  
10 to 90% RH (non-condensing)

**Windows Compatibility:**  
**Software:** XP SP3/Vista and 7 (32-bit and 64-bit)  
**Dimensions:** 71 H x 140 W x 30 mm D (2.8 x 5.5 x 1.2"), antenna is 175 mm (7") long  
**Weight:** 200 g (7 oz)

**AVAILABLE FOR FAST DELIVERY!**

### To Order (Specify Model Number)

Model No.	Price	Description
OM-CP-RFEXT-KIT	\$999	RF transceiver pair
OM-CP-RFEXT	599	Extra RF transceiver

Comes with complete operator's manual, PC interface cable and remote interface cable (connects to data logger).

**Ordering Example:** OM-CP-RFEXT-KIT radio frequency transceiver pair and OMEGACARE<sup>SM</sup> 1 year extended warranty for OM-CP-RFEXT-KIT (adds 1 year to standard 1 year warranty), \$999 + 99 = \$1098.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters