

Real-Time Temperature and Humidity Monitor

OM-EL-USB-RT

\$75



OM-EL-USB-RT, \$75, shown larger actual size.

- ✓ Displays Real-Time Temperature and Humidity Readings on Your PC Using the Windows Control Software
- ✓ Plugs Directly Into USB Port—No USB Cable Required
- ✓ User-Programmable Alarm Thresholds for Temperature and Relative Humidity
- ✓ Email, Text or Audible Alarm Notification
- ✓ Dew Point Indication via Windows Control Software

The OM-EL-USB-RT is a real time temperature and humidity monitor that displays real time temperature and humidity data on your computer via the Windows® control software (it is not a data logger and does not have any internal memory).

The software displays the temperature, relative humidity and dew point in real-time and saves it to a file which can store up to 7 day's worth of data. This data file is overwritten at the beginning of each new logging session. The software provides the option for the user to save the data permanently to the computer's hard drive. Temperature, relative humidity and dew point data can be graphed, printed and exported to other applications such as Excel.

The OM-EL-USB-RT Windows control software provides an environment whereby the user can view the current temperature and relative humidity and graph either the current data file or previously saved files. Users can set up high and low alarms for temperature and humidity within the software which can send emails, text alerts or audible alarms via the PC's internal speaker. The software can also show the current temperature and humidity in the notification area within the Window's tool-bar. Right clicking on the OM-EL-USB-RT icon in the notification area enables the user to access the full functionality of the software.


Specifications

TEMPERATURE
Measurement Range: -20 to 70°C (-4 to 158°F)
Repeatability: ±0.3°C (±0.6°F)
Accuracy: ±1.5°C (±3.0°F) overall error; requires 15 minutes temperature stabilization in environment
Temperature Units: °C or °F selectable in software
Response Time: 20 seconds typical, 30 seconds max

HUMIDITY
Measurement Range: 0 to 100% RH
Repeatability: Non-condensing ±0.5% RH (short term)
Accuracy: ±4.5% RH (overall error, 20 to 80% RH)
Response Time: 5 seconds
Long Term Stability: 1% RH/year
DEW POINT
Accuracy: ±2.5°C (±5°F)—overall error @ 25°C, 40 to 100% RH

GENERAL
High/Low Alarms: Selectable in software for temperature and humidity


Software: Windows® 2000/XP/VISTA
Software Logging Rate: 1 second
Weight: 11 g (0.4 oz)
Dimensions: See dimensional drawing below



Windows Software shows data in graphical format



OM-EL-USB-RT shown connected to a laptop computer USB port (laptop not included).



AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
OM-EL-USB-RT	\$75	Real-time temperature and humidity monitor

Comes with Windows software and operator's manual on CD ROM.

Ordering Example: OM-EL-USB-RT, real-time temperature and humidity monitor, \$75.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters