


# OMB-DBK20 and OMB-DBK21

## 48-Line General-Purpose Digital I/O Cards for OMB-LOGBOOK and DAQBOARD-2000 Series

Model OMB-DBK20/21

**\$209**



### Offers 48 I/O Lines Expandable in 8-Bit Groups as Inputs or Outputs

The OMB-DBK20 and OMB-DBK21 general-purpose digital I/O cards expand the number of digital I/O lines by forty-eight per card. The OMB-DBK20 and OMB-DBK21 connect to the digital I/O connectors on the OMB-LOGBOOK, OMB-DAQBOARD-2000 Series or OMB-DIGIBOOK-72 data acquisition systems.

Please note that when either the OMB-DBK20 or OMB-DBK21 is connected, the OMB-LOGBOOK, OMB-DAQBOARD-2000 Series or OMB-DIGIBOOK-72 digital I/O lines do not function as digital I/O lines for user-connected digital signals. Thus, for example, the first OMB-DBK20 or OMB-DBK21 card attached increases the system's number of usable digital I/O lines from twenty-four to forty-eight, and subsequent cards each add forty-eight additional lines of user-programmable digital I/O.

The OMB-DBK20, \$209 and OMB-DBK21, \$209 increase the digital I/O capacity of the OMB-LOGBOOK and DAQBOARD-2000 Series (OMB-DBK20 shown above)

Up to four OMB-DBK20 or OMB-DBK21 cards can be attached to the P2 port of a system, for a total of 192 lines.

The OMB-DBK20 and OMB-DBK21 differ only in that the OMB-DBK20 features screw-terminals for signal outputs, whereas the OMB-DBK21 provides DB37 male connectors for signal outputs.

### Specifications

48 I/O channels programmable in 8-bit groups as inputs or outputs

**Connector:** DB37 male, mates with P2 pinout on an OMB-LOGBOOK, OMB-DAQBOARD-2000 Series (attachment to the DAQBOARD's P2 further requires the use of an optional OMB-CA-60 cable) or with P2-1, P2-2 or P2-3 on the OMB-DIGIBOOK-72; the OMB-DBK20 offers screw-terminals for signal outputs; the OMB-DBK21 offers DB37 male connectors for signal outputs



**Device:** 82C55 x 2

**Output Voltage Levels**

**Minimum "1" Voltage:**

3.0 @ 2.5 mA sourcing

**Maximum "0" Voltage:**

0.4 @ 2.5 mA sinking

**Output Currents**

**Maximum Source Current:** 2.5 mA

**Maximum Sink Current:** -2.5 mA

**Input Voltage Levels**

**Minimum Required "1" Voltage**

**Level:** 2 V

**Maximum Allowed "0" Voltage**

**Level:** 0.8 V

**Output Float Leakage Current:**

10  $\mu$ A

**Cables:** Use OMB-CA-37-x cable with OMB-LOGBOOK and OMB-DAQBOARD-2000 Series

**ALL MODELS AVAILABLE FOR FAST DELIVERY!**

### To Order (Specify Model Number)

Model Number	Price	Description
OMB-DBK20	\$209	48-Line General-Purpose Digital I/O Card with Screw Terminal Connectors
OMB-DBK21	209	48-Line General-Purpose Digital I/O Card with DB37 Field Interface

**Ordering Example:** OMB-DBK20 is a 48-line general-purpose digital I/O card with screw terminals, \$209.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters