

OM-CP-TEMP1000S Rugged Temperature Data Logger with 1" Integral Probe Part of the NOMAD® Family



OM-CP-TEMP1000S data logger, \$499, shown slightly larger than actual size.

\$499
Basic Unit



- ✓ Rugged Stainless Steel Construction
- ✓ Memory Size: 32,767 Readings
- ✓ Programmable Start Time
- ✓ User Calibration Through Software
- ✓ Real Time Operation

The OM-CP-TEMP1000S temperature logger is a rugged, waterproof, battery powered, stand-alone device used for automatically recording temperatures from -40 to 150°C (-40 to 302°F). This all-in-one compact, portable, easy-to-use device will measure and record up to 32,767 temperature measurements. It includes a 1" rigid external probe and is ideal for use in harsh environments.

The OM-CP-TEMP1000S is a major leap forward in both size and durability. Its real time clock ensures that all data is time and date stamped. The storage medium is non-volatile solid state memory, providing maximum data security even if the battery becomes discharged. Its small size allows it to fit almost anywhere. Data retrieval is simple. Plug it into an available COM port and the easy-to-use Windows software does the rest.

The software converts your PC into a real time strip chart recorder.

Data can be printed in graphical or tabular format and can also be exported to a text or Microsoft Excel file.

Specifications

TEMPERATURE CHANNEL

Temperature Sensor:

100 Ω platinum RTD

Temperature Range:

-40 to 150°C (-40 to 302°F)

Temperature Resolution: 0.05°C

Calibrated Accuracy: ±0.5°C

(0 to 50°C)

GENERAL SPECIFICATIONS

Temperature Calibration:

Digital calibration through software

Calibration Date: Automatically

recorded within device to alert user

when calibration is required

Start Time: Start time and date are

programmable through software up

to 6 months in advance


Real Time Recording: Device may

be used with PC to monitor and

record data in real time

Recording Interval: 2 seconds

to 12 hours selectable in software



OM-CP-IFC200, \$129, Windows software displays data in graphical or tabular format

Power: 3.6 V lithium battery included (not field installable)

Battery Life: 1 year typical

Time Accuracy: ±1 minute per

month at 20°C when RS-232 port

is not in use

Data Format: Date and time

stamped, °C, °F, °K, °R,

Computer Interface:

PC serial or USB (interface cable

required); 2400 baud

Software: XP SP3/Vista and 7

(32-bit and 64-bit)

Operating Environment:

-40 to 150°C (-40 to 302°F),

0 to 100% RH non-condensing

Dimensions: 147 L x 26 mm dia

(5.8 x 1.0")

Weight: 255 g (8 oz)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
OM-CP-TEMP1000S	\$499	Temperature data logger with 1" integral probe
OM-CP-TEMP1000S-CERT	559	Temperature data logger with 1" integral probe and NIST calibration certificate
OM-CP-IFC200	129	Windows software & 3.7 m (12') USB interface cable

Operator's manual and USB interface cable are included with the OM-CP-IFC200 Windows software (software is required to operate the data logger and is sold separately).

The entire data logger/probe assembly is not submersible. Only the probe portion can be immersed (do not immerse the probe past the joint area where it connects into the body of the data logger as this joint area can be penetrated by liquid).

Ordering Example: OM-CP-TEMP1000S-CERT temperature data logger with integral probe with NIST calibration certificate and OM-CP-IFC200 Windows software and USB interface cable, \$559 + 129 = \$688.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters