

OMG-PCI-DIO Digital I/O Boards for PCI Bus Computers




OMG-PCI-DIO
\$159
 Basic Unit

- Models with 24, 32, 48 and 96 Channels of Buffered Digital I/O
- 8255 Compatible
- 10K Pull Up Resistors On Each Port Bit
- Provides 50-Pin IDC Connectors to Industry Standard Relay Racks
- Includes Driver and Utility Software for 98/ME/NT/2000/XP and Linux

The OMG-PCI-DIO series provide 24, 32, 48, and 96 channels of buffered digital I/O emulating 8255s for industrial control applications. 10K pull up resistors are included on each port bit. Each board contains 8 bit I/O ports configurable as inputs or outputs. This gives the user the ability to customize the combination inputs or outputs as needed. In addition, the low order bit of the first port can be set to generate an interrupt for status monitoring applications. A special factory configurable interrupt feature allows the user to request conditional I/O combinations for interrupt generation. When the I/O combinations occurs, a hardware interrupt is triggered.

Software

The OMG-PCI-DIO includes drivers, utilities, and programming samples for Windows 98/ME/NT/2000/XP and Linux to aid in the development of reliable applications for the OMG-PCI-DIO family of digital I/O boards.



OMG-PCIDIO48, shown smaller than actual size

Connectors and Terminal Panels

All of the I/O signals are accessed through a standard 50-pin connector. The 24 and 32 channel boards contain one connector, the 48 channel board contains two connectors and the 96 channel board has four connectors. OMEGA provides an optional OMG-TB07 terminal panel for wiring to the I/O connector. One terminal panel is required for each I/O connector. An OMG-CA167 is also needed for each terminal panel. The I/O connector is also compatible with industry standard relay racks. A OMG-CA135 cable can be used to connect each I/O connector to a relay rack.

Specifications

Channels: 24, 32, 48, 96
Operating Temperature: 0 to 50°C (32 to 122°F)

Storage Temperature:

-20 to 70°C (-4 to 158°F)

Humidity Range:

10 to 90% RH

Output:

24mA(sink), 15mA(source)

Power:

OMG-PCI-DIO24 +5V @ 480mA
 OMG-PCI-DIO32 +5V @ 500mA
 OMG-PCI-DIO48 +5V @ 794mA
 OMG-PCI-DIO96 +5V @ 1000mA

Connectors: 50 Pin IDC with cable lock. The OMG-PCI-DIO24 and OMG-PCI-DIO32 have one connector, the OMG-PCI-DIO48 has two connectors, and the OMG-PCI-DIO96 has four connectors.

Physical Dimensions:

OMG-PCI-DIO24,32:
 12 cm L x 9.39 cm H (4.72 x 3.7")
 OMG-PCI-DIO48,96:
 15.49 cm L x 10.41 cm H
 (6.1 x 4.1")

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model Number	Price	Description
OMG-PCI-DIO24	\$159	24 channel digital I/O board
OMG-PCI-DIO32	179	32 channel digital I/O board
OMG-PCI-DIO48	199	48 channel digital I/O board
OMG-PCI-DIO96	299	96 channel digital I/O board
OMG-TB07	40	50 pin terminal block (requires OMG-CA167)
OMG-CA167	10	40 inch 50 pin IDC cable, connects OMG-PCI-DIO boards to OMB-TB07
OMG-CA135	20	40 inch 50 pin edge cable, connects OMG-PCI-DIO to industry standard solid state relay racks

All boards include utility software and a complete user's manual on CD-ROM.
Ordering Example: OMG-PCI-DIO48 48 channel digital I/O board, two OMG-TB07 terminal panels and two OMG-CA167 cables, \$199 + 2 (40) + 2 (10) = \$299.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters