

OM-CP-THERMOVAULT Oven Temperature Data Logger

Part of the NOMAD® Family

\$999



Basic Unit

- ✓ Single Channel Thermocouple Input
- ✓ Programmable Start Time; Immediate or Date/Time
- ✓ Miniature Size
- ✓ Record Short Thermal Profiling Events

The OM-CP-THERMOVAULT is a thermally insulated, battery-powered, stand-alone data logger used for thermal profiling of events. This device can be used to record the temperature inside an oven for later downloading to a PC. This all-in-one, compact, portable, easy-to-use device will measure and record up to 16,383 temperature measurements. It can withstand an oven temperature of 752°F for 10 minutes when properly sealed. The OM-CP-THERMOVAULT is a major leap forward in both cost reduction and performance. Its real-time clock ensures that all data is time and date stamped. The storage medium is non-volatile solid state memory, providing maximum data security even if the battery becomes discharged. The thermovault's small size allows it to fit almost anywhere. Data retrieval is simple. Plug it into an available COM port and our easy-to-use software does the rest. The software converts your PC into a real-time strip chart recorder. Data can be printed in graphical or tabular format and can be exported to a text or Microsoft Excel file.

Specifications

Thermocouple Connection:

Fixed 2 position screw terminal

Cold Junction Compensation:

Automatic

Accuracy* (based on internal channel at uniform 20°C):

J, K, T, E, N: ±0.5°C

R, S, B: ±2.5°C

Resolution:

J, K, T, E, N: 0.1°C

R, S, B: 0.5°C

Memory: 16,383 readings/channel

Temperature Measurement Range: Type

J: -210 to 760°C

K: -270 to 1370°C

T: -270 to 400°C

E: -270 to 980°C

R: -50 to 1760°C

S: -50 to 1760°C

B: 50 to 1820°C

N: -270 to 1300°C

Recording Interval:

2 seconds to 12 hours selectable in software

Start Time: Start time and date are programmable through software

Power: 3.6 V lithium battery included

Battery Life: 1 year typical

Data Format: Date and time stamped, °C, °F, °K, °R, mV

Computer Interface: PC serial, RS-232C COM or USB
Software: XP SP3/Vista and 7 (32-bit and 64-bit)

Operating Environment for Internal Data Logger:

-40 to 80°C (-40 to 176°F)

0 to 95% RH non-condensing

Operating Environment for OM-CP-THERMOVAULT System:

-40 to 400°C (-40 to 752°F)


0 to 95% RH non-condensing

Dimensions: 76 H x 153 L x 102 mm D (3 x 6 x 4")

Weight: 0.9 kg (2 lbs)

Enclosure (Thermal Box): Thermal insulators encased in stainless steel

Enclosure (Logger): ABS Plastic



OM-CP-IFC200, \$129, Windows software displays data in graphical or tabular format

OM-CP-THERMOVAULT data logger, \$999, shown smaller than actual size

Maximum Exposure Temperature vs Duration	
Ambient Temp °C (°F)	Max Duration in Minutes**
100 (212)	52
150 (302)	30
200 (392)	22
250 (482)	17
260 (500)	16
300 (572)	15
350 (662)	12
400 (752)	10

* Accuracy does not include errors due to thermocouple.

** Assuming logger box is initially at 25°C.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
OM-CP-THERMOVAULT	\$999	Oven temperature data logger
OM-CP-THERMOVAULT-CERT	1059	Oven temperature data logger with NIST calibration certificate
OM-CP-IFC200	129	Windows software and 3.7 m (12') USB interface cable
OM-CP-BAT105	15	Replacement 3.6 V lithium battery

Operator's manual, battery and USB interface cable are included with the OM-CP-IFC200. Windows software (required to operate the data logger) is sold separately.

Ordering Example: OM-CP-THERMOVAULT-CERT, oven temperature data logger with NIST calibration certificate, OM-CP-IFC200, Windows software and USB interface cable, \$1059 + 129 = \$1188.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters