



OMG-PIO-24-LPCI

Low Profile PCI 24-Channel TTL I/O Board



\$159
All Models

OMG-PIO-24-LPCI, \$159,
Shown smaller than actual size



- ✓ 24 Channels of Buffered TTL I/O
- ✓ Each 8-Bit Port Individually Configurable as Input or Output
- ✓ 8255 Mode 0 Compatible
- ✓ 10K Pull up Resistors on Each Bit
- ✓ ±5V Power and Ground Provided on Connector
- ✓ MD1 Low Profile and Universal Bus (3.3 V and 5 V) Compatible
- ✓ Includes a 1 m (3.3') Ribbon Cable with (2) 26-Pin IDC Connectors to an Industry-Standard 50-Pin IDC Connector

The OMG-PIO-24-LPCI Low Profile PCI digital I/O interface provides 24 channels of buffered drive digital I/O emulating 8255 mode zero. The board can be utilized for PC-based control and automation of equipment including sensors, switches, security control systems, and other industrial automation systems.

10K pull-up resistors are included and optional values are available. The OMG-PIO-24-LPCI contains three groups of eight-bit I/O ports. Each group is individually configurable as input or output to suit the automation task.

The board is MD1 Low Profile and Universal Bus (3.3 V and 5 V) compatible and ships with a ribbon cable terminating in an industry-standard 50-pin IDC connector. The OMG-PIO-24-LPCI is for use in Low Profile PCI slots only. If you have a standard size PCI slot, order the OMG-PIO-24-PCI.

These boards are compatible with Windows 98/2000/XP and Linux and include programming support for Visual Basic 6 (and higher) and Visual C/C++.

Specifications

- Number of Channels:** 24 (TTL)
- Power Requirement:** ±5V @ 1A
- Output Specifications:** Sink up to 24 mA; source up to 15 mA
- Connector:** 50 pin header
- Operating Temperature:** 0 to 70°C (32 to 158°F)
- Storage Temperature:** -50 to 105°C (-58 to 221°F)
- Humidity Range:** 10 to 90% RH
- Dimensions:** 64 W x 119 mm L (2.5 x 4.7")
- Weight:** 45 g (1.6 oz)

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model Number	Price	Description
OMG-PIO-24-LPCI	\$159	LPCI 24 channel TTL digital I/O board
OMG-PIO-24-PCI	159	PCI 24 channel TTL digital I/O board

Each unit supplied with utility software, 1 m (3.3') ribbon cable with (2) 26-pin IDC connectors to an industry-standard 50-pin IDC connector and complete operator's manual on CD.

Ordering Example: OMG-PIO-24-LPCI low profile PCI 24 channel TTL digital I/O board and OMEGACARE™ 1 year extended warranty for the OMG-PIO-24-LPCI (adds 1 year to standard 1 year warranty), \$159 + 25 = \$184.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters