

Portable Handheld Data Logger

OM-DAQPRO-5300

- ✓ 8-Channel Data Logger—Measures Voltage; Current; PT100 RTD; J, K, T Thermocouples; 2252 Ω or 10 K Ω Thermistors; Frequency/Pulse Input
- ✓ Alarm Output
- ✓ 16-Bit Sampling Resolution
- ✓ Fast USB Communications
- ✓ Rapid Sampling—Up to 4000 Samples/Sec (Single Channel Burst Mode)
- ✓ Large Data Storage—512 KB RAM
- ✓ Graphical Display—Shows Collected Data as Measured Values, Graphs or Tables
- ✓ Multiple Logging Sessions—Stores up to 100 Recording Sessions
- ✓ Powerful Analysis Software for Windows 98/NT/2000/ME/XP/VISTA

The OM-DAQPRO-5300 is an 8-channel portable data acquisition and logging system with graphic display and built-in analysis functions. The data logger is powered by an internal rechargeable battery and is capable of sampling, processing and displaying measurements without being connected to a computer.

The OM-DAQPRO-5300 is a professional, cost-effective, compact and stand-alone data logging system that can be used with a wide variety of applications. This 16-bit, high-resolution, 8-channel data logger has graphic displays and analysis functions for measuring voltage, current and temperature in real time. With its high-resolution and fast analog-to-digital converter (ADC), the OM-DAQPRO-5300 meets the majority of data logging requirements in most industrial applications. Its unique ability to display measured values and analyze them in real time on a

Starts at
\$995



OM-DAQPRO-5300,
\$995, shown smaller
than actual size

graphical interface minimizes the need to download collected data to a computer for further analysis. Every OM-DAQPRO-5300 datalogger is embedded with a unique serial number and can be loaded with a descriptive comment for safe identification.

The data logger is very easy to use because all its functions are broken down into an 8-icon menu. The four buttons on the data logger's front keypad can be used to browse every menu and execute any of the commands.

Inputs

The OM-DAQPRO-5300 has eight input channels for measuring voltage, current, temperature and pulses. User-selectable input types/ranges are 0 to 24 mA, 0 to 50 mV, 0 to 10 V, 2252 Ω or 10 K Ω thermistors, PT100 RTDs, type J/K/T thermocouple temperature sensors, internal temperature, pulse counter, frequency meter and up to 20 user-defined sensors (used for scaling analog voltage or current inputs in engineering units).

The OM-DAQPRO-5300 can record data from up to eight 2-wire or four 3-wire PT100 RTD inputs (two input channels are required for each 3-wire PT100 RTD input connected). Frequency/pulse counter is only available for input 1.



The data logger provides a simple and straightforward tool for defining up to 20 custom sensors. Almost any 0 to 10 V and 4 to 20 mA sensor or transducer can be displayed and scaled in meaningful engineering units, e.g., psi or gpm. The sensor definitions are stored in the data logger's memory and are added to the sensors list. The sensor's readings are displayed in the user-defined units both on the OM-DAQPRO-5300's LCD screen and the Windows software.

The inputs use pluggable screw terminal blocks for easy connection. An internal clock and calendar keep track of the date and time of every sample measured.



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

The OM-DAQPRO-5300 data logger includes Windows software on CD ROM, 110 Vac adaptor, USB cable, operator's manual.



OM-DAQPRO-5300, \$995, with sensors, shown smaller than actual size

Outputs

The OM-DAQPRO-5300 can automatically activate an external alarm device, e.g., energize an audible alarm or turn on a warning light, when an input channel is outside a specified range (Input/Output 8 serves as either an input or an alarm output). The external alarm device (audible or visual alarm) is connected to the screw terminals of Input/Output 8. The alarm output is an open collector output, which is analogous to an electrical switch. High/low alarm levels and also whether the alarm output is activated during an out-of-limit condition can be set for each input channel individually.

Windows Software

The OM-DAQPRO-5300 system also comes with powerful Windows software. When the data logger is connected to a PC, live displays can be viewed at rates of up to 100 samples/sec, and automatic downloads can be carried out at higher rates.

The software can display the data in graphs, tables or meters; analyze data with various mathematical tools; or export data to a spreadsheet. The Windows software also enables you to set up the data logger and to send advanced commands such as alarm settings, triggering conditions and text notes.

Applications

- Quality Assurance
- Plant and Machine Condition Monitoring
- Field Monitoring Stations
- Automotive Testing
- HVAC
- Plant Trouble-Shooting
- Electricity Transients Failure Detection
- Environmental Monitoring
- Monitor Food, Drug and Electronic Equipment Storage Conditions
- Water Quality Testing
- Research

Specifications

INPUTS
Number of Inputs: 8 differential analog inputs
Input Type: Selectable type for each input: 0 to 24 mA, 0 to 50 mV, 0 to 10 V, 2252 Ω or 10 K Ω thermistor, PT100 RTD, J/K/T thermocouple, pulse and frequency (input 1 only)

0 to 24 mA
Range: 0 to 24 mA
Resolution: 0.47 μ A
Accuracy: $\pm 0.5\%$ FS
Loop Impedance: 21 Ω


0 to 50 mV
Range: 0 to 50 mV
Resolution: 3 μ V
Accuracy: $\pm 0.5\%$ FS
Input Impedance: 50 M Ω

0 to 10 V

Range: 0 to 10 V
Resolution: 200 μ V
Accuracy: $\pm 0.5\%$ FS
Input Impedance: 125 K Ω
TEMPERATURE THERMISTOR
Thermistor Type: 2252 Ω /10 K Ω Thermistor (OMEGA 44000 Series)
Range: -25 to 150°C (-13 to 302°F)
Resolution: 0.05°C
Accuracy: $\pm 0.5\%$ FS

TEMPERATURE PT100 RTD

RTD Type: 100 Ω Pt RTD, $\alpha = 0.00385$
Range: -200 to 400°C (-328 to 752°F)
Resolution: 0.1°C (7 m Ω)
Accuracy: -200 to -50°C, $\pm 0.5\%$ of reading; 50 to 400°C, $\pm 0.5\%$ of reading; -50 to 50°C, $\pm 0.5\%$
No. of RTD Inputs: Up to eight PT100 2-wire channels or four PT100 3-wire channels



Windows software displays data in graphical or tabular format

Windows software high/low alarm setup

The OM-DAQPRO-5300 data logger includes Windows software on CD ROM, 110 Vac adaptor, USB cable, operator's manual and carrying case



INTERNAL TEMPERATURE
Range: -25 to 70°C (-13 to 158°F)
Resolution: 0.1°C (1µV)
Accuracy: ±0.3°C

PULSE COUNTER (INPUT 1 ONLY) OPTOCOUPLER INPUT
Range: 0 to 65,000 counts
Resolution: 1 count
Input Signal: 0 to 5 V
Input Impedance: 470 Ω
Bandwidth: 0 to 25 Hz

FREQUENCY METER (INPUT 1 ONLY) OPTOCOUPLER INPUT
Range: 20 to 4000 Hz
Time Resolution: 6.5 µs
Input Signal: 0 to 5 V
Input Impedance: 470 Ω

GENERAL A/D SPECIFICATIONS
Noise: 30 µV RMS
Internal Linearity Error: ±0.08% of FSR
Offset Error: 0.1%

OPEN COLLECTOR ALARM OUTPUT (OUTPUT 8)
Maximum Current Sink: 50 mA @ 5 Vdc (fuse protected)
Input Impedance: 50 Ω

COMMUNICATION
 USB 1.1 compliant

SAMPLING
Capacity: 512 KB (512,000 samples total)
Analog Sampling Rate: The number of sensors in use limits the maximum sampling rate:
 1. Maximum sampling rate with one sensor is 4000 samples/sec
 2. Maximum temperature sampling rate 1 sample/sec
 3. Maximum sampling rate with two sensors or more is 1 sample/sec
 4. Maximum sampling rate with two PT100 RTD sensors or more is every 10 seconds
 5. Maximum sampling rate with five sensors or more and at least one thermistor or thermocouple (J, K or T) is every 10 seconds
 6. Maximum sampling rate with seven sensors or more is every 10 seconds
 7. Maximum sampling rate with eight PT100 RTD sensors or more is every 10 seconds
 8. Data logger displays readings in real time at rates up to 1 sample/sec
 9. Data logger software displays online readings at rates up to 1 sample/sec

Analog Sampling Resolution:
 16-Bits

MAN/MACHINE INTERFACE
Keyboard: Full keyboard operation—enables manual programming of the data logger
Display: graphic LCD 64 x 128 pixels

POWER SUPPLY
Power: Internal rechargeable 7.2 V Ni-MH battery, built in battery charger, external 9 to 12 Vdc input via included 110 Vac adaptor
Battery Life: 40 hrs between charges

OPERATING TEMPERATURE
Operating Temperature Range: 0 to 50°C (32 to 122°F)

MECHANICAL
Enclosure: ABS plastic
Dimensions: 182 H x 100 W x 28 mm D (7.17 x 3.94 x 1.10")
Weight: 450 g (1.0 lb)

STANDARDS COMPLIANCE
 CE, FCC


Thermocouple Table

Thermocouple Type	Range	Accuracy*	Resolution
J	-200 to -50°C (-328 to -58°F) -50 to 50°C (-58 to 122°F) 50 to 1200°C (122 to 2192°F)	±0.5% of reading ±0.5°C ±0.5% of reading	0.1°C (1µV)
K	-250 to -50°C (-418 to -58°F) -50 to 50°C (-58 to 122°F) 50 to 1200°C (122 to 2192°F)	±0.5% of reading ±0.5°C ±0.5% of reading	0.1°C (1µV)
T	-200 to -50°C (-328 to -58°F) -50 to 50°C (-58 to 122°F) 50 to 400°C (122 to 752°F)	±0.5% of reading ±0.5°C ±0.5% of reading	0.1°C (1µV)

* Accuracy does not include cold junction compensation (CJC). CJC error: ±0.5°C



The OM-DAQPRO-5300 data logger includes Windows software on CD ROM, 110 Vac adaptor, USB cable, operator's manual



Windows software displays data in graphical or tabular format

ANALYSIS SOFTWARE

Operating System: Windows 2000/ME/XP/VISTA

FEATURES:

- Fast data download
- Data displayed in numeric or graphical form
- Graphical analysis tools such as Zoom and Cursors
- Storage of selected data on disk files
- Hard-copy printing of the collected data
- Direct data export to Excel
- Online retrieval and display of data in real time
- Incorporates data processing functions
- Data logger setup
- Data logger calibration
- Defining new sensors

Maximum No. of Samples vs. No. of Input Channels

No. of Channels	Max. No. of Samples
1	512,000
2	256,000
3	128,000
4	128,000
5	64,000
6	64,000
7	64,000
8	64,000

OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

Ready-Made Insulated Thermocouples with Stripped Leads

5TC Series

\$33

5 Pack Basic Unit

MEETS OR EXCEEDS SPECIAL LIMITS OF ERROR (SLE) AND EN 60584-2: Tolerance Class 1


MADE IN USA

- ✓ Available from Stock in Convenient 5-Packs
- ✓ PFA Teflon[®], Kapton or Glass Braid Insulation
- ✓ 20, 24, 30, 36 and 40 AWG Wires
- ✓ 1 and 2 m (40 and 80") Lengths Standard
- ✓ NIST Calibration Available


For more information, please visit omega.com

Custom Lengths, Insulations and Configurations Available

"TT" PFA Teflon[®] insulation



"GG" Glass braid insulation



AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
OM-DAQPRO-5300	\$995	Portable handheld data logger (110 Vac adaptor)
OM-DAQPRO-5300-230VAC	995	Portable handheld data logger (230 Vac adaptor)

Accessories

Model No.	Price	Description
OM-DAQPRO-BOX	\$157	Weatherproof IP67 enclosure for data logger
OM-DAQPRO-COMCABLE	20	USB communications cable (spare)
OM-DAQPRO-110-ADAPTOR	15	110 Vac adaptor (spare)
OM-DAQPRO-220-ADAPTOR	15	220 Vac adaptor (spare)
OM-DAQPRO-5300-BATTERY	39	Rechargeable battery pack (spare)
OM-DAQPRO-5300-CONNECTOR	6	Input terminal block (spare)

Each OM-DAQPRO-5300 data logger includes Windows software on CD ROM, 110 Vac or 230 Vac adaptor, USB cable, operator's manual and carrying case. **Ordering Example:** OM-DAQPRO-5300 portable handheld datalogger and OCW-1, OMEGACARESM extends standard 1-year warranty to a total of 2 years (\$99), \$995 + 99 = \$1094.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters