



Wireless Vibration Transmitter

OMWT-VIB

Starts at
\$145



OMWT-VIB, \$145, shown actual size.




- Transmits up to 180 m (600')*
- Digital Broad Range Vibration Measurement via Internal Weighted Accelerometer
- 64-Bit Unique ID
- Up to 100 Sensors Can Coexist
- Compact ABS Enclosure
- Complies With Part 15 of the FCC Rules
- Internal Loop Antenna

The OMWT-VIB Wireless Vibration Transmitter is a battery operated digital vibration sensor with a microprocessor controlled 418 MHz FCC certified radio transmitter. This transmitter is useful in applications that need to sense when vibration is present or not or exceeds a threshold, e.g., to determine whether or not an engine is running. The OMWT-VIB has an on board time of day clock that allows it to spend most of the time in a low power quiescent state. At pre-determined time intervals the clock will wake up the onboard microprocessor. Unique serial number information and digital vibration data is combined with a CRC-16 error check and transmitted in a very short data packet that results in a transmitter on time of only 15 milliseconds. This architecture allows the OMWT-VIB to consume very low energy resulting in a battery life of up to 2 years.

The electronics are coated with a conformal rubber material that provides a moisture barrier against condensation. Submersion in water is not recommended. An integral pushbutton is used to activate the service switch. The OMWT-VIB is shipped with the transmitter turned off (anytime the device is to be shipped the transmitter should be turned off or must be placed in a shielded container to prevent interference that might cause shipping problems).

Using the OMWT Series Windows® software incoming data being received from OMWT Series Wireless Transmitters can be viewed in a real-time or historical time-base chart or numerical view. High/low alarms can also be set for each transmitter signal with either a visual or audible alarm indication on the PC. Data can also be logged to disk at a user-specified rate in a text file format that can be opened up into Microsoft Excel. The OMWT Series Windows software also includes a DDE Server that can interface the data being received from OMWT Series Wireless Transmitters to other Windows software packages.



OMWT-SOFT displays real-time historical chart or numerical data, \$100. Laptop not included.

SPECIFICATIONS

- Vibration Range:** Not a calibrated range (transmits a value of 0 to 100%)
- Transmission Frequency:** 418 MHz
- Transmission Range*:** Up to 180 m (600')
- Transmission Rate:** 30 to 37 sec
- Operating Temperature:** -40 to 85°C (-40 to 185°F)
- Storage Temperature:** -40 to 85°C (-40 to 185°F)
- Humidity:** 10 to 90% RH non-condensing
- Battery:** 3.6V, lithium battery (included)
- Battery Life with Transmissions:** 2 years
- Shelf Life with Battery Installed:** 4 years in quiescent mode
- FCC Certified:** FCC ID: M5ZVM1
- Dimensions:** 38 H x 53 W x 15 mm D (1.5 x 2.1 x 0.6")
- Weight:** 43 g (1.5 oz)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
MODEL NO.	PRICE	DESCRIPTION
OMWT-VIB	\$145	Wireless vibration transmitter
OMWT-REC232	222	Wireless receiver and 1.8 m (6') RS232 cable with DB9F termination
OMWT-SOFT	100	OMWT Series Windows® software (WIN98/NT/2000/XP)
OM-MLT-BATT	15	Replacement 3.6V lithium battery

Comes complete with 3.6V lithium battery and operator's manual.

* Depending on environmental conditions.

Ordering Example: OMWT-VIB wireless vibration transmitter, OMWT-REC232 wireless receiver and OMWT-SOFT Windows software, \$145 + 222 + 100 = \$467.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters