

# ECONOMICAL LIQUID TURBINE FLOWMETERS

FTB-1300 Series  
Starts at

**\$800**



- ✓ **±1% of Actual Flow Accuracy**
- ✓ **Pressure Rating Up to 345 bar (5000 psi)**
- ✓ **Stainless Steel Construction with Tungsten Carbide Bearing**
- ✓ **Easy Maintenance Design**

The FTB-1300 Series of turbine flow meters are designed for industrial and laboratory measurement of water, solvents and other low viscosity fluids. The FTB-1300 Series turbine flow meters feature a 316 stainless steel body and a tungsten carbide bearing. They offer good accuracy and reliability with very little pressure drop. The standard turbine flow meters feature threaded end connections.

The FTB-1300 series of turbine flow meters is designed with a wear resistant rotor assembly to provide trouble free operation and a long service life. Fluid moving through the flow meter causes the rotor to turn at a speed proportional to the flow rate, and as the rotor blades cut through the magnetic field of the pickup, an electronic pulse is generated. The pulse train is used to represent the actual flow or total amount of fluid passing through the flow meter. The number of electronic pulses generated per unit volume is known as a K-factor. The value is constant over each flow meter's operating range, and is unique to each meter.

## SPECIFICATIONS

**Accuracy:** ±1% reading  
**Pressure Max:** 345 bar (5000 psi)  
**Wetted Materials:** Stainless Steel (316L, 303 and 1.4122) and carbide with nickel binder (be sure that the operating fluid is compatible with these materials)



FTB-1302, \$860, 1.1 to 11 LPM flowmeter, shown smaller than actual size.


## Outputs

### Square Wave (FTB-1300 Models):

- Supply Voltage:** 10 to 28 Vdc
- Supply Current:** 8 mA @ 12 Vdc, 12 mA @ 24 Vdc
- Duty Signal:** 50% ±15%
- Minimum Signal:** 0.5 Hz
- Frequency Output:** Flow dependent, up to 2000 Hz
- Driving Capacity:** 50 mA Max resistive load
- Output Impedance:** ~ 40 Ω, analog switch and self-resetting fuse
- Temperature Range:** -40 to 85°C (-40 to 185°F)
- Cable Length:** 60 cm (24")


### Current (FTB-1310 Models):

- Supply Voltage:** 10 to 30 Vdc
- Input:** 0.25 Hz to 5 KHz
- Update Time:** 1/F + 25 msec
- Amplitude:** 1V p-p to 40V p-p
- Linearity:** ±0.01% of reading
- Output:** 4 to 20 mA
- Enclosure Certifications:** NEC Class I Groups C, D; Class II Groups E, F, G (FTB-1310 Series)
- Temperature Range:** -40 to 85°C (-40 to 185°F)





FTB-1313, \$1065, with 4 to 20 mA transmitter (standard) on FTB-1310 Series. Shown smaller than actual size.



Turbine Dimensions: mm (in)

Model No.	A	B	C	D	E*	F
FTB-13X1	76.2 (3)	34.29 (1.35)	30.48 (1.20)	½ NPT	55.88 (2.20)	97.79 (3.85)
FTB-13X2	76.2 (3)	34.29 (1.35)	30.48 (1.20)	½ NPT	55.88 (2.20)	97.79 (3.85)
FTB-13X3	76.2 (3)	34.29 (1.35)	30.48 (1.20)	½ NPT	57.15 (2.25)	100.33 (3.95)
FTB-13X4	76.2 (3)	34.29 (1.35)	30.48 (1.20)	½ NPT	57.15 (2.25)	101.6 (4)
FTB-13X5	76.2 (3)	39.37 (1.55)	35.56 (1.40)	1 NPT	62.23 (2.45)	104.14 (4.10)
FTB-13X6	76.2 (3)	39.37 (1.55)	35.56 (1.40)	1 NPT	64.77 (2.55)	107.95 (4.25)
FTB-13X7	76.2 (3)	54.61 (2.15)	49.53 (1.95)	1½ NPT	76.2 (3)	116.84 (4.60)
FTB-13X8	101.6 (4)	68.58 (2.70)	64.77 (2.55)	2 NPT	91.44 (3.60)	133.35 (5.25)

\* 4 to 20 mA output adds 168 mm (6.6") to the E dimensions for protection head.

**MOST POPULAR MODELS HIGHLIGHTED!**

**To Order (Specify Model Number)**

Model No.	Price	Fittings NPT	Range LPM	GPM	Pulses Per Gallon	Output and Description
FTB-1301	\$1013	½	0.3 to 1.5	0.08 to 0.4	125,000	Amplified square wave, 60 cm (24") cable
FTB-1302	860	½	1.1 to 11	0.3 to 3	48,000	
FTB-1303	800	½	3.4 to 34	0.9 to 9	15,000	
FTB-1304	875	½	6 to 60	1.6 to 16	10,500	
FTB-1305	890	1	6 to 60	1.6 to 16	10,500	
FTB-1306	925	1	11 to 121	3 to 32	1450	
FTB-1307	1005	1½	19 to 200	5 to 53	800	
FTB-1308	1405	2	49 to 757	13 to 200	100	
FTB-1311	1278	½	0.3 to 1.5	0.08 to 0.4	4 to 20 mA, industrial head electronics enclosure	
FTB-1312	1125	½	1.1 to 11	0.3 to 3		
FTB-1313	1065	½	3.4 to 34	0.9 to 9		
FTB-1314	1140	½	6 to 60	1.6 to 16		
FTB-1315	1155	1	6 to 60	1.6 to 16		
FTB-1316	1190	1	11 to 121	3 to 32		
FTB-1317	1280	1½	19 to 200	5 to 53		
FTB-1318	1670	2	49 to 757	13 to 200		

**Accessories**

Model No.	Price	Description
FTB-1310 CONNECTOR	\$68	Recommended for use with FTB-1311 through FTB-1318
DPF701	260	6-digit rate or total display (see page M-5 for complete details)

Comes complete with operator's manual.

For a 5-point NIST certificate, add suffix "-NIST" to model number, add \$670 to price.

**Ordering Examples:** FTB-1301, ½ male NPT turbine, 0.3 to 1.5 LPM (0.08 to 0.4 GPM) range with square wave frequency output and DPF701, ½ DIN digital panel LED display \$1013 + 260 = \$1273.

FTB-1313, stainless turbine with linear 4 to 20 mA output, ½ NPT connections and a range of 3.4 to 34 LPM (0.9 to 9 GPM), \$1065.

Recommended Reference Book: A First Course in Fluid Mechanics, FW-0121, \$80.  
Visit [omega.com/bobi](http://omega.com/bobi) for Additional Books





#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters