

# HIGH-TEMPERATURE LIQUID-LEVEL SWITCHES

## All Stainless Steel Construction

LV-40/50 Series

**\$75**




- ✓ Well Suited for Rough or Corrosive Liquids
- ✓ Water-Purifying and Medical Application Models
- ✓ High-Pressure Models up to 750 psi
- ✓ Normally Open or Normally Closed SPST Switch, User Selectable
- ✓ Mounts Vertically at Top or Bottom of Tank

LV-40, \$75, shown smaller than actual size.



LV-50, \$79, shown smaller than actual size.



Constructed entirely of 316 SS, the LV-40 single-station level switch is designed to withstand the effects of a wide range of chemicals. With a maximum operating temperature of 149°C (300°F), this switch is ideal for medical and water purification. Its small float displacement allows for high accuracy and reliability in shallow tanks and reservoirs.

See [omega.com/level\\_ref](http://omega.com/level_ref) for maximum voltage/current ratings.

The LV-50 Series level switches deliver superlative performance and dependability under the most severe operating conditions. The sensor incorporates a larger float displacement and all stainless steel construction for consistent level monitoring in liquids pressurized up to 750 psi. Ideal for level sensing in chemical plants and systems, models are available for temperatures up to 249°C (480°F).

### SPECIFICATIONS

**Stem Material:** 316 SS

**Float Material:** 316 SS

**Operating Temperature:**

-40 to 149°C (-40 to 300°F);

-40 to 249°C (-40 to 480°F) for LV-52

**Pressure Rating:** 100 psi for LV-40; 750 psi for LV-50 Series

**Mounting:** 1/2" NPT for LV-40; 1/2" NPT for LV-50 Series

**Switch:** SPST

**Switch Actuation:** Approx. 1/2 the distance from end of stem to mounting, or at halfway point of float travel


**Lead Wires:** 22 AWG, 24" polymeric; 18 AWG, 24" polymeric for LV-50 Series

**Specific Gravity of Float:**

LV-40: 0.62; LV-50: 0.64

To determine fluid specific gravity, add 0.1 to float specific gravity in clean liquids and 0.3 to float specific gravity in dirty or viscous liquids.

Solid State Relays Available!



For complete technical and ordering information, please refer to the OMEGA® Temperature Measurement Handbook®.

**MOST POPULAR MODELS HIGHLIGHTED!**

### To Order (Specify Model Number)

Model No.	Price	Temp. Rating	Switch Rating
LV-40	\$75	-40 to 149°C (-40 to 300°F)	10 VA
LV-50	79	-40 to 149°C (-40 to 300°F)	20 VA
LV-51	75	-40 to 149°C (-40 to 300°F)	100 VA
LV-52	122	-40 to 249°C (-40 to 480°F)	20 VA

Comes complete with operator's manual.

**Ordering Example:** LV-51, all stainless steel high-temperature liquid-level switch with a 100 VA rating, \$75.

LV-40, all stainless steel high temperature liquid-level switch with a 10 VA rating, \$75.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters