



Benchtop Microprocessor-Based Conductivity/Resistivity/TDS Meters

CDB-387
\$1531



- ✓ Measures 5 Conductivity Ranges, 4 TDS Ranges and 2 Resistivity Ranges (Additional Probes May Be Required)
- ✓ Autoranging for Maximum Resolution
- ✓ Analog and Digital Outputs Standard
- ✓ Standard RS232 Output

The CDB-387 is a microprocessor-based, benchtop conductivity, resistivity and TDS meter. The unit has a large LCD display and membrane keypad for easy operation. The meter features automatic temperature compensation, programmable temperature coefficient, recorder output and bi-directional RS232C output. The CDB-387 measures 5 conductivity ranges, 2 resistivity ranges and 4 TDS ranges. The CDB-387 will automatically select the most suitable range to provide maximum resolution.

The CDB-387 operates off ac power or a 9V battery. The 9V battery serves as a back-up to retain calibration data, even in the event of a power failure, and allows for portable field measurements. The unit is supplied with a glass dip-style conductivity cell with an integral temperature sensor, K = 1.0, calibration solutions and 9V adaptor.



Shown smaller than actual size.

Includes CDE-5001-GD1 glass dip style conductivity probe with integral temperature sensor. Replacement available, \$156.

Specifications

Conductivity Ranges:

0 to 20.00 $\mu\text{S}/\text{cm}$; 0 to 200.0 $\mu\text{S}/\text{cm}$;
0 to 2000 $\mu\text{S}/\text{cm}$; 0 to 20.0 mS/cm ;
0 to 200 mS/cm

TDS Ranges:

0 to 20.00 ppm; 0 to 200.0 ppm;
0 to 2000 ppm; 0 to 20 kppm

Resistivity Ranges:

0 to 2.000 $\text{M}\Omega/\text{cm}$, 0 to 20.00 $\text{M}\Omega/\text{cm}$

Accuracy: $\pm 1\%$ of reading

Automatic Temperature Compensation:

0 to 50°C (32 to 122°F)

Reference Temperature: 25°C (77°F)

[selectable 20°C (68°F)]

Temperature Coefficient: User

Temperature Measurement Range:

-30 to 130°C (-22 to 266°F)

Resolution: 0.1°C

Accuracy: $\pm 0.3^\circ\text{C}$

Recorder Output: 0 to 200 mV

Digital Output: Bi-directional RS232C

Power: 115 Vac with 9V adaptor

or 9V battery (included)


Display: 12.7 mm (0.5") LCD

Dimensions: 210 L x 150 W x 88 mm H
(8.3 x 5.9 x 3.5")

Weight: 600 g (1.3 lb)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
CDB-387	\$1531	Benchtop conductivity, TDS, resistivity meter, glass dip-style conductivity probe with integral temperature sensor, K = 1.0, calibration solution, 9V adaptor, RS232 output
CDE-5001-GD1	156	Glass dip-style conductivity probe, K = 1.0 with ATC, platinum plates, 12 x 130 mm (0.5 x 5.1")
CDE-5002-PD1	140	Polymer dip-style probe, K = 1.0 with ATC, platinum plates, 12 x 135 mm (0.5 x 5.3")
CDE-5004-ED10	326	Epoxy dip-style probe, K = 10 with ATC, carbon plates, 26 x 353 mm (1.0 x 13.9")
CDE-5014-GD01	160	Glass dip-style probe, K = 0.1 with ATC, platinum plates, 20 x 130 mm (0.8 x 5.1")
MN1604	3	Replacement 9V battery
FW-300	100	Reference Book: Water Wells and Septic Systems Handbook 

Comes complete with meter, CDE-5001-GD1 glass dip probe, conductivity solution, power adaptor, 9V battery and operator's manual.

Note: Other cell configurations are available. Contact OMEGA'S pH and Conductivity Engineers.

Ordering Example: CDB-387, benchtop conductivity/resistivity and TDS meter and CDE-5004-ED10, epoxy dip probe, \$1531 + 326 = \$1857.

Order Online

omega.com

Over 100,000 Products Available!

To download information and to order Conductivity Instrument products online, visit **omega.com**



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters