


SIDE-MOUNTED LIQUID-LEVEL SWITCHES

For High, Low, or Intermediate Level Sensing

LV-90/100
Starts at
\$34




LV-101, \$290, shown smaller than actual size.

LV-91A, \$34, shown smaller than actual size.

- ✓ Ideal for Tanks with Inaccessible Tops or Bottoms
- ✓ Low-Cost, Large-Volume OEM Models Available
- ✓ High-Pressure Models Up to 900 psi
- ✓ All-Polysulfone Models Suitable for Food Industry
- ✓ Easy to Install and Maintain

Compact, rugged, and virtually maintenance-free, the LV-90 Series level switch can meet the needs of large-volume OEMs. The sensor is designed for side mounting into tanks that have restricted space or inaccessible tops or bottoms. The all-polysulfone construction makes these switches compatible with a wide range of chemicals and is suitable for food processing applications. Magnetic SPST switch operation is normally open (dry) when units are installed with float downward, or normally closed (dry) when installed with float upward.

The LV-100 Series liquid-level switch requires side mounting into vessels, and is highly reliable. The unit should be installed in environments that are free from excessive contamination and high shock. LV-100 models are available with either Buna or 316 SS float material, both of which have positive float and cam action. These versatile level sensors feature SPDT switches that can be wired as either normally open or normally closed; other models feature SPST switches that are dedicated as either normally open or normally closed. For high-pressure applications, the switches constructed of 316 SS will withstand up to 900 psi. Visit omega.com/level_ref for maximum voltage/current ratings.



Dimensions: mm (in)

SPECIFICATIONS

Other Wetted Material:

304 SS, 316 SS, beryllium, copper, PFA, ceramic for LV-100; 304 SS, PFA, ceramic for LV-101, LV-102, LV-103

Mounting:

1/2 NPT for LV-90; 5/8"-11 thd. and locknut for LV-91; 1 NPT for LV-100 Series

Switch:

SPST; SPDT for models LV-100 and LV-101

Weight:

LV-90 Series: 42.5 g (1.5 oz)

LV-100 Series: 374 g (13.2 oz)

Lead Wires:

LV-90 Series:
22 AWG, 24" polymeric

LV-100 Series:
18 AWG, 24" polymeric

Liquid Specific Gravity:

0.8 minimum for LV-90 Series;
0.8 minimum for LV-100; 0.9 minimum for LV-101, LV-102, LV-103

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Switch Rating	Stem/Float	Maximum		Liquid Spec. Gravity
				Temp.	Pres.	
LV-91A	\$34	20 VA	Polypropylene	225°F	100 psi	0.8 min
LV-100	195	20 VA	Brass/Buna	180°F	150 psi	0.8 min
LV-101	290	20 VA	316 SS	300°F	900 psi	0.9 min
LV-102	315	100 VA (NO)	316 SS	300°F	900 psi	0.9 min
LV-103	315	100 VA (NC)	316 SS	300°F	900 psi	0.9 min

Comes complete with operator's manual.

* LV100 Series has CE approval.

** LV-91A is UL rated.

NO = normally open; NC = normally closed.

Ordering Examples: LV-100, side-mounted liquid-level switch with a brass stem and Buna float, \$172.

LV-91A, side mounted liquid level switch with Polypropylene stem and float, \$34.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters