

PORTABLE CONDUCTIVITY METERS WITH BUILT-IN PRINTER

\$570
CDH-35P

- ✓ Programmable Temperature Coefficient
- ✓ Built-In Printer Uses Non-Fading Paper
- ✓ Single Probe Measures from 0.01 $\mu\text{S}/\text{cm}$ to 199.0 mS/cm
- ✓ Automatic Shut-Off Preserves Battery Life

The Model CDH-35P portable conductivity meter with built-in printer offers maximum precision with automatic calibration using five memorized standard values, automatic temperature compensation, and a 4-ring potentiometric probe.

Not only is the CDH-35P precise, but it is also easy and convenient to use. Ideal for monitoring processes, the meter has a datalogging feature that allows users to take measurements at user-selectable intervals of 1 to 180 minutes. The built-in printer uses regular, non-fading paper for permanent recordkeeping. An automatic shut-off system and a 12 VDC power socket feature help maintain long battery life.



EE
pH

SPECIFICATIONS

Range:

Conductivity:

0.0 to 150.0 $\mu\text{S}/\text{cm}$
0 to 1500 $\mu\text{S}/\text{cm}$
0.00 to 15.00 mS/cm
0.0 to 199.9 mS/cm

Temperature:

0 to 60°C (32 to 140°F)

Resolution:

Conductivity: 0.1 $\mu\text{S}/\text{cm}$,
1 $\mu\text{S}/\text{cm}$, 0.01 mS/cm , 0.1 mS/cm
Temperature: 0.1°C

Accuracy:

Conductivity: 1% Full Scale
Temperature: $\pm 0.5^\circ\text{C}$ ($\pm 0.9^\circ\text{F}$)

Calibration: Automatic 1 point at 0, 84, 1413, 12, 880 or 80,000 $\mu\text{S}/\text{cm}$

Temperature Compensation:

Automatic from 0 to 60°C (32 to 140°F) with a variable β from 0.0 to 3.0%/°C

Printer: Low-power impact type-belt, 14 characters per line using 38 mm (1.5") plain, non-fading paper

Printing Interval:

Selectable: 1, 2, 5, 10, 15, 30, 60, 120 or 180 minutes

Environment:

0 to 50°C (32 to 122°F), 100% RH

Dimensions:

196 x 80 x 57 mm (7.7 x 3.1 x 2.2")

Battery Type/Life:

4 x 1.5 V/500 hours with 60-minute measuring intervals, power socket for 12 Vdc supply

Weight: 425 g (15 oz)

To Order (Specify Model Number)		
Model No.	Price	Description
CDH-35P	\$570	Portable conductivity meter with printer, 4-ring probe with 1 m (3') cable and hard plastic carrying case
CDE-35	142	4-ring probe with 1 m (3') cable (replacement)

Ordering Example: CDH-35P, portable conductivity meter with printer, 4-ring probe with 1 m (3') cable and hard plastic carrying case, \$570.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters