



pH FIELD & LAB INSTRUMENTS

pH/mV Bench Meter



PHE-1411 electrode, \$63.

Shown smaller than actual size.

PHB-209 is supplied with combination double-junction refillable pH electrode with 1 m (3.3') cable, 12 Vdc adaptor, and operator's manual.

PHB-209
\$295




- ✓ **Oriented for Simplicity**—PHB-209 was Built Around the Idea Of Simplicity with a Large LCD, Easy-to-Operate Knobs, and a pH/Temperature Chart on the Front Panel
- ✓ **User-Friendly Design**
- ✓ **Manual Calibration**—To Illustrate the Calibration Process, Manual Potentiometers Allow the User to Adjust the Offset and Slope Characteristics

The rugged ABS casing with sturdy knobs, and a reference chart for pH and temperature on the front panel make PHB-209 an ideal meter for all users. The keypad has membrane keys for changing the mode and knobs for slope and offset calibration. The pH offset and slope are manually adjustable in order to display the calibration concept and the electrode characteristics to the students. Measurements can be performed for pH with manual temperature compensation as well as for REDOX (Reduction Oxidation Potential). The selected temperature is displayed to ensure better accuracy. The LCD displays the temperature comprehensively while manually compensating for its effects. Practicality, simplicity and comprehensive operating procedures in addition to an affordable price make this meter one of the most popular, basic pH meters available today. A rugged double-junction refillable pH electrode and 12 Vdc power supply are also included.

Specifications

- Range:** 0.00 to 14.00 pH; ± 1999 mV
- Resolution:** 0.01 pH; 1 mV
- Accuracy (@68°F/20°C):** ± 0.01 pH; ± 0.1 mV
- Typical EMC Deviation:** ± 0.03 pH; ± 2 mV
- pH Calibration:** Manual 2 points through offset and slope knobs
- Temperature Compensation:** Manual from 0 to 100°C (32 to 212°F)
- Electrode:** Combination double-junction refillable pH electrode BNC with 1 m (3.3') cable (included)
- Input Impedance:** $10^{12} \Omega$
- Power Supply:** 110 Vac to 12 Vdc adaptor included
- Environment:** 0 to 50°C (32 to 122°F); 95% R.H.
- Dimensions:** 240 L x 182 W x 74 mm D (9.4 x 7.2 x 2.9")
- Weight:** 1.0 kg (2.2 lb)

AVAILABLE FOR FAST DELIVERY!

| To Order (Specify Model Number) | | |
|---------------------------------|-------|---|
| Model No. | Price | Description |
| PHB-209 | \$295 | pH/mV benchtop meter with pH electrode |
| PHE-1411 | 63 | Double junction, plastic body, gel-filled combination pH electrode with 1 m (3.3') cable |
| ORE-1411 | 91 | Double junction ORP probe |
| PHA-77 | 35 | Third arm electrode holder |
| PHA-4 | 5 | 4.00 pH buffer solution 500 ml (1 pint) bottle |
| PHA-7 | 5 | 7.00 pH buffer solution 500 ml (1 pint) bottle |
| PHA-10 | 5 | 10.00 pH buffer solution 500 ml (1 pint) bottle |
| PHB-200PS | 11 | 220 Vac to 12 Vdc adaptor |
| CM-4448 | 100 | Reference Book: Rules of Thumb for Chemical Engineers  |

Comes complete with pH electrode, BNC with 1 m (3.3') cable, 110 Vac to 12 Vdc adaptor and operator's manual.

Ordering Example: PHB-209, pH/mV benchtop meter, PHA-4, 4.00 buffer solution, PHA-7, 7.00 buffer solution, \$295 + 5 + 5 = \$305.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters