



## Colorimeter Reagent Systems

- ✓ Over 50 Pre-Programmed Water Analysis Factors
- ✓ Automatic Wavelength Selection
- ✓ Friendly Menu-Driven Operation with Simple Six-Button Keypad

SC-1919  
Starts at  
**\$900**



The user-friendly SC-1919 Colorimeter is the direct reading colorimeter for complete on-site water analyses. All pre-programmed tests can be run on this compact instrument and each test features automatic wavelength selection. The entire multi-LED optical system is embedded in the light chamber and optimized for OMEGA test reagent systems. This enables the analyst to simply select the test and put in the sample with reagent. The microprocessor, which selects the wavelength, also allows the user to load up to 10 tests for analyzing custom reagent systems.

The SC-1919 Colorimeter is a portable, microprocessor controlled, direct reading colorimeter. It has a graphical 4 line, 16 character liquid crystal display for graphical, alphabetical and numerical messages. The operation is controlled with the keypad through menu driven software in response to selections shown on the display.

The test library consists of 100 tests (not all 100 may be available at present) and 10 "User Tests". The tests are precalibrated for the reagent systems. The colorimeter displays the results of these tests directly in units of concentration. The 10 "User Tests" may be used to enter additional calibrations. All of these tests may be arranged in any of 3 sequences. These sequences can be modified a limitless number of times to meet changing testing needs.

The optics feature 4 different colored LEDs. Each LED has a corresponding silicon photodiode with an integrated interference filter. The interference filters select a narrow band of light from the corresponding LED for the colorimetric measurements. The microprocessor automatically selects the correct LED/photodiode combination for a test. An RS232 serial port on the back of the colorimeter, and optional software, allows the SC-1919 to be interfaced with a personal computer for real time data acquisition and data storage. This port also allows an interface with a RS232 serial printer.

Due to its portability, alternate power sources, and rugged construction, the SC-1919 Colorimeter is ideal for lab and field use.



SC-1919, \$900 shown smaller than actual size.

**MOST POPULAR MODEL HIGHLIGHTED!**

### To Order (Specify Model Number)

Model No.	Price	Description
SC-1919	\$900	Colorimeter with 4 sample tubes, AC adapter, and instruction manual, 120V, 60 Hz
SC-1919-LCS	177	Large carrying case
SC-1919-SCS	106	Small field carrying case
SC-1912-CD-01	186	Interface cable/communication program on CD

Comes complete with 4 sample tubes, AC adaptor, battery, and instruction manual.

For 230V add -230V. No additional cost.

**Ordering Example:** SC-1919, digital colorimeter, SC-1912-CD-01 communication program and cable, SC-1919-SCS small carrying case, \$900 + 186 + 106 = \$1192.

Recommended Reference Book: Wastewater Treatment, ES-2253, \$159  
See Section Y For Additional Books



### Specifications

**Light Source:** LED/filter setup at 430nm, 520nm, 570nm, 630nm

**Detector:** Photodiode

**Display:** 122 x 32 LCD, 16 x 4 line graphics display

**Range:** 0 to 125%T

**Resolution:** 1% FS

**Accuracy:** 2% FS

**CE Mark:** Yes

**Sample Cell:** 25 mm (0.99") round cell, 10 mm (0.39") square cuvette, 16 mm (0.63") COD tubes



**Power:** 9V battery or AC adapter (included)  
**Battery Life:** 500 tests  
**Datalogging:** RS232, time and date stamped  
**Calibration:** Factory set  
**Keypad:** 6-button membrane switch  
**Size:** 15 x 8 x 5.5 cm (6 x 3.25 x 2.5")  
**Weight:** 900 g (2 lb)

The SC-1919 Colorimeter is complemented by easy-to-use reagent systems. Choose the desired test factors from the list below. Several packaging options are available for field use, making your SC-1919 Colorimeter a "field laboratory."

OMEGA uses ACS raw materials to manufacture reagent systems that have high reproducibility. We design our reagent systems to overcome test interference so results are fast and dependable.



SC-1919, \$900, shown smaller than actual size.

Model No.	Price	Test Factor	Range (ppm)	Test Method (# of Reagents)	# of Tests	Case Size*
SC-3641	\$68	Aluminum	0 to 0.3	Eriochrome Cyanine R (4)	50	L
SC-3643-B	50	Bromine	0 to 9.0	DPD Tablets (2)	100	S
SC-3643-C	50	Chlorine	0 to 4.0	DPD Tablets (2)	100	S
SC-3644	30	Chlorine Dioxide	0 to 8.0	DPD Tablet/Glycine (2)	50	S
SC-3646	16	Copper	0 to 6.0	Diethyldithiocarbamate (1)	100	S
SC-3640	55	Copper	0 to 3.5	Bicinchoninic Acid (1)	50	S
SC-3660	86	Cyanide	0 to 0.35	Pyridine-Barbituric Acid (5)	50	L
SC-3661	37	Cyanuric Acid	0 to 200	Melamine (1)	50	L
SC-3647	45	Fluoride	0 to 2.0	SPADNS (2)	50	L
SC-3662	37	Hydrogen Peroxide	0 to 1.5	DPD Tablets (2)	100	S
SC-3648	37	Iron	0 to 6.0	Bipyridyl (2)	50	S
SC-3668	40	Iron	0 to 5.0	1,10 Phenanthroline (2)	50	S
SC-4031	70	Lead	0 to 5.0	PAR (5)	50	S
SC-3669	75	Manganese (HR)	0 to 15.0	Periodate (2)	50	S
SC-3699-01	50	Molybdenum	0 to 50	Thioglycolate (3)	50	L
SC-3649	41	Nitrate	0 to 3.0	Cadmium Reduction (2)	20	S
SC-3650	41	Nitrite	0 to 0.8	Diazotization/Coupling (2)	20	S
SC-3688	37	Oxygen, Dissolved	0 to 11.0	Winkler Colorimetric (3)	200	S
SC-3651	195	Ozone	0 to 0.4	Indigo Trisulfonate (3)	100	L
SC-3700	45	pH	5.0 to 9.6	Colorimetric (3)	100	L
SC-3652	49	Phenols	0 to 6.0	4-Aminoantipyrine (3)	50	L
SC-3655	20	Phosphate (HR)	0 to 70.0	Molybdovanadate (1)	50	S
SC-3639	52	Potassium	0.5 to 10.0	Tetraphenylboron (2)	100	S
SC-3664	49	Silica	0 to 4.0	Heteropoly Blue (4)	100	S
SC-3687	37	Silica (HR)	0 to 75	Silicomolybdate	50	S
SC-3665	26	Sulfate	0 to 100	Barium Chloride (1)	100	S
SC-3654	58	Sulfide	0 to 3.0	Methylene Blue (3)	50	L
SC-3666	46	Tannin	0 to 10	Tungsto-Molybdophosphoric Acid (2)	50	L

Kit contents vary. Each kit comes complete with everything necessary to perform the specified test.

Ordering Example: SC-3641, aluminum reagent test kit, \$68.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters