

BENCHTOP DISSOLVED OXYGEN METERS DOB-930



DOB-930
\$1420



Model PRT-341,
Printer (optional),
\$725

- ✓ % Concentration and PPM Readings
- ✓ Includes Swing Arm Holder
- ✓ Analog and RS-232 Outputs
- ✓ B.O.D. Mode Feature
- ✓ Alarms


The DOB-930 benchtop dissolved oxygen meter uses a Clark-type polarographic electrode, optimized for both stability and speed of response. Dissolved oxygen levels can be measured either as % saturation or as concentration in mg/l (ppm). The meter also has a mode dedicated to the determination of B.O.D. (Biochemical Oxygen Demand).

The graphics mode liquid crystal display facilitates plain-language, menu-based operating procedures and clear presentation results. The results phase permits the simultaneous display of dissolved oxygen level and temperature.

The sensor measures the partial pressure of oxygen, with the reported results influenced by atmospheric pressure. The DOB-930 allows atmospheric pressure and salinity values to be entered through the menu options for automatic correction.

A real-time clock is built into the meter and displays either day, month and year or seconds, minutes and hours. The clock feature also enables calibration checks to be prompted at intervals determined by the operator.

The unit includes a 100-location memory for logging the results for subsequent recall to the display or downloading via the bi-directional RS-232 link to a printer or PC.



Set-up Menu



Standard Display

SPECIFICATIONS:

DO₂:

Ranges: 0 to 199%, 0 to 25.0% or 0 to 19.99 mg/l

Resolution: 1%, 0.1%, 0.01 mg/l

Accuracy: ±2% within 10°C (18°F) of calibration temperature

TEMPERATURE:

Ranges: -10 to 60°C, (14 to 140°F)

Resolution: 0.1°C/1°F

Accuracy: ± 0.5°C/±1°F

ATC range:

0 to 60°C (32 to 140°F)

Outputs:

Analog 1 mV per digit, bi-directional RS-232, Hi/Lo Alarm outputs, open collector 0.5 A 50 V max

Clock: 24 hour, hours/min/sec or day, month year (leap year corrected)

Stirrer speed: 0 to 100%

Alarm points:

0 to 199.9% and 0 to 19.99 mg/L; calibration reminder

Display: LCD graphics

Power: 115 ac adaptor supplied, (power supply 9 V ac)

Size: 275 L x 240 W x 150 mm D (10.8 x 9.5 x 5.9")

Weight: 1.2 kg (2.6 lb)

To Order (Specify Model Number)

Model No	Price	Description
DOB-930	\$1420	Benchtop dissolved oxygen meter with probe, ATC probe, swing arm holder, spare membranes, KCl filling solution, zero powder, and power supply

Ordering Example: DOB-930, benchtop dissolved oxygen meter with probe, ATC probe, swing arm holder, spare membrane, KCl filling solution, zero powder and power supply, \$1420





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters