

# OMEGA-FLO® 2-WAY GENERAL PURPOSE SOLENOID VALVES

1/8 TO 1/4 NPT

SV-300 Series Starts at

**\$109**



- Ideal for Natural Gas, Air, and Water
- Available in Brass or Stainless Steel
- Temperature Range to 90°C (194°F)
- 120 Vac Standard (DC Optional)

The SV-300 Series 2-way solenoid valves have a brass or stainless steel body and seat, stainless steel valve internals, and Viton® seal material. Temperature range is -10 to 90°C (14 to 194°F). These valves are ideal for neutral media such as compressed air, natural gas, water, and hydraulic oil (viscosity of approximately 2.3 x 10<sup>-4</sup> ft<sup>2</sup>/s).

## Specifications

**Mounting Position:** Any (preferably with the solenoid system upright)

**Max Ambient Temp:** 54°C (130°F)

**Voltage Tolerance:** ±10%

**Power Consumption (in Warm State):**

**AC:** 21 (inrush); 12 VA/8 W (hold)

**DC:** 8 W

**Opening Time (ms):** Approx. 20, depending on pressure

**Closing Time (ms):** Approx. 30

**Cycling Rate:** Approx. 1000 cpm

*(Times measured at outlet A on energizing/de-energizing until attainment of pressure rise to 90%/pressure drop to 10% at a working pressure of 85 psi.)*

## Accessory

Model No.	Price	Description
FW-306	\$125	Reference Book: Valve Handbook



Technical Books Available Online!

books1.com™  
omega.com

## Duty Cycle:

Continuous (100%)

## FM Approvals:

Non-incendiary for hazardous locations Class I Div. 2 Group A, B, C, D; Class II Div. 2 Group F, G; Class III Div. 1 and 2; Operating Temperature T4A

## Options (no additional charge)

Ordering Suffix	Description
-24VDC	24 Vdc operation
-12VDC	12 Vdc operation
-240VAC	240 Vac operation
-BUNA	Buna-N seal

Options not available on all models.



SV-301, \$109, shown smaller than actual size.

**MOST POPULAR MODELS HIGHLIGHTED!**

## To Order (Specify Model Number)

Model No.	Price	Port Conn. (NPT)	Cv	Pressure Range (psi) <sup>1</sup>		Max Allow. Back Pressure (psi)	Orifice Dia.	Body Material
				AC	DC			
<b>Normally Closed Valve</b>								
SV-301	\$109	1/8	0.14	0 to 355	0 to 230	70	5/64"	BR
SV-302	148	1/8	0.14	0 to 355	0 to 230	70	5/64"	SS
SV-303	116	1/4	0.14	0 to 355	0 to 230	70	5/64"	BR
SV-304	173	1/4	0.14	0 to 355	0 to 230	70	5/64"	SS
SV-305*	93	1/8	0.19	0 to 230	0 to 140	50	7/64"	BR
SV-306	173	1/8	0.19	0 to 230	0 to 140	50	7/64"	SS
SV-307	109	1/8	0.27	0 to 140	0 to 85	35	1/8"	BR
SV-308	148	1/8	0.27	0 to 140	0 to 85	35	1/8"	SS
SV-309	109	1/4	0.37	0 to 55	0 to 20	9	5/32"	BR
SV-310	173	1/4	0.37	0 to 55	0 to 20	9	5/32"	SS
SV-311	173	1/4	0.82	0 to 20	0 to 7	4	1/4"	BR
SV-312	173	1/4	0.82	0 to 20	0 to 7	4	1/4"	SS
<b>Normally Open Valve</b>								
SV-321	\$122	1/8	0.14	0 to 170		70	5/64"	BR
SV-322	138	1/4	0.14	0 to 170		70	5/64"	BR
SV-323*	118	1/8	0.19	0 to 115		50	7/64"	BR
SV-324	138	1/4	0.19	0 to 115		50	7/64"	BR
SV-325	118	1/8	0.27	0 to 85		35	1/8"	BR
SV-326	138	1/4	0.27	0 to 85		35	1/8"	BR

<sup>1</sup> Also suitable for vacuum down to 38 torr.

\* The SV-305 and SV-323 are not UL listed.

Comes with complete operator's manual.

**Ordering Examples:** SV-303, normally closed valve, 0.14 Cv, \$116.

SV-303-24VDC, normally closed valve with 24 Vdc coil, \$116.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters