



DISSOLVED OXYGEN INSTRUMENTATION

2-Wire Isolated Dissolved Oxygen Transmitter System

DOTX-45
\$1325
Complete System



DOTX-45 transmitter,
\$675, shown smaller
than actual size.

- ✓ Reliable 3-Electrode Amperometric Sensor
- ✓ Replaceable Sensor Cartridge
- ✓ Sensor Membrane Puncture/Tear Diagnostic
- ✓ Microprocessor-Based System
- ✓ Large, Dual-Display Format
- ✓ Loop Powered, Fully Isolated

Sensor Features

The DOE-45PA dissolved oxygen sensor is a highly dependable membrane-covered galvanic sensor. The polymer membrane has hydrophobic properties to help resist fouling from biological growth and maximize diffusion of oxygen into the sensor. The DOE-45PA also has automatic temperature compensation to correct for membrane permeability errors.

Transmitter Features

The microprocessor-based transmitter is loop powered and fully isolated for high reliability. The transmitter includes devices that protect the system from power surges and brownout events. The large, high-contrast, super-twist display is readable over a wide operating temperature range, even in low-light conditions. The main display line consists of large, segmented characters with measurement units. The secondary display line displays calibration and diagnostic messages in readable dot-matrix characters. Two of four measured parameters can be displayed simultaneously. Programming is intuitive, with a 4-button, menu-driven interface. The 4 to 20 mA transmitter output can be configured to represent any portion of the measurement range. Output hold, alarm, and simulation features give the user complete control of the system output under any condition. Diagnostic messages clearly describe system conditions, which eliminates confusing error codes. The flexible calibration method includes stability monitors that check temperature and main parameter stability before accepting data.



Specifications (DOE-45PA Sensor)

- Measuring Range:** 0 to 40 ppm
- Sensor Cable:** 9.1 m (30')
- Measurement Response Time:** 90% in less than 3 minutes
- Measurement Principle:** Membrane covered galvanic
- Electrode Material:**
 - Cathode:** Platinum
 - Anode:** Lead
- Electrolyte:** Potassium chloride based
- Pressure Range:** 0 to 150 psig @ 25°C (77°F)
- Temperature Compensation:** Pt100
- Temperature Range:** -5 to 55°C (23 to 131°F)
- Minimum Flow Rate:** 6 mm (0.02") per second

- Membrane Thickness:** 50 microns
- Membrane Material:** FEP (fluorinated ethylene propylene)
- Wetted Materials:** 316 SS, FKM, Noryl
- Sensor Cable:** 5-conductor
- Sensor-to-Transmitter Distance:** 305 m (1000')
- Mounting:** Submersion 1 NPT
- Shipping Weight:** 0.45 kg (1 lb)

Specifications (DOTX-45 Transmitter)

- Performance Specifications**
- Displayed Parameters:** Main input, 0 to 40.0 ppm
- % Saturation:** 0 to 200%
- Loop Current:** 4 to 20 mA
- Sensor Temperature:** 0 to 50°C (32 to 122°F)
- Power:** 16 to 35 Vdc

DISSOLVED OXYGEN INSTRUMENTATION



Main Parameter Range: 0 to 40 ppm
Repeatability: 0.1% of span or better
Sensitivity: 0.05% of span
Non-Linearity: 0.1% of span
Stability: 0.1% of span per 24 hours, non-cumulative
Warm-Up Time:
 4 seconds to rated performance
Supply Voltage Effects: ±0.05% of span
Transmitter Response Time: 4 seconds to 90% of step input at lowest setting
Temperature Drift: Span or zero, 0.02% of span/°C
Temperature Compensation: 0 to 50°C (32 to 122°F), Pt1000 element; sensor is internally compensated for membrane permeability changes with temperature
Sensor-to-Transmitter Distance: 305 m (1000')
Enclosure: NEMA 4X (IP66), polycarbonate, stainless steel hardware, weatherproof and corrosion resistant, 112 H x 112 W x 89 mm D (4.4 x 4.4 x 3.5")
Mounting Options: Wall, panel, pipe, DIN rail, integral-sensor
Conduit Openings: 2-PG9 openings, 1-1 NPT center opening, cordgrips and plug included
Weight/Shipping Weight: 0.45 kg (1 lb)
Display: Large, high-contrast, super-twist LCD; 4-digit main display with sign, 19.1 mm (0.75"), 7-segment characters; 12-digit secondary display, 7.6 mm (0.3") 5 x 7 dot matrix character
Keypad: 4-key membrane type with tactile feedback, polycarbonate with UV coating, integral EMI/static shield and conductively coated window
Operating Temperature: -20 to 60°C (-4 to 140°F)
Storage Temperature: -30 to 70°C (-22 to 158°F)
Ambient Humidity: 0 to 95%, non-condensing
Location: Designed for hazardous and non-hazardous areas
EMI/RFI Influence: Designed to EN 61326-1
Voltage Range: 16 to 35 Vdc (2-wire device)
Output Isolation: 600V galvanic isolation
Transmitter Cable Type: Belden twisted-pair, shielded
Filter: Adjustable 1 to 99 seconds additional damping to 90% step input
Temperature Input: Selectable Pt1000 or Pt100, automatic compensation

DOTX-45, \$675.



DOE-45PA sensor, \$650, sold separately, shown smaller than actual size.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
DOTX-45	\$675	Dissolved oxygen transmitter
DOTX-45-115VAC-R2	925	Dissolved oxygen transmitter with relays
DOE-45PA**	650	Dissolved oxygen sensor
PSU-93	40	Unregulated power supply
PHTX-45-SMH	95	Submersion mounting hardware, 1.8 m (6')

Accessories

Model No.	Price	Description
DOE-45PA-DOE**	\$35	DO electrolyte, 4 oz bottle
DOE-45PA-EC	35	Electrolyte chamber
DOE-45PA-MH	30	316 SS membrane holder
DOE-45PA-RLE	15	Replacement lead electrode
DOE-45PA-RM**	15	Membranes, 5 mil 10-pack
DOE-45PA-SE	200	Submersible sensing-element body
DOE-45PA-SH	400	Submersible sensing-element holder assembly
DOE-45PA-SM	250	Submersible sensing module

Comes complete with wall mount bracket and operator's manual.

** When purchasing the DOE-45PA for the first time it is necessary to also purchase the DOE-45PA-DOE electrolyte solution and DOE-45PA-RM membranes.

Ordering Examples: DOTX-45, dissolved oxygen transmitter, DOE-45PA, sensor, DOE-45PA-DOE, electrolyte solution 4 oz bottle, DOE-45PA-RM, 5 mil 10-pack membranes, \$675 + 650 + 35 + 15 = \$1375.

Ordering Examples: DOTX-45, dissolved oxygen transmitter, DOE-45PA, sensor, PSU-93, unregulated power supply, DOE-45PA-DOE, electrolyte solution 4 oz bottle, DOE-45PA-RM, 5 mil 10-pack membranes, DOE-45PA-MH, 316SS membrane holder, \$675 + 650 + 40 + 35 + 15 + 30 = \$1445.

Recommended Reference Book:
 Handbook of Drinking Water Quality,
 ES-2036, \$160. Visit
omega.com/bobi for Additional Books



Order Online
omega.com[®]
 Over 100,000 Products Available!

To download information and to order Dissolved Oxygen Instrumentation products online, visit omega.com



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters