

OMEGA-FLO® 2-WAY STEAM SOLENOID VALVES ½ to 2 NPT

SV-400 Series
Starts at

\$460



- ✓ Works for Steam or Hot Water
- ✓ Temperatures up to 180°C (356°F)
- ✓ Zero Differential Pressure
- ✓ 120 Vac Operation
- ✓ Normally Closed

SV-400 Series 2-way solenoid valves are internally piloted, with a piston, forced lifting, and an epoxy-encapsulated coil. The valve opens fully from 0 psi pressure differential. These valves have a brass body, stainless steel valve seats, PTFE sealing materials for the main seat, and a temperature range from 0 to 180°C (32 to 356°F). They are ideal for neutral media such as steam and hot water; for use on the vacuum side of autoclaves; and in the textile, plastics, and woodworking industries.

SPECIFICATIONS

Mounting Position:

Any (preferably with solenoid system upright)

Max Ambient Temp: 54°C (130°F)

Voltage Tolerance: ±10%

Power Consumption:

Orifice Size	Inrush	Hold
½ to 1½"	120 VA	35 VA/16 W
2"	28 W	28 W

Response Times:

Orifice Size	Opening Time (ms)	Closing Time (ms)
½ to 1"	100 to 200	300 to 500
1½ to 2"	200 to 1200	1000 to 3000

Note: Response times are measured with water at an operating pressure of 85 psi. They depend on the nominal size of the valve as well as on the pressure and viscosity of the medium.

Cycling Rate: Approx. 60 cpm

Duty Cycle: Continuous (100%)

Normally Closed Valve

MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)							
Model No.	Price	Port Connection (NPT)	Cv	Pressure Range ¹ (psi)	Orifice Diameter	Weight kg (lb)	Body Material
SV-401	\$460	½	4.3	0 to 140	½"	1.0 (2.2)	Brass
SV-402	470	¾	5.8	0 to 140	¾"	1.4 (3.1)	Brass
SV-403	875	1	11.7	0 to 140	1"	1.9 (4.2)	Brass
SV-405*	850	1½	19.0	0 to 140	1½"	3.6 (8.0)	Brass
SV-406*	1100	2	42.0	0 to 140	2"	7.8 (17.2)	Brass

¹ Also suitable for vacuum down to 38 Torr.

* Only the SV-401, SV-402 and SV-403 are UL listed.

Comes complete with operator's manual.

Ordering Examples: SV-403, 1 NPT brass valve, for 1" orifice, \$875.

SV-406, 2 NPT brass valve, for 2" orifice, \$1100.



SV-403, \$875, shown actual size.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters