

1/8 DIN BATCH CONTROLLER

for Amplified Frequency Inputs

DPF11
Starts at
\$370



- ✓ 5-Digit Scaling Factor
- ✓ Display Rate, Batch Size and Batch/Total or Grand Total
- ✓ Second B Relay Programmable for Output at Prewarn or Selected Batch/Grand Total
- ✓ Security Lockout
- ✓ NEMA 4X (IP65) Front
- ✓ Optional RS422 or RS232
- ✓ Analog Output Available

The DPF11 miniature batcher is ideal for all batching applications. The display will show batch amount, rate and batch/grand total at the push of a button. The start and stop buttons make batching simple.

The DPF11 is a 6-digit totalizer and 4.5 digit ratemeter with two relay outputs. One output is dedicated to the batch amount (preset A), the other can be activated for prewarn or batch/grand total. The unit can count up to the preset (reset to 0) or down from the preset (set to preset). start, stop and reset functions can be activated from the front panel or remote inputs.

An analog output (assignable for rate or batch amount) is optional for data logging.

Up to 99 units can communicate to a host computer on a single RS232 or RS422 loop.

SPECIFICATIONS

Accuracy: 0.01% FS (± 1 display digit)

Display: 6-digit, 13.97 mm (0.55") high LED (± 1 display digit)

Input Power: 110 Vac $\pm 15\%$, 220 Vac $\pm 15\%$, 24 Vac $\pm 15\%$

Current: 250 mA dc max or 6.5 VA AC

Output Power: (AC powered units only) 12 Vdc @ 50 mA, unregulated -10 +50%

Temperature:

Operating: 0 to 54°C (32 to 130°F)

Storage: -40 to 93°C (-40 to 200°F)

Humidity: 0 to 90% RH, non-condensing



DPF11 1/8 DIN, \$370, shown actual size.

Memory: EEPROM stores data for 10 years if power is lost

Approvals: CE approved

Pulse Input:

Low: 0 to 1 Vdc

High: 4 to 30 Vdc 10 k Ω impedance, up to 10 kHz; min 0.05 Hz for rate indication

Mag. Input:

30 mV input, (50V max) signals 10 k Ω imp. 5 kHz max

Output Relays: (2) rated 5 A, 120/240 Vac or 28 Vdc (NC relay contacts and NPN transistor output available with solder jumpers)

Panel Cutout:

92 W x 45 H x 108 mm D (3.622 x 1.772 x 4.245")

Dimensions: 113 W x 67 H x 126 mm D (4.44 x 2.63 x 4.95")

Shipping Weight:

9 kg (2 lb)



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
DPF11	\$370	4/30 V pulse input (FLSC-AMP-A may be needed)
DPF12	425	Low level MAG. input (No FLSC-AMP-A required)

Options

Ordering Suffix	Add'l Cost	Description
-A	\$135	Analog output, 0 or 4 to 20 mA proportional to rate/total*
-220VAC	N/C	220 Vac power
-24VAC	N/C	24 Vac power
-RS232	130	RS232 communications*
-RS422	130	RS422 communications*

* "-A", "RS232" and "RS422" options are mutually exclusive. Only one may be ordered with a unit.

Accessories

Model No.	Price	Description
DPP-5	\$525	1/8 DIN panel punch
FLSC-AMP-A	70	Amplifies low-level turbine and paddlewheel sensors

Comes complete with operator's manual.

Ordering Examples: DPF11-RS232 is a ratemeter/batch controller with RS232 output, \$370 + 130 = \$500. OCW-3 OMEGACARESM extends standard 2-year warranty to a total of 5 years (\$93), \$370 + 93 = \$463.

DPF12-A, ratemeter/batcher with 4 to 20 mA output, \$425 + 135 = \$560.

Recommended Reference Book: Flow Measurement, GE-1400, \$110. Visit omega.com/bobi for Additional Books





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters