



Water Analysis Portable Turbidity Meters

- ✓ EPA Compliant
- ✓ For Field and Lab Use
- ✓ For Range 0 to 4000 NTU
- ✓ RS-232 Interface
- ✓ Very Economical
- ✓ Micro-Processor Based
- ✓ User-Friendly Calibration and Operation

The TRB-2020 combines laboratory accuracy and reliability in an extremely compact, portable instrument for turbidity measurement over the wide range of 0 to 4000 NTUs.

A multi-detector optical configuration assures long term stability and minimizes stray light and color interference. All readings are determined by the process of signal-averaging over a 5-second period minimizing fluctuations in readings attributable to large particles and enabling rapid, highly repeatable measurements.

Supplied with a 9 volt alkaline battery, the TRB-2020 is an ideal choice for regulatory monitoring, process water testing, and environmental water analysis in the field or laboratory.

This nephelometric turbidity instrument meets or exceeds EPA design specifications for NPDWR and NPDES turbidity monitoring programs as specified by USEPA method 180.1. There is also an EPA compliance reading mode which rounds the readings to meet EPA reporting requirements.

Range: 0 to 4000 NTUs. The microprocessor enables auto-ranging over the full range of 0 to 4000 nephelometric turbidity units (NTUs) and provides direct digital readout with a resolution of 0.01 for the lowest range and an accuracy of $\pm 2\%$.

The simple calibration procedure involves activating the UP or DOWN arrow keys until the reading matches the standard. The microprocessor adjusts the factory-programmed calibration curve accordingly. Two primary turbidity standards are provided.

An RS-232 port is provided to interface with a datalogger or computer.

Attractively priced, the TRB-2020 portable turbidity meter comes with 0, 1, and 10 NTU standards, sample bottles, 4 sample vials, extra battery, and illustrated instruction manual, all in a sturdy carrying case.

TRB-2020-E
\$900
Basic Unit



TRB-2020-E,
\$900.



TRB-2020-E, \$900,
shown smaller
than actual size.

Specifications

Instrument Type: Nephelometric turbidity; in NTU, FNU, FAU, ASBC or EBC

Range: 0 to 4000 (Auroranging) NTU

Resolution: 0.01 NTU/FNU 0.00 to 10.99, 0.1 NTU/FNU 11.00 to 109.9, 1 NTU/FNU 110 to 4000

Response Time: <5 seconds

Repeatability: 0.02 NTU/FNU, 0.5 FAU

Reading Stability:

Within 1% of final value

Accuracy: 0.05 NTU or $\pm 2\%$ of reading

Datalogging: Up to 4000 points

Display: 3½-digit LCD, Battery and Lamp status (EPA), LED (ISO)

Light Source: Tungsten filament lamp

Languages: English, French, Spanish, Japanese, Italian, and Portuguese

Serial Interface: RS-232

Power: 9V battery (included), or 120V/60 Hz or 220V/50Hz, 100 mA, with optional adaptor

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
TRB-2020-E	\$900	Portable turbidity meter kit with USEPA 180.1 standard

Kit comes complete with rugged, waterproof carrying case, 0, 1, and 10 NTU standards, sample bottle, 4 sample tubes, and extra battery.

Accessories

Model No.	Price	Description
SC-1912-CD-01	\$186	CD RS232 software and cable
TRB-1754	45	AC adapter (variable 100 to 204 Vac)
TRB-0641	12	2-Pack vial ring
TRB-0475	27	6-Pack of vials
TRB-1480	28	0 NTU standard (ISO and EPA) 60 ml
TRB-1481	44	1 NTU standard (ISO) 60 ml
TRB-1482	44	10 NTU standard (ISO) 60 ml
TRB-1483	44	100 NTU standard (ISO) 60 ml
TRB-1484	44	1 NTU standard (EPA) 60 ml
TRB-1485	44	10 NTU standard (EPA) 60 ml
TRB-1486	44	100 NTU standard (EPA) 60 ml

Ordering Example: TRB-2020-E, portable turbidity meter kit for USEPA and SC-1912-CD-01, CD RS232 software and cable, \$900 + 186 = \$1086.

Recommended Reference Book: Hands On Water and Wastewater Equipment Maintenance, ES-2208, \$125. See Section Y for Additional Books.





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters