

SOLENOID VALVE TIMERS

For DIN 43650A Connectors

FSV-AT2000

\$69



- ✓ Analog Version for Economy
- ✓ Valve Test Function on Both Models

These full featured, high quality electronic timers are designed to control solenoid valves. They are ideal for: autodrain valves, sampling valves, lubrication systems and air dryers. They mount directly on solenoid valves with DIN 43650A Form A connectors. Model has LED indicator to indicate valve status.

FSV-AT2000, \$69, shown much larger than actual size.

SPECIFICATIONS

Supply Voltage:
24 to 240 Vac/dc (50 to 60 Hz)

Current Consumption: 4 mA max

Operating Temperature: -20 to 52°C (-4 to 125°F)

Environmental Protection:
NEMA 4 (IP65)

Switch Holding Voltage: 400V

Inrush Current: 10 Amps for 10 mSec

Duty Cycle: 100%


Switch Life: 300 million operations

Manual Override: Test

Repeat Accuracy: ±1%

Timing Temp. Coefficient: ±0.005%/°C

Time:
ON Time: 0.5 to 10 sec
OFF Time: 30 sec to 45 min



Dimensions: mm (in)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
FSV-AT2000	\$69	Analog timer

Accessories

Model No.	Price	Description
FSV-CABLE	\$18	1.8 m (6') grounded 115 Vac cable with DIN 43650A connector, UL approved
FW-331	155	Reference Book: Analytical Instrumentation

Comes complete with operator's manual.

Compatible with FSV30 Series valves on page J-22.

Ordering Example: FSV-AT2000, analog timer, with FSV-CABLE, 1.8 m (6') grounded cable, \$69 + 18 = \$87.





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters