

ULTRASONIC NON-CONTACT LEVEL TRANSMITTER

For 0.3 to 18.3 m (1 to 60')

LVU41
Starts at

\$1150



- ✓ RS232 or RS485 Communications Available
- ✓ Programmable
- ✓ Pushbutton Calibration
- ✓ Elimination of Unwanted Echoes
- ✓ Temperature Compensated
- ✓ Field/Bench Calibration
- ✓ Self-Cleaning Sensor Face
- ✓ Non-Volatile Memory (Batteries Not Required)

The LVU40 Series consists of advanced ultrasonic level measurement sensors for liquids. These products continue to prove useful in demanding applications.

The microprocessor-based circuits provide a temperature-compensated signal for improved accuracy. All models have the ability to filter false echoes produced by peripheral obstructions.

These transmitters can perform continuous level measurement in a range of 0.3 to 18.3 m (1.0 to 60'), with several power and programmability options. Point level can also be obtained by using a PLC (programmable logic controller) or one of OMEGA's CNI Series process controllers.

SPECIFICATIONS

Accuracy: ±0.25% of max range (in air)
Range: 0.3 to 18.3 m (1 to 60')
Resolution: 6.9 mm (0.270")
Frequency: 45 kHz
Dead Zone Range: 0.3 m (1')
Operating Temperature Range: -40 to 60°C (-40 to 140°F)
Pressure: 1 bar (15 psig max)
Mounting: 3 NPT
Beam Angle: 6 to 12° at -3 dB (model dependent)
Loss of Echo Hold: 30 seconds, 22 mA output

CNI833, \$310, shown smaller than actual size (see page M-41).



Power Options:

AC: 115 Vac, 60 Hz or 230 Vac, 50 Hz (±20%) 1.7 VA
DC: 12 to 30 Vdc @ 0.07 A, @ 24 Vdc R load = $(V_s - 6)/24$ mA
Output: 4 to 20 mA or 20 to 4 mA, 6.1 µA resolution; 750 Ω (isolated on 4-wire models only)
Optional: RS232 or RS485 communications port
Fuse: 0.125 A/250 V type



LVU41-RS232, \$1150, shown smaller than actual size.

Temperature Compensation:

Onboard the sensor

Calibration: Pushbutton or optional programmable

Diagnostics (Echo Profile): Via optional programmable port

Approval: Entela, CE

Conduit Entry: ½ NPT hole (PVC only)

Enclosure: Aluminum with PVC antenna ingress protection [NEMA 4X (IP66)]

Housing Dimensions: 101.6 x 226.1 mm (4 x 8.9")

Sensor Diameter: 76.2 mm (3")

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Description
LVU41-RS232	\$1150	3-wire 12 to 30 Vdc ultrasonic level transmitter with RS232 communications and Windows software
LVU41-RS485	1150	3-wire 12 to 30 Vdc ultrasonic level transmitter with RS485 communications and Windows software
LVU42-RS232	1200	4-wire 115 Vac ultrasonic level transmitter with RS232 communications and Windows software
LVU42-RS485	1400	4-wire 115 Vac ultrasonic level transmitter with RS485 communications and Windows software

Accessories

Model No.	Price	Description
CNI3233	\$195	½ DIN controller with relays, see page M-41 for details
DPI32	150	½ DIN panel meter, see page M-37 for details
PSR-24S	60	Regulated power supply, 90 to 264 Vac input, 24 Vdc output, 400 mA, screw terminals, UL
PSR-24L	60	Regulated power supply, 90 to 264 Vac input, 24 Vdc output, 400 mA, stripped leads, UL
PSR-24L-230	60	Regulated power supply, 230 Vac input, 24 Vdc output, 400 mA, stripped leads, CE

Comes complete with software and operator's manual.

Ordering Examples: LVU42-RS485, 4-wire ultrasonic transmitter with RS485, \$1400.
 LVU41-RS232, 3-wire ultrasonic level transmitter with RS232, \$1150.

Recommended Reference Book: The Consumer Guide to Non-Contact Level Gauges, **FW-205, \$250**. See Section Y for Additional Books.





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters