

OMEGA-FLO® 2-WAY ZERO DIFFERENTIAL SOLENOID VALVES

1/2 TO 2 1/2 NPT

SV-350 Series Starts at

\$180



- ✓ Zero Differential Pressure
Ideal for Gravity Feed Processes
- ✓ Available in Brass or Stainless Steel
- ✓ Process Temperature Range to 130°C (266°F)
- ✓ Normally Closed

SV-350 Series 2-way solenoid valves are internally piloted, with a diaphragm and forced lifting that open fully from 0 psi pressure differential. Their brass or stainless steel bodies and FKM seal material allow for high flow rates. A temperature range of -10 to 130°C (14 to 266°F) makes these valves ideal for neutral media such as water, compressed air, and hydraulic oil (viscosity of approximately 2.3×10^{-4} ft²/s). Electrical connection is by conduit plug.

SPECIFICATIONS

Mounting Position: Any (preferably with solenoid system upright)

Max Ambient Temp: 54°C (130°F)

Operating Voltage: 120 Vac

Voltage Tolerance: ±10%

Power Consumption in Warm State:

Opening Time (ms): 100 to 1000

Closing Time (ms): 700 to 4000 (switching times are measured using water and are dependent on valve orifice size and fluid pressure and viscosity)

Cycling Rate: Approx. 10 to 20 cpm

Duty Cycle: Continuous (100%)



SV-355, \$395, shown smaller than actual size.

Orifice Size	Inrush	Hold
7/16"	80 W	6 W
3/4 to 1 1/2"	100 W	9 W
2 to 2 1/2"	28 W	28 W

Normally Closed Valve

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model No.	Price	Port Connection (NPT)	C _v	Range (psi) ¹	Orifice Diameter	Body Material
SV-351	\$180	1/2	3.3	0 to 230	7/16"	BR
SV-352	485	1/2	3.3	0 to 230	7/16"	SS
SV-353	320	3/4	5.8	0 to 230	3/4"	BR
SV-355	395	1	11.7	0 to 230	1"	BR
SV-356	875	1	11.7	0 to 230	1"	SS
SV-359*	800	2	44	0 to 170	2"	BR

¹ Also suitable for vacuum down to 38 Torr.

* The SV-359 is not UL listed.

Comes complete with operator's manual.

Ordering Examples: SV-351, 1/2 NPT brass valve, \$180.

SV-353 3/4 NPT brass valve, \$320.

Recommended Reference Book: Valve Handbook, FW-306, \$135. See Section Y For Additional Books





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters