

FAN HEATER



CR27 Series
Starts at
\$166



- ✓ Compact Fan Heater in PTC Technology
- ✓ Heating Power Adjusts to Ambient Temperature
- ✓ Integrated Adjustable Thermostat and Control Light
- ✓ DIN Rail Mountable

An easy DIN rail mountable design makes the CR27 Series fan heater an ideal accessory for any enclosure. The CR27 maintains minimum operating temperatures in enclosures and helps to prevent failure of electronic components caused by condensation and corrosion.

To determine the required heater size follow this equation:

$$PH = (A \times \Delta T \times k) - P_v$$

PH = Required heating power for your application in Watts (W)

P_v = Heating power generated by existing components (e.g. a transformer) in Watts (W)

A = Exposed enclosure surface area square meters (m²)

ΔT = Temperature differential between the desired minimum interior temperature and lowest possible external temperature of the enclosure in Kelvin (K), 1.8°F = 1°C = 1K

k = Heat transmission coefficient of the enclosure material used:

- Stainless Steel: 3.7 W/m²K
- Painted Steel: 5.5 W/m²K
- Aluminum: 12 W/m²K
- Polyester/Plastic: 3.5 W/m²K

For outdoor applications it is recommended to double the heating power.

Specifications

Heating Element: PTC-semiconductor/resistor, self-regulating with changing ambient temperature (see graph)

Thermostat Range: 0 to 60°C (32 to 140°F)

Overheat Protection: Built-in temperature limit in case of fan failure

Function Control Light: LED

Housing: Plastic, UL94V-0

Dimensions:
165 H x 100 W x 128 mm D
(6.5 x 3.94 x 5")

Connection: 2-pole terminal, 2.5 mm² (AWG 14 max)

Mounting: Clip for 35 mm DIN rail (EN 50022)

Protection Class: II (double insulated)

Protection Type: NEMA 2 (IP20)

Axial Fan (Ball Bearing):

CR2700900,
CR2700901: 35 m³/h (20 cfm)

CR2701900,
CR2701901: 45 m³/h (26 cfm)

Max Current (Inrush):



CR2700900,
CR2700901: 14 A
CR2701900,
CR2701901: 15 A

Weight:

CR2700900,
CR2700901: 0.9 kg (2 lb),
CR2701900,
CR2701901: 1.1 kg (2.4 lb)



CR2701900, \$186, shown smaller than actual size.



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Description
CR2700900	\$166	Fan heater, 550 W, 120 Vac, with adjustable thermostat 32 to 140°F
CR2700901	166	Fan heater, 550 W, 120 Vac, with adjustable thermostat 0 to 60°C
CR2701900	186	Fan heater, 650 W, 120 Vac, with adjustable thermostat 32 to 140°F
CR2701901	186	Fan heater, 650 W, 120 Vac, with adjustable thermostat 0 to 60°C
XBANS3575P	9	DIN rail 35 x 7.5 mm x 2 m (1.4 x 0.30" x 6') slotted

Comes complete with operator's manual.

Ordering Examples: CR2700900, fan heater, 550 W, 120 Vac, with adjustable thermostat 32 to 140°F, \$166.

CR2701901, fan heater, 650 W, 120V, with adjustable thermostat, 0 to 60°C, \$186.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters