

ULTRASONIC DOPPLER FLOWMETERS

Flow Reference Section

INTRODUCTION

The Ultrasonic doppler flowmeter incorporates a technology offering an increased range of applications. Because of its non-invasive nature, no pressure drop is created, and this type of flowmeter can be used to measure the flow of fluids and slurries which ordinarily cause damage to conventional sensors.

The basic principle of operation employs the frequency shift (Doppler Effect) of an ultrasonic signal when it is reflected by suspended particles or gas bubbles (discontinuities) in motion. This metering technique utilizes the physical phenomenon of a sound wave that changes frequency when it is reflected by moving discontinuities in a flowing liquid. Ultrasonic sound is transmitted into a pipe with flowing liquids, and the discontinuities reflect the ultrasonic wave with a slightly different frequency that is directly proportional to the rate of flow of the liquid (Figure 1). Current technology requires that the liquid contain at least 100 parts per million (PPM) of 100 micron or larger suspended particles or bubbles.

A typical system incorporates a transmitter/indicator/totalizer and a transducer. The transducer is mounted on the exterior of the pipe. It is driven by a high frequency oscillator in the transmitter through an interconnecting cable. The transducer generates an ultrasonic signal which it transmits through the wall of the pipe into the flowing liquid. The transmitter measures the difference between its output and input frequencies and converts this difference into electronic

pulses which are processed to provide an analog indication and a voltage or current output signal. Additionally, the pulses are scaled and totaled to provide flow quantity.

The transmitter frequency power levels and transducer configuration are selected to accommodate a wide variety of liquids, pipe sizes, percentage of solids, and pipe liners.

The transmitter also incorporates circuitry which allows adjustment of the signal threshold, permitting elimination of undesirable ambient noises (both mechanical and electrical). As a result, instrumentation is possible in a variety of locations subject to high levels of sonic, mechanical, and electrical noise.

ACCURACY

Without Field Calibration

The accuracy of a flowmeter operating on the Doppler principle is mainly a characteristic of flow velocity profile integration by the ultrasonic wave. The ability to do this is basically a function of: percentage of sound reflectors (solids and bubbles), their size, variation and distribution, the line size, and the flowmeter's design features. Therefore, it is unrealistic to state a general accuracy without knowing the full application details and the transducer selection.

With Field Calibration

The accuracy of this method with a field flow calibration can be as high as $\pm 1\%$ plus the accuracy of the flow calibration on the actual application at given conditions.

Clean Liquids

As noted, the basic ultrasonic Doppler flowmeter requires that the liquid to be measured contain a minimum of at least 100 PPM of suspended solids or bubbles at least 100 microns or larger in size. The transducer frequency for these requirements is 1 megahertz. Lower frequencies require more PPM and a larger micron size. Until recently, 100 PPM of suspended solids or bubbles of at least 100 microns or larger, constituted the cleanest measurable application. The solution for clean liquid applications is the FDT family of Transit Time Ultrasonic flow meters FDT-30, FDT-80 and FDT100 products. In these designs, the time of flight of the ultrasonic signal is measured between two transducers—one upstream and one downstream. The difference in elapsed time going with or against the flow determines the fluid velocity. Transit time flow meters feature the world's most advanced non-invasive flow measurement technology—providing a measuring system with unsurpassed accuracy, versatility, ease of installation and dependability. Designed primarily for clean liquids, the flow meter operates reliably with small amounts of suspended solids or aeration. Transit time flow meters are designed for long- or short-term measurement flow surveys on full-pipe liquid systems and are ideal for verifying calibration of permanently mounted flow meters of all types.

When the flow is zero, the time for the signal T1 to get to T2 is the same as that required to get from T2 to T1. When there is flow, the effect is to boost the speed of the signal in the downstream direction, while decreasing it in the upstream direction. The flowing velocity (V_f) can be determined by the following equation:

$$V_f = Kdt/T_L$$

where K is a calibration factor for the volume and time units used, dt is the time differential between upstream and downstream transit times, and T_L is the zero-flow transit time.

Transit Time Ultrasonic flow meters are specifically designed to work in clean and ultra-clean liquid applications. Bridging the gap is the FD-7000 enhanced ultrasonic flow meter. Examples of liquids that fall into the gap between Doppler and Transit Time technologies include: ground water, gray water, carbonated beverages, waste or return activated sludge, mining slurries and filter backwash.




Figure 1: The Ultrasonic Doppler Flow Sensor



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters