


CERAMIC HEATER PLATES

CRHF Series
With Flange
Starts at
\$370



- ✓ 980°C (1800°F) Operating Temperature for Imbedded Heating Element Construction
- ✓ 980°C (1800°F) Operating Temperature for Exposed Element Construction
- ✓ Imbedded Heating Elements Standard
- ✓ Optional Exposed Heating Elements

Imbedded heating elements standard, exposed optional, no additional cost.

CRHF-18650/230, \$555, shown smaller than actual size.

With Flanges

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model Number	Wattage	Dimensions: mm (in)				Voltage	Price	Weight kg (lb)
		A	B	C	D			
CRHF-18650/230	2700	457 (18)	168 (6 $\frac{5}{8}$)	38 (1 $\frac{1}{2}$)	244 (9 $\frac{5}{8}$)	230	\$555	9.8 (21.6)
CRHF-21650/230	3150	533 (21)	168 (6 $\frac{5}{8}$)	38 (1 $\frac{1}{2}$)	244 (9 $\frac{5}{8}$)	230	370	11.4 (25.2)
CRHF-24650/230	3600	610 (24)	168 (6 $\frac{5}{8}$)	38 (1 $\frac{1}{2}$)	244 (9 $\frac{5}{8}$)	230	750	13.1 (28.8)
CRHF-121250/230	3600	305 (12)	321 (12 $\frac{5}{8}$)	38 (1 $\frac{1}{2}$)	397 (15 $\frac{5}{8}$)	230	600	10.6 (23.4)
CRHF-151250/230	4500	381 (15)	321 (12 $\frac{5}{8}$)	38 (1 $\frac{1}{2}$)	397 (15 $\frac{5}{8}$)	230	750	13.3 (29.3)
CRHF-181250/230	5400	457 (18)	321 (12 $\frac{5}{8}$)	38 (1 $\frac{1}{2}$)	397 (15 $\frac{5}{8}$)	230	900	15.9 (35.1)
CRHF-211250/230	6300	533 (21)	321 (12 $\frac{5}{8}$)	38 (1 $\frac{1}{2}$)	397 (15 $\frac{5}{8}$)	230	1050	18.6 (41)
CRHF-241250/230	7200	610 (24)	321 (12 $\frac{5}{8}$)	38 (1 $\frac{1}{2}$)	397 (15 $\frac{5}{8}$)	230*	1200	21.2 (46.8)
CRHF-181850/230	7100	457 (18)	473 (18 $\frac{5}{8}$)	51 (2)	549 (21 $\frac{5}{8}$)	230*	1240	28.2 (62.1)
CRHF-211850/230	9450	533 (21)	473 (18 $\frac{5}{8}$)	51 (2)	549 (21 $\frac{5}{8}$)	230*	1450	32.8 (72.4)
CRHF-241850/460	10800	610 (24)	473 (18 $\frac{5}{8}$)	51 (2)	549 (21 $\frac{5}{8}$)	460	1655	37.6 (82.8)
CRHF-242450/460	14400	610 (24)	625 (24 $\frac{5}{8}$)	51 (2)	702 (27 $\frac{5}{8}$)	460†	2105	48 (105.8)

Comes with complete operator's manual.

* These heaters contain two 230V circuits which may be wired in parallel for 230V operation or in series for 460V operation.

** Add suffix "-E" for exposed element construction, same price.

† Indicates heater containing two 460V circuits.

Ordering Examples: CRHF-21650/230, flanged ceramic heater plate, 3150 Watts, 230 Vac, \$370.

CRHF-21650/230-E, flanged ceramic heater plate, 3150 Watts, 230 Vac, \$370.

CRHP Series
Without Flange
Starts at

\$260



Heating Surfaces up to 24 x 24 inches.
Optional Exposed Construction Shown**

OMEGALUX® ceramic heater plates provide surface temperatures of up to 980°C (1800°F). The large, 16 mm (5/8") ID grooves permit the use of exceptionally heavy gauge heating wire for low element watt densities and high wattage per square inch of radiating surface. The elements can be imbedded in ceramic, or exposed, depending on requirements.

Special sizes, shapes, wattages, voltages, thermocouple access holes and extra long braided leads are available. Contact OMEGALUX Sales department for ordering information.

For Sales and Service in the U.S. and Canada:

1-800-872-4328®
1-800-USA-HEAT

Without Flanges

MOST POPULAR MODELS HIGHLIGHTED

To Order (Specify Model Number)

Model Number	Wattage	Dimensions: mm (in)			Voltage	Price	Wt. lb (kg)
		A	B	C			
CRHP-12650/230	1800	305 (12)	168 (6 $\frac{5}{8}$)	38 (1 $\frac{1}{2}$)	230	\$260	4.5 (9.9)
CRHP-15650/230	2250	381 (15)	168 (6 $\frac{5}{8}$)	38 (1 $\frac{1}{2}$)	230	320	5.6 (12.4)
CRHP-18650/230	2700	457 (18)	68 (6 $\frac{5}{8}$)	38 (1 $\frac{1}{2}$)	230	380	6.8 (14.9)
CRHP-21650/230	3150	533 (21)	68 (6 $\frac{5}{8}$)	38 (1 $\frac{1}{2}$)	230	440	7.9 (17.5)
CRHP-24650/230	3600	610 (24)	68 (6 $\frac{5}{8}$)	38 (1 $\frac{1}{2}$)	230	510	9 (19.8)
CRHP-121250/230	3600	305 (12)	321 (12 $\frac{5}{8}$)	38 (1 $\frac{1}{2}$)	230	485	8.6 (18.9)
CRHP-151250/230	4500	381 (15)	321 (12 $\frac{5}{8}$)	38 (1 $\frac{1}{2}$)	230	605	10.8 (23.8)
CRHP-181250/230	5400	457 (18)	321 (12 $\frac{5}{8}$)	38 (1 $\frac{1}{2}$)	230	730	12.8 (28.4)
CRHP-211250/230	4500	533 (21)	321 (12 $\frac{5}{8}$)	38 (1 $\frac{1}{2}$)	230	850	15 (33.1)
CRHP-241250/230	7200	610 (24)	321 (12 $\frac{5}{8}$)	38 (1 $\frac{1}{2}$)	230*	970	17.1 (37.8)
CRHP-181850/230	7100	457 (18)	473 (18 $\frac{5}{8}$)	51 (2)	230*	1070	24.3 (53.6)
CRHP-211850/230	9450	533 (21)	473 (18 $\frac{5}{8}$)	51 (2)	230*	1250	28.4 (62.6)
CRHP-241850/460	10800	610 (24)	473 (18 $\frac{5}{8}$)	51 (2)	460	1430	32.3 (71.3)
CRHP-242450/460	14400	610 (24)	625 (24 $\frac{5}{8}$)	51 (2)	460†	2105	42.8 (94.3)

Includes complete operator's manual.

*These heaters contain two 230V circuits which may be wired in parallel for 230V operation or in series for 460V operation.

**Add suffix "-E" for exposed element construction, same price.

†Indicates heater containing two 460V circuits.

Ordering Example: **CRHP-21650/230**, ceramic heater plate, 3150 Watts, 230 Vac, \$440.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters