

HEAT CABLE ACCESSORIES

Splice and Tee Box

RTST
Starts at
\$97



The RTST splice and tee box is a NEMA 4X (IP66) rated junction box designed to make straight or tee connections for all OMEGALUX® heating cables. This model provides waterproof cable entry (for two cables for a splice or three cables for a tee), enclosure support, terminal block, and a waterproof, corrosion-resistant wiring enclosure. A pipe strap (PS series) is required to attach this model to a pipe. To order, see page 51.


Splice and tee kit includes:

- 1 molded junction box consisting of:
 - 1 base • 1 box • 1 lid
 - 1 three-position terminal block
 - 1 mounting screw for terminal block
 - 3 GRSR self-regulating cable sealing grommets
 - 3 GRCW constant wattage cable sealing grommets



CAUTION AND WARNING!

Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel.



RTST, \$97, splice and tee box and accessories, shown smaller than actual size.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model No.	Price	Description
RTST	\$97	Splice and tee box
RTST-SL1	165	Splice and tee box with signal light, 120V
RTST-SL2	165	Splice and tee box with signal light, 208 to 240V
RTST-SL3	165	Splice and tee box with signal light, 277V

Ordering Example: RTST, splice and tee box for heating cable, \$97.

Power Connection Box

RTPC
Starts at
\$97



The RTPC power connection box is a NEMA 4X (IP66) rated junction box designed to connect all OMEGALUX® heating cables to customer-supplied power wiring. This kit provides waterproof cable entry for up to three cables, enclosure support, terminal block, and a waterproof, corrosion-resistant wiring enclosure with a 3/4" opening to accept a conduit hub (model CCH-2). A pipe strap (PS series) is required to attach this model to a pipe. To order model CCH conduit fitting and PS series pipe strap, see page 51.

Power connection kit includes:

- 1 molded junction box consisting of:
 - 1 base
 - 1 box (with conduit opening)
 - 1 lid
 - 1 three-position terminal block
 - 1 mounting screw for terminal block
 - 1 GRSR self-regulating cable sealing grommet
 - 1 GRCW constant wattage cable sealing grommet



RTPC, \$97, power connection box and accessories, shown smaller than actual size.

To Order (Specify Model Number)


Model No.	Price	Description
RTPC	\$97	Power connection box
RTPC-SL1	165	Power connection box with signal light, 120V
RTPC-SL2	165	Power connection box with signal light, 208 to 240V
RTPC-SL3	165	Power connection box with signal light, 277V

Ordering Example: RTPC, power connection box for heating cable, \$97.

HEAT CABLE CONNECTION ACCESSORIES




Technician installing RTST splice and tee box.



OMEGALUX® heat cable shown installed on piping and valves. Heating cable is held in place by FT-2 fiberglass tape.



The appropriate grommet must be ordered separately to provide a watertight seal to the accessory.



Mounting plate kit attachments (MP-1) for installing RTPC and RTST kits on flat surfaces. Kit includes: 1 mounting plate, 1 lock washer, 1 bolt, 1 washer and 1 nut.

Accessories

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
GRS	\$5	Capillary/RTD grommet
GRO	5	Blank grommet
GRCW	5	Constant wattage grommet
GRSR	5	Self-regulating grommet
PS-1	4	Metal pipe strap for ½ to ¾" pipe size
PS-3	4	Metal pipe strap for 1 to 3½" pipe size
PS-10	6	Metal pipe strap for 2½ to 9" pipe size (for use with RTPC and RTST kits)
CCH-2	23	Corrosion-resistant conduit hub (fits ¾" conduit). Fits opening in model RTPC; has ground connector
MP-1	15	Mounting plate and hardware for installing RTPC and RTST kits on flat surfaces (all parts are stainless steel)
AT-1	49	Aluminum tape; to aid heat transfer on plastic pipes; apply over cable along entire length of circuit; 1 roll of aluminum foil installation tape with pressure-sensitive acrylic adhesive, 2 mm thickness with high tensile strength; tape is 2½" wide x 180' long and has a 93°C (200°F) rating, minimum application temperature is 5°C (40°F)
FT-3	14	Fiberglass tape ¾" wide

Ordering Example: PS-1, metal pipe strap for ½ to ¾" pipes, \$4.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters