



ELECTRIC STUD HEATERS

CBH Series
Starts at
\$1000



CBH-1815/120, \$1000, shown smaller than actual size.

- ✓ Reliable, Premium Quality
- ✓ Steel Sheath
- ✓ 1150 to 8000 W
- ✓ 120, 240 Vac
- ✓ 18" (46 cm), to 60" (152 cm) Lengths



CBH Series heaters are constructed of rugged metal sheathed tubular elements homogeneously combined with a metal sleeve that has been accurately dimensioned to provide a proper clearance and ease of inserting into standard drill hole sizes so large bolts or studs may be rapidly expanded and tightened with a wrench, providing "shrink fit tightness" when cool

Useful in assembly of large compressors, presses, turbines, die blocks, cylinders, engine heads, pressure vessels, etc. Quick heat-up is important to avoid heat drain-away of surrounding metal. CBH heaters are generally used in sets to permit uniform tightening of mating parts.

SPECIFICATIONS

Sheath Material: Steel

Max Sheath Temperature: 1600°F

Power: 120 or 240 Vac

Terminal: Standard octagon box with handle

CAUTION AND WARNING!
Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel. See inside back cover for additional warning.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)									
Watts	Dimensions: Inches (cm)						Model No.	Price	Weight lb (kg)
	A Lgth.	B Htd. Lgth.	C Htd. Dia.	D Cold End	E Cold End	Max. Stud Hole Dia. †			
1150	18 (46)	12 (30)	.553 (1.4)	1 1/8 (3)	6 7/8 (17)	.616 (1.6)	CBH-1815/120	\$1000	5 (2)
1500	24 (61)	18 (46)	.553 (1.4)	1 1/8 (3)	6 7/8 (17)	.616 (1.6)	CBH-2415/120	1100	5 (2)
2250	30 (76)	24 (61)	.553 (1.4)	1 1/8 (3)	6 7/8 (17)	.616 (1.6)	CBH-3025/*	1150	5 (2)
2600	36 (91)	30 (76)	.553 (1.4)	1 1/8 (3)	6 7/8 (17)	.616 (1.6)	CBH-3625/*	1150	5 (2)
1200	18 (46)	12 (30)	.660 (1.7)	1 1/8 (3)	6 7/8 (17)	.735 (1.9)	CBH-1816/120	1100	6 (3)
1700	24 (61)	18 (46)	.660 (1.7)	1 1/8 (3)	6 7/8 (17)	.735 (1.9)	CBH-2416/120	1100	6 (3)
2300	30 (76)	24 (61)	.660 (1.7)	1 1/8 (3)	6 7/8 (17)	.735 (1.9)	CBH-3026/120	1200	6 (3)
2800	36 (91)	30 (76)	.660 (1.7)	1 1/8 (3)	6 7/8 (17)	.735 (1.9)	CBH-3626/120	1250	6 (3)
1700	18 (46)	12 (30)	.730 (1.9)	1 1/4 (3)	6 3/4 (17)	.860 (2.2)	CBH-1827/120	1200	5 (2)
2500	24 (61)	18 (46)	.730 (1.9)	1 1/4 (3)	6 3/4 (17)	.860 (2.2)	CBH-2427/120	1250	5 (2)
4200	36 (91)	30 (76)	.730 (1.9)	1 1/4 (3)	6 3/4 (17)	.860 (2.2)	CBH-3647/120	1350	6 (3)
6000	48 (122)	42 (107)	.730 (1.9)	1 1/4 (3)	6 3/4 (17)	.860 (2.2)	CBH-4867/**	1500	6 (3)
7500	60 (152)	54 (137)	.730 (1.9)	1 1/4 (3)	6 3/4 (17)	.860 (2.2)	CBH-6177/240	1650	7 (3)
2700	24 (61)	18 (46)	.855 (2.2)	1 1/4 (3)	6 3/4 (17)	.985 (2.5)	CBH-2438/240	1300	7 (3)
3600	30 (76)	24 (61)	.855 (2.2)	1 1/4 (3)	6 3/4 (17)	.985 (2.5)	CBH-3048/120	1400	8 (4)
5300	42 (107)	36 (91)	.855 (2.2)	1 1/4 (3)	6 3/4 (17)	.985 (2.5)	CBH-4258/**	1500	8 (4)
6500	48 (122)	42 (107)	.855 (2.2)	1 1/4 (3)	6 3/4 (17)	.985 (2.5)	CBH-4868/240	1550	9 (4)
6000	42 (107)	36 (91)	.980 (2.5)	1 1/4 (3)	6 3/4 (17)	1.110 (2.8)	CBH-4269/**	1900	9 (4)
8000	54 (137)	48 (122)	.980 (2.5)	1 1/4 (3)	6 3/4 (17)	1.110 (2.8)	CBH-6189/240	2300	9 (4)

† Hole diameter should be held as close to heater diameter as possible for maximum heat transfer and heater life.

* Designate voltage, Insert "120" for 120 Vac or "240" for 240 Vac.

** Those model numbers containing /120, /240, or /480 are available only in that voltage.

Ordering Examples: **CBH-3025/240**, 2250 Watt, 240 Vac stud heater, **\$1150**.

CBH-1815/120, 1150 Watt, 120 Vac stud heaters, **\$1000**.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters