

INCOLOY SHEATH HIGH WATT DENSITY CARTRIDGE HEATERS 1 cm (1/2") Diameter

- ✓ Premium Quality
- ✓ 120 and 240 V
- ✓ Lengths from 3 to 46 cm (1 1/4 to 18")
- ✓ Lengths from 1 1/4 to 36"

- ✓ Rugged, Shock and Vibration Resistant
- ✓ UL Component Recognized
- ✓ CSA Certified

OMEGALUX® CIR series high watt density cartridge heaters are especially well suited for use in applications involving molds, dies, platens, hot plates, and sealing operations.

1/2" (1 cm) Dia. Type CIR Series
(Actual Dia. & Tolerance: 0.498"+ 0.000"-0.005")

MOST POPULAR MODELS HIGHLIGHTED!

To Order																	
Shth. Lgth. (cm)	Watt	W/in ²	Model No.	Price	Wt. lbs. (kg)	Shth. Lgth. (cm)	Watt	W/in ²	Model No.	Price	Wt. lbs. (kg)	Shth. Lgth. (cm)	Watt	W/in ²	Model No.	Price	Wt. lbs. (kg)
1 1/4 (3)	50	44	CIR-3014/120	\$36	.09(.4)	3 (8)	500	128	CIR-3030/*	\$44	.17(.08)	6 (15)	850	99	CIR-3060/*	\$58	.34(.15)
1 1/4 (3)	100	85	CIR-3012/120	36	.09(.4)	3 (8)	600	154	CIR-3034/*	44	.17(.08)	6 (15)	1000	117	CIR-3064/*	58	.34(.15)
1 1/4 (3)	125	107	CIR-3019/*	36	.09(.4)	3 (8)	750	192	CIR-30301/*	44	.17(.08)	6 1/2 (17)	1000	108	CIR-30601/240	61	.37(.17)
1 1/4 (3)	150	128	CIR-3013/*	36	.09(.4)	3 1/2 (9)	250	53	CIR-3035/*	46	.20(.09)	7 (18)	250	25	CIR-3070/120	64	.40(.18)
1 1/4 (3)	200	170	CIR-30121/240	36	.09(.4)	3 1/2 (9)	500	105	CIR-3037/*	46	.20(.09)	7 (18)	500	50	CIR-3071/*	64	.40(.18)
1 1/4 (3)	250	210	CIR-30122/240	36	.09(.4)	3 1/2 (9)	750	160	CIR-3038/240	46	.20(.09)	7 (18)	600	60	CIR-3072/*	64	.40(.18)
1 1/2 (4)	50	32	CIR-30151/120	37	.10(.05)	3 1/8 (10)	500	96	CIR-3039/*	48	.21(.11)	7 (18)	1000	98	CIR-3075/240	64	.40(.18)
1 1/2 (4)	100	60	CIR-3016/120	37	.10(.05)	4 (10)	150	28	CIR-3045/*	49	.22(.11)	7 1/2 (19)	500	46	CIR-3076/240	67	.43(.20)
1 1/2 (4)	125	80	CIR-3017/*	37	.10(.05)	4 (10)	180	33	CIR-3040/*	49	.22(.11)	7 1/2 (19)	1000	91	CIR-3077/240	67	.43(.20)
1 1/2 (4)	150	96	CIR-3015/*	37	.10(.05)	4 (10)	250	44	CIR-30402/*	49	.22(.11)	8 (20)	250	21	CIR-3083/240	70	.45(.20)
1 1/2 (4)	200	128	CIR-3018/*	37	.10(.05)	4 (10)	300	55	CIR-3042/*	49	.22(.11)	8 (20)	300	26	CIR-3085/*	70	.45(.20)
2 (5)	75	32	CIR-30204/120	39	.12(.05)	4 (10)	350	65	CIR-3046/*	49	.22(.11)	8 (20)	400	34	CIR-3081/240	70	.45(.20)
2 (5)	100	43	CIR-30201/*	39	.12(.05)	4 (10)	400	73	CIR-3043/*	49	.22(.11)	8 (20)	500	42	CIR-3084/*	70	.45(.20)
2 (5)	200	85	CIR-3021/*	39	.12(.05)	4 (10)	500	92	CIR-3041/*	49	.22(.11)	8 (20)	750	62	CIR-30801/240	70	.45(.20)
2 (5)	250	107	CIR-30202/*	39	.12(.05)	4 (10)	750	137	CIR-3044/*	49	.22(.11)	8 (20)	1000	85	CIR-3080/*	70	.45(.20)
2 (5)	300	128	CIR-30203/*	39	.12(.05)	4 (10)	1000	183	CIR-30401/240	49	.22(.11)	8 (20)	1500	128	CIR-3082/240	70	.45(.20)
2 (5)	400	171	CIR-3020/*	39	.12(.05)	4 3/8 (11)	550	91	CIR-3048/*	50	.22(.11)	8 (20)	2000	170	CIR-3086/240	70	.45(.20)
2 1/4 (6)	75	28	CIR-30221/120	41	.13(.06)	4 1/2 (11)	500	79	CIR-3047/*	48	.25(.11)	8 1/2 (22)	300	24	CIR-3087/240	73	.45(.20)
2 1/4 (6)	125	45	CIR-30222/120	41	.13(.06)	4 1/2 (11)	750	119	CIR-3049/*	48	.25(.11)	8 1/2 (22)	500	40	CIR-3088/240	73	.45(.20)
2 1/4 (6)	250	85	CIR-3022/*	41	.13(.06)	4 13/16 (12)	300	146	CIR-30403/240	50	.26(.12)	8 1/2 (22)	1000	80	CIR-3089/240	73	.45(.20)
2 1/4 (6)	400	145	CIR-30223/*	41	.13(.06)	4 13/16 (12)	1000	146	CIR-30404/240	50	.26(.12)	9 (23)	500	37	CIR-3090/240	76	.50(.23)
2 1/4 (6)	500	170	CIR-30224/*	41	.13(.06)	5 (13)	200	28	CIR-3053/*	51	.27(.12)	9 (23)	1000	74	CIR-3091/240	76	.50(.23)
2 3/8 (6)	75	26	CIR-3025/*	41	.13(.06)	5 (13)	350	50	CIR-3051/*	51	.27(.12)	9 1/2 (24)	500	36	CIR-3092/240	79	.53(.24)
2 3/8 (6)	100	34	CIR-3026/*	41	.13(.06)	5 (13)	400	56	CIR-3054/*	51	.27(.12)	9 1/2 (24)	1000	72	CIR-3093/240	79	.53(.24)
2 3/8 (6)	120	41	CIR-3027/*	41	.13(.06)	5 (13)	500	71	CIR-30501/*	51	.27(.12)	10 (25)	475	32	CIR-3100/240	82	.56(.25)
2 3/8 (6)	250	85	CIR-3023/*	41	.13(.06)	5 (13)	750	107	CIR-3050/*	51	.27(.12)	10 (25)	500	34	CIR-3103/*	82	.56(.25)
2 3/8 (6)	450	154	CIR-3024/*	41	.13(.06)	5 (13)	1000	142	CIR-30502/240	51	.27(.12)	10 (25)	1000	68	CIR-3101/*	82	.56(.25)
2 3/8 (6)	500	170	CIR-30231/*	41	.13(.06)	5 1/4 (13)	250	34	CIR-3052/*	53	.29(.13)	10 (25)	1500	101	CIR-3102/240	82	.56(.25)
2 1/2 (6)	100	32	CIR-30255/*	42	.14(.06)	5 1/2 (14)	500	64	CIR-3055/*	55	.31(.14)	10 (25)	2000	134	CIR-3105/240	82	.56(.25)
2 1/2 (6)	150	48	CIR-30251/*	42	.14(.06)	5 1/2 (14)	650	83	CIR-3056/240	55	.31(.14)	12 (30)	550	31	CIR-3121/*	95	.67(.30)
2 1/2 (6)	250	80	CIR-30252/*	42	.14(.06)	5 1/2 (14)	750	97	CIR-3057/*	55	.31(.14)	12 (30)	1000	56	CIR-3122/*	95	.67(.30)
2 1/2 (6)	400	128	CIR-30253/*	42	.14(.06)	5 13/16 (15)	300	36	CIR-30582/240	56	.32(.15)	12 (30)	1500	84	CIR-3120/240	95	.67(.30)
2 1/2 (6)	500	160	CIR-30254/*	42	.14(.06)	5 13/16 (15)	700	85	CIR-3058/*	56	.32(.15)	12 (30)	2000	112	CIR-3125/240	95	.67(.30)
2 1/2 (6)	300	96	CIR-3028/*	42	.14(.06)	6 (15)	200	22	CIR-3065/240	58	.34(.15)	14 (36)	1000	48	CIR-3141/240	107	.78(.35)
2 5/8 (7)	350	106	CIR-3029/240	42	.14(.06)	6 (15)	250	27	CIR-3067/*	58	.34(.15)	14 (36)	1600	76	CIR-3140/240	107	.78(.35)
2 5/8 (7)	300	92	CIR-30291/240	42	.14(.06)	6 (15)	300	35	CIR-3061/*	54	.34(.15)	14 (36)	2300	110	CIR-3142/240	107	.78(.35)
2 3/4 (8)	400	113	CIR-30271/*	43	.14(.06)	6 (15)	350	41	CIR-3068/240	58	.34(.15)	15 (38)	1500	66	CIR-3150/240	114	.84(.38)
3 (8)	125	32	CIR-30302/*	44	.17(.08)	6 (15)	400	45	CIR-3066/240	58	.34(.15)	16(41)	1000	41	CIR-3160/240	120	.84(.38)
3 (8)	250	64	CIR-3031/*	44	.17(.08)	6 (15)	500	58	CIR-3062/*	58	.34(.15)	18(46)	1500	55	CIR-3182/240	132	1.0(.45)
3 (8)	400	103	CIR-3033/*	44	.17(.08)	6 (15)	750	87	CIR-3063/*	58	.34(.15)	18(46)	1700	62	CIR-3180/240	132	1.0(.45)

* Designated voltage; ie: insert "120" for 120 Vac or "240" for 240 Vac. Model numbers that contain "/120" or "/240" are available only in those voltages. Note: 1/2" diameter CIR series cartridge heaters use 16 AWG stranded lead wire.
Ordering Example: CIR-3019/120, 1/2" diameter cartridge heater, 120 Vac, \$36.

CARTRIDGE HEATERS

SPECIFICATIONS

Sheath: Material, Incoloy; black oxide finish for efficient heat transfer; max temp 1500°F; welded, sealed tip.

Leads: Type "F"; stranded, flexible manganese nickel wire insulated with fiberglass, max temp 450°C (842°F), 14" standard length; longer leads available

Heater Wire: Premium grade nickelchromium resistance wire for longer life, and consistent performance

Insulation: Specially formulated refractory insulation, rigidly controlled, densely compacted to improve thermal conductivity and dielectric strength

Internal Connections: Patented connector for high reliability and longer life; vibration and shock resistant construction

Voltage: 120V or 240V must be specified at time of order



CIR-1014/120V, \$51, shown smaller than actual size.

5/8" (1 cm) Nominal Dia. CIR Series
(Actual Dia. & Tolerance: 0.622" + 0.000" - 0.055")

MOST POPULAR MODELS HIGHLIGHTED!

To Order

Stht. Lgth. (cm)	Watt	W/in ²	Model No.	Price	Wt. lbs. (kg)	Stht. Lgth. (cm)	Watt	W/in ²	Model No.	Price	Wt. lbs. (kg)	Stht. Lgth. (cm)	Watt	W/in ²	Model No.	Price	Wt. lbs. (kg)
1¼ (3)	50	34	CIR-4011/120	\$45	.10(.05)	5 (13)	250	28	CIR-4056/*	\$62	.32(.14)	10% (27)	500	25	CIR-4107/*	\$102	.68(.31)
1¼ (3)	200	135	CIR-4012/120	45	.10(.05)	5 (13)	500	57	CIR-4051/*	62	.32(.14)	10% (27)	1700	85	CIR-4105/*	102	.68(.31)
1¼ (3)	250	169	CIR-4013/120	45	.10(.05)	5 (13)	750	85	CIR-4050/*	62	.32(.14)	12 (30)	500	224	CIR-4125/*	109	.75(.34)
1½ (4)	100	51	CIR-4016/*	47	.10(.05)	5 (13)	1000	114	CIR-4052/*	62	.33(.15)	12 (30)	900	40	CIR-4129/240	129	.75(.34)
1½ (4)	200	101	CIR-4015/*	47	.10(.05)	5 (13)	1300	148	CIR-4053/240	62	.32(.07)	12 (30)	1000	45	CIR-4120/240	111	.75(.34)
1½ (4)	250	126	CIR-4017/*	47	.10(.05)	5% (14)	285	30	CIR-4055/*	64	.34(.07)	12 (30)	1500	67	CIR-4121/240	111	.75(.34)
2 (5)	100	34	CIR-40201/120	50	.13(.06)	5% (14)	800	84	CIR-4054/*	64	.34(.07)	12 (30)	2000	89	CIR-4122/240	111	.75(.34)
2 (5)	200	68	CIR-4020/*	50	.13(.06)	6 (15)	300	28	CIR-4067/*	69	.34(.07)	12% (33)	550	23	CIR-4128/240	117	.81(.36)
2 (5)	300	103	CIR-4021/*	50	.13(.06)	6 (15)	500	47	CIR-4061/*	69	.38(.17)	14 (36)	3700	139	CIR-4140/240	123	.88(.40)
2 (5)	500	171	CIR-4022/*	50	.13(.06)	6 (15)	750	70	CIR-4063/240	69	.38(.17)	15 (38)	600	21	CIR-4151/240	130	.95(.43)
2¼ (6)	100	29	CIR-4023/120	52	.15(.07)	6 (15)	1000	93	CIR-4060/*	69	.38(.17)	15 (38)	750	27	CIR-4153/240	130	.95(.43)
2¼ (6)	250	72	CIR-4028/*	52	.15(.07)	6 (15)	1500	140	CIR-4062/*	69	.38(.17)	15 (38)	1500	53	CIR-4152/240	130	.95(.43)
2¼ (6)	350	102	CIR-4029/*	52	.15(.07)	6% (17)	350	30	CIR-4066/*	72	.41(.18)	15 (38)	2400	85	CIR-4150/240	130	.95(.43)
2% (6)	125	34	CIR-4025/*	52	.15(.07)	6% (17)	500	43	CIR-4068/*	72	.41(.18)	15 (38)	4000	140	CIR-4154/240	130	.95(.43)
2% (6)	150	41	CIR-4026/*	52	.15(.07)	6% (17)	1000	85	CIR-4065/*	72	.41(.18)	16 (38)	2500	82	CIR-4160/240	137	1.02(.45)
2% (6)	180	49	CIR-4027/*	52	.15(.07)	7 (18)	500	39	CIR-4072/*	75	.45(.20)	16 (38)	4500	148	CIR-4167/240	137	1.02(.45)
2% (6)	280	77	CIR-4024/*	52	.15(.07)	7 (18)	1000	79	CIR-4070/240	75	.45(.20)	18 (46)	1500	44	CIR-4180/240	150	1.18(.5)
3 (8)	150	31	CIR-4035/120	56	.20(.09)	7 (18)	1500	118	CIR-4071/240	75	.45(.20)	18 (46)	2600	76	CIR-4181/240	150	1.18(.5)
3 (8)	250	51	CIR-4031/*	56	.20(.09)	8 (20)	400	27	CIR-4081/240	82	.50(.22)	18 (46)	3000	88	CIR-4182/240	150	1.18(.5)
3 (8)	400	82	CIR-4032/*	56	.20(.09)	8 (20)	500	34	CIR-4085/*	82	.50(.22)	18 (46)	4700	138	CIR-4184/240	150	1.18(.5)
3 (8)	500	103	CIR-4030/*	56	.20(.09)	8 (20)	750	51	CIR-4082/240	82	.50(.22)	20 (51)	1500	40	CIR-4200/240	164	1.26(.5)
3 (8)	600	123	CIR-4033/240	56	.20(.09)	8 (20)	850	58	CIR-4088/240	82	.50(.22)	20 (51)	3500	92	CIR-4203/240	164	1.26(.6)
3 (8)	750	154	CIR-4034/240	56	.20(.09)	8 (20)	1000	68	CIR-4083/240	82	.50(.22)	20 (51)	4700	123	CIR-4205/240	164	1.26(.6)
3¾ (10)	240	38	CIR-4038/*	61	.20(.09)	8 (20)	1200	82	CIR-4080/*	82	.50(.22)	21 (53)	2800	70	CIR-4210/240	171	1.32(.6)
3¾ (10)	525	83	CIR-4037/*	61	.20(.09)	8 (20)	1500	103	CIR-4084/240	82	.50(.22)	24 (61)	1200	26	CIR-4241/240	191	1.51(.7)
4 (10)	250	37	CIR-4044/*	63	.26(.11)	8 (20)	2000	137	CIR-40801/240	82	.50(.22)	24 (61)	2000	44	CIR-4242/240	191	1.51(.7)
4 (10)	400	58	CIR-4045/*	63	.26(.11)	8% (22)	450	27	CIR-4087/240	87	.50(.22)	24 (61)	3000	65	CIR-4240/240	191	1.51(.7)
4 (10)	500	73	CIR-4041/*	63	.26(.11)	10 (25)	500	27	CIR-4103/*	96	.64(.3)	24 (61)	2700	102	CIR-4243/240	191	1.51(.7)
4 (10)	600	88	CIR-4046/240	63	.26(.11)	10 (25)	750	40	CIR-4104/240	96	.64(.3)	36 (91)	3000	44	CIR-4361/240	275	2.27(1)
4 (10)	750	110	CIR-4040/*	63	.26(.11)	10 (25)	1000	54	CIR-4100/240	96	.64(.3)	36 (91)	3500	51	CIR-4360/240	275	2.27(1)
4 (10)	1000	147	CIR-4042/240	63	.26(.11)	10 (25)	1500	81	CIR-4101/240	96	.64(.3)						
4% (11)	240	32	CIR-4043/*	65	.28(.13)	10 (25)	2000	108	CIR-4102/240	96	.64(.3)						

* Specify voltage, insert "-120" for 120 Vac or "-240" for 240 Vac. Model numbers that contain "/120" or "/240" are available only in those voltages. Note: ½" diameter CIR series cartridge heaters use 16 AWG stranded lead wire.
Ordering Example: CIR-4020/240, 5/8" diameter cartridge heater, 120 Vac, \$50.

To Order, Call **1-800-872-4328** or Shop Online at **omega.comSM**



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters