

HIGH WATT DENSITY CARTRIDGE HEATERS WITH INCOLOY® SHEATH

1/4" (1CM) DIAMETER



- ✓ Reliable Premium Quality
- ✓ Rugged, Shock and Vibration Resistant
- ✓ UL Component Recognized
- ✓ CSA Certified
- ✓ Lengths from 3 to 15 cm (1¼ to 6")
- ✓ 120 and 240 Vac Models

OMEGALUX® CIR series high watt density cartridge heaters are manufactured to the highest industry standards using only premium materials. They have been designed to last longer and outperform any other brand cartridge heater in both laboratory and industrial applications. Their heavy duty construction provides high dielectric strength as well as shock and vibration resistance.



CIR Series Starts at \$47

CAUTION AND WARNING!
Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel. See inside back cover for additional warnings.

1/4" Nominal Diameter CIR Series
(Actual Dia. and Tolerance: 0.248" ± 0.005") 0.000"

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)																	
Shth. Lgth.	Watts	W/in ²	Model No.	Price	Wt lbs	Shth. Lgth.	Watts	W/in ²	Model No.	Price	Wt. lbs	Shth. Lgth.	Watts	W/in ²	Model No.	Price	Wt. lbs
1¼	75	128	CIR-1013/120	\$47	.02	2	250	214	CIR-1024/*	\$51	.03	4	150	53	CIR-1044/240	\$60	.04
1¼	100	171	CIR-1012/120	47	.02	2	300	256	CIR-10201/240	51	.03	4	200	73	CIR-1042/*	60	.04
1¼	150	256	CIR-1014/120	47	.02	2½	175	112	CIR-1025/*	53	.03	4	250	92	CIR-1043/240	60	.04
1¼	225	388	CIR-10121/240	51	.02	2½	200	128	CIR-1027/*	53	.03	4	300	110	CIR-1040/*	60	.04
1½	50	64	CIR-1016/120	48	.02	2½	250	160	CIR-1029/*	53	.03	4½	200	61	CIR-1046/120	66	.05
1½	100	128	CIR-1017/120	48	.02	3	100	51	CIR-1031/*	56	.04	4½	300	93	CIR-1045/240	66	.05
1½	125	160	CIR-1015/120	48	.02	3	150	77	CIR-1034/*	56	.04	5	100	28	CIR-1051/120	69	.05
1½	150	192	CIR-1018/120	48	.02	3	200	103	CIR-1030/*	56	.04	5	150	42	CIR-1050/1240	69	.05
1½	175	220	CIR-1019/120	48	.02	3	250	129	CIR-10301/240	56	.04	5	200	57	CIR-1052/*	69	.05
1½	200	256	CIR-10151/*	48	.02	3	300	153	CIR-1032/*	56	.04	5	300	85	CIR-1053/*	69	.05
1½	250	290	CIR-10153/240	48	.02	3	400	205	CIR-1033/240	56	.04	5	350	100	CIR-1050/240	69	.05
2	80	67	CIR-1026/120	51	.03	3½	100	43	CIR-1035/*	58	.04	5	400	111	CIR-1054/240	69	.05
2	100	85	CIR-1021/120	51	.03	3½	200	85	CIR-1036/*	58	.04	5½	150	38	CIR-1055/240	73	.05
2	125	107	CIR-1022/*	51	.03	3½	225	96	CIR-1038/240	58	.04	5½	500	126	CIR-1056/240	73	.05
2	150	128	CIR-1020/*	51	.03	3½	300	127	CIR-1037/240	58	.04	6	400	93	CIR-1060/240	76	.06
2	200	171	CIR-1023/*	51	.03	4	100	37	CIR-1041/*	60	.04						

* Designate voltage, insert "120" for 120 Vac or "240" for 240 Vac. Those model numbers containing 120 or 240 are only available in that voltage. Note: 1/4" diameter CIR series cartridge heaters use 22 AWG stranded lead wire.

Ordering Example: CIR-1014/120, 1¼" long, high watt density cartridge heater, \$47.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters