

WATER-CIRCULATING TEMPERATURE CONTROLLER

CMX Series
Starts at
\$4350

- ✓ Water and Water/Glycol Solutions to 121°C (250°F)
- ✓ 4.5 to 24 kW (15 to 82 Mbh)
- ✓ 240 and 480V, 3-Phase, 60 Hz
- ✓ 57 kg (125 lb) Carbon Steel Construction
- ✓ Heavy-Duty 0.430" Dia. Incoloy Sheath Elements
- ✓ ¾ hp Cast-Iron Bronze Fitted Centrifugal Pump (30 GPM @ 20 psi TDH)
- ✓ Dual Digital Display: PID Temperature and Process Control
- ✓ Built-In Indicators for Pump Overload, Low Water Pressure, and Overtemperature
- ✓ Portable Cabinet with Casters
- ✓ Easy-to-Access Service Features
- ✓ NEMA 1 (IP23) Electrical Enclosure with 120V Control Transformer and Magnetic Contactors
- ✓ Dual Pressure Gauges Monitor Pressure to and From Process
- ✓ Open- or Closed-Loop Cooling (3.8 ft² Heat Exchanger)
- ✓ Automatic Air Purge Valve
- ✓ Large-Diameter (1¼ NPT) Piping Connections
- ✓ ASME 125 psig Relief Valve

APPLICATIONS

OMEGA's CMX Series water-circulating temperature controllers are compact, versatile, and completely self-contained water heating and cooling systems. They can be used for any application that requires precise temperature control of a heating and cooling water circulation system, but are particularly useful in the plastics industry as mold temperature controllers. Applications include the following:

- Injection molding machines—thermoplastics and thermosets
- Platens and dies
- Rolls, laminating, and calendering
- Pipeline heating and tracing
- Jacketed vessels and tanks

The built-in electronic temperature and process controller features separate PID algorithms for heat and cool control modes, dual display of setpoint and process temperatures, and simple configuration parameters with alphanumeric cues. Even though these systems are sophisticated and state of the art, they are still easy to use and require very little training to program and operate. Standard NPT-threaded piping connections allow for convenient hook-up to external piping.



CMX-250-4/240-NM, \$4350, shown smaller than actual size.

OPTIONS

- Alternative voltages available for 208 and 575V, 3-phase, 60 Hz, and 240, 380 and 415V, 3-phase, 50 Hz distribution systems
- Alternative pumps rated 1.5, 3, 5 or 7.5 hp with pumping capacities to 80 GPM @ 70 psi TDH
- Power controllers—electronic solid state (SCR)
- Surge reduction valve
- Digital communication interface
- Expanded open- or closed-loop cooling
- High temperature operation to 275°F
- Electrical enclosure door interlock
- IEC-style "dry contact" power contactor

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model No.	Price	kW	V	Phase	Pump Motor (hp)	Dimensions: (in)			Cooling Type	Wt. (lb)
						H	W	D		
CMX-250-4/240-NM	\$4350	4.5	240	3	¾	29	15	25	Open loop	200
CMX-250-4/480-NM	4350	4.5	480	3	¾	29	15	25	Open loop	200
CMX-250-4C/240-NM	5250	4.5	240	3	¾	29	15	25	Closed loop	215
CMX-250-4C/480-NM	5445	4.5	480	3	¾	29	15	25	Closed loop	215
CMX-250-9/240-NM	4450	9	240	3	¾	29	15	25	Open loop	200
CMX-250-9/480-NM	4390	9	480	3	¾	29	15	25	Open loop	200
CMX-250-9C/240-NM	5525	9	240	3	¾	29	15	25	Closed loop	215
CMX-250-9C/480-NM	5475	9	480	3	¾	29	15	25	Closed loop	215
CMX-250-12/240-NM	4775	12	240	3	¾	29	15	25	Open loop	200
CMX-250-12/480-NM	4585	12	480	3	¾	29	15	25	Open loop	200
CMX-250-12C/480-NM	5755	12	480	3	¾	29	15	25	Closed loop	215
CMX-250-12C/240-NM	5850	12	240	3	¾	29	15	25	Closed loop	215
CMX-250-18/240-NM	4850	18	240	3	¾	29	15	25	Open loop	200
CMX-250-18/480-NM	5405	18	480	3	¾	29	15	25	Open loop	200
CMX-250-18C/240-NM	5405	18	480	3	¾	29	15	25	Closed loop	215
CMX-250-18C/480-NM	5405	18	480	3	¾	29	15	25	Closed loop	215
CMX-250-24/240-NM	5599	24	240	3	¾	29	15	25	Open loop	200
CMX-250-24/480-NM	4855	24	480	3	¾	29	15	25	Open loop	200
CMX-250-24C/240-NM	5885	24	240	3	¾	29	15	25	Closed loop	215
CMX-250-24C/480-NM	5710	24	480	3	¾	29	15	25	Closed loop	215

Ordering Examples: CMX-250-12/240-NM, 12 kW, 240V, \$4775.
CMX-250-4/480-NM, 4.5 kW, 480V, \$4350.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters