

# PORTABLE DIAL GAUGE CALIBRATOR KIT

## FOR USE WITH 1/4% ACCURACY TEST GAUGES

DWT1327D  
**\$2725**  
 Dial Gauges  
 Additional




- ✓ Portable—Weighs Less than 40 lb
- ✓ 1/4% Accuracy When Used with OMEGA® Test Dial Gauges
- ✓ 2-Stage Hydraulic Pump
- ✓ Vernier Screw Adjustment
- ✓ Rugged Metal Case Holds Up to 4 Dial Gauges

A portable pressure standard with 1/4% accuracy dial gauges, the DWT1327D test set is ideal for field testing or remote in-plant applications. It consists of a 2-stage hydraulic pump and a manifold that is pressurized during operation. The pump features a shuttle valve that increases the speed of pressure buildup and makes it easier to use the pump handle. The manifold has 2 connections: one for a 4 1/2" PGT-45L solid-front test dial gauge (1/4% dial gauge span accuracy), the other for most standard-size dial gauges.

### SPECIFICATIONS

#### TEST SET

**Accuracy:** 1/4% of dial gauge span  
**Operating Pressure:** 0 to 10,000 psi (0 to 70,000 kPa) max  
**Body Material:** Aluminum alloy  
**Operating Fluid:** SAE 20 automotive or machine oil  
**O-Ring:** Standard Buna-N  
**Reservoir Volume:** Approximately 0.7 liter (1.5 pints)



DWT1327D, \$2725, with PGT-45L-600, \$390, shown smaller than actual size.

#### Included Accessories:

Complete test set includes 2-stage hydraulic pump with base; 3 wrenches for dial gauge installation and removal; spare O-rings; all piping, fittings, and 1/4 and 1/2 NPT adaptors; rugged metal carrying case that holds up to 4 test dial gauges; and operator's manual

#### TEST DIAL GAUGES

**Type and Size:** PGT-45L 4 1/2" test dial gauges, see page G-58

**Accuracy:** 1/4% of dial gauge span

**Bourdon Tube Materials:** Monel®

**AVAILABLE FOR FAST DELIVERY!**

### To Order (Specify Model Number)

MODEL NO.	PRICE	DESCRIPTION
DWT1327D	\$2725	Portable dial gauge calibration kit

1/4% TEST DIAL GAUGES 4 1/2" DIAL SIZE (Order Test Dial Gauges Separately)

MODEL NO.	PRICE	RANGE (psi)	GRADUATIONS	
			MAJOR	MINOR
PGT-45L-100	\$390	0 to 100	5	0.5
PGT-45L-600	390	0 to 600	50	2
PGT-45L-1000	390	0 to 1000	50	5
PGT-45L-5000	390	0 to 5000	500	20
PGT-45L-10,000	390	0 to 10,000	500	50

**Note:** Test dial gauges are available with ranges from 15 to 10,000 psi; see page G-61 for additional ranges.

Comes complete with pump, wrenches, spare o-rings, piping, fittings and NPT adaptors, rugged carrying case, and operator's manual.

**Ordering Example:** DWT1327D, portable dial gauge calibration kit, plus 4 test dial gauges (order separately): PGT-45L-100 (100 psi range), PGT-45L-600 (600 psi range), PGT-45L-1000 (1000 psi range) and PGT-45L-5000 (5000 psi range), \$2725 + 390 + 390 + 390 + 390 = \$4285.

Recommended Reference Book: Accepting Sampling in Quality Control, GE-2567, \$120. Visit [omega.com/bobi](http://omega.com/bobi) for Additional Books





#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters