

MINIATURE DC OUTPUT LVDT DISPLACEMENT TRANSDUCERS WITH ACETAL BEARINGS

LD400 Series

±1 to ±5 mm
(±0.04 to ±0.20")

Starts at
\$360



- ✓ High-Output Miniature Transducers
- ✓ Acetal Bearings for Precise Motion
- ✓ Infinite Resolution
- ✓ Rugged, Low-Mass Construction
- ✓ Compatible with Standard DC Signal
- ✓ Conditioning Modules and Instruments

The LD400 Series miniature DC to DC transducers can measure displacements up to ±5 mm (±0.20") with very high accuracy and infinite resolution. Their free-guided armature incorporates acetal bearings, which provide near-frictionless motion to detect the smallest movement the associated instrumentation is capable of identifying.

These transducers use a precision linear variable differential transformer as the measuring source, along with hybrid ICs, including an oscillator, demodulator, and filter. Together, they make up a self-contained unit that accepts DC input and provides DC output relative to armature position. The unit's high linearity and low mass of moving parts are ideal for applications in civil, mechanical, chemical, and production engineering.



LD400-5, \$390, shown actual size.

SPECIFICATIONS

ELECTRICAL

Linearity: 0.3% FS
Sensitivity: (mV/V/mm) see chart below (actual output supplied with each unit)

Excitation: 10 to 24 Vdc regulated

Energizing Current at 10 Vdc:
LD400-1, 10 mA; LD400-25, 10 mA;
LD400-5, 13 mA

Response Time: LD400-1 and
LD400-2.5 = 5 ms; LD400-5 = 3 ms

Frequency Response: 50 Hz for -3 dB
Ripple: <1% FS

Thermal Effect: Zero: LD400-1 <0.02%
FS/°C; LD400-2.5 and LD400-5 <0.01%
FC/°C; sensitivity: <0.025% FC/°C

Compensated Temperature Range:
-20 to 80°C (-4 to 176°F)

Operating Temperature Range:
-20 to 80°C (-4 to 176°F)

Electrical Connection: 2.9 m (9')
shielded, color-coded cable

Sensitivity and Linearity Data:
Provided with a transducer output
impedance of 2.4 kΩ into a calibration
load of 20 kΩ at 20°C (68°F); variations
in these parameters will change
performance

MECHANICAL

Threaded Core: M2 thread

Core Material: Ni/Fe—Radio Metal 50

Case Material:

400 Series stainless steel

Weight: See chart on page J-12

CONNECTIONS

Electrical Connections:

Red: + Excitation

Blue: - Excitation

White: + Signal*

Green: - Signal

Yellow: No connection

* White and red in phase for positive
inward displacement.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

MODEL NO.	STROKE	PRICE	SENSITIVITY	COMPATIBLE METERS**
LD400-1	±1.0 mm (0.06")	\$360	75 mV/V/mm	DP41-S, DP25B-S
LD400-2.5	±2.5 mm (0.10")	380	75 mV/V/mm	DP41-S, DP25B-S
LD400-5	±5.0 mm (0.20")	390	54 mV/V/mm	DP41-S, DP25B-S

** See section D for compatible meters.

Ordering Example: LD400-5, stroke of -5 mm, \$390.

MINIATURE DC DISPLACEMENT TRANSDUCERS




DP25B-S, \$245, see pages D-23 to D-25 for details.



DP41-S, \$545, see pages D-29 to D-32 for details.

Both meters shown slightly smaller than actual size.




See Section Y for a Selection of Scientific, Technical, and Reference Books Available from omega.com

LD400-5, \$390, shown actual size.

COMPATIBLE INSTRUMENTS

MODEL NO.	PRICE	DESCRIPTION
DP25B-S	\$245	Ratiometric voltage and current input meter with excitation
DP41-S	545	115 Vac powered strain gage indicator



MODEL NO.	LINEAR STROKE mm (in)	DIMENSIONS*: mm (in)		WEIGHT g (oz)	
		A	B	BODY	CORE (GUIDED)
LD400-1	±1.0 (0.04)	21.5 (0.85)	37 (1.46)	26 (1.02)	1.0 (0.04)
LD400-2.5	±2.5 (0.10)	21.5 (0.85)	37 (1.46)	26 (1.02)	1.0 (0.04)
LD400-5	±5.0 (0.20)	20.5 (0.81)	43 (1.69)	30 (1.18)	1.2 (0.04)

* At electrical zero.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters