

MULTIFUNCTION CALIBRATOR

PORTABLE, HIGH ACCURACY

PCL1200 Series

\$1895



PCL1200, \$1895,
shown smaller
than actual size.

Three sets
of leads
included!



- ✓ Measures and Sources T/C (13 Types), RTDs (13 Types), Ohms, Current, Voltage, Frequency
- ✓ Sources Pulse Trains
- ✓ Isolated mA/V Readback Circuit for Complete Transmitter Calibration
- ✓ Pressure Module Communication Port Compatible with OMEGA Pressure Modules
- ✓ Built-In 24V Supply Can Drive 4 to 20 mA Loops Up to 1000 Ω
- ✓ Direct Entry of Custom RTD Coefficients (R0, A, B, C)
- ✓ All Source Modes Can be Programmed with Dedicated Setpoints to Speed Calibration and Linearity Tests
- ✓ Highest Accuracy in Class—to 0.015% of Reading
- ✓ Meets CE Requirements and is Designed to IEC 1010 Safety Standards
- ✓ Supplied with Full Rubber Boot

The PCL1200 multifunction calibrator has a feature set unmatched by other high-accuracy handheld calibrators in its price range. It is portable, provides the functions and accuracy of a laboratory-grade instrument, and has everything needed for virtually any calibration task. It can also measure and source thermocouples, RTDs, current, voltage, and frequency, and it can source pulse trains. It has a communications port for pressure modules and an isolated mA/V readback circuit. Arrow keys, direct numeric keypad entry, and 3 software-driven function buttons combine with a large, backlit, menu-driven graphics display to provide a highly intuitive yet powerful interface. A built-in 250 Ω resistor for Hart® compatibility, compatibility with smart transmitters and PLCs, full fuseless protection, and a serial communications port for control using ASCII commands are additional features that make the PCL1200 indispensable for calibration tasks. It comes with a

tough rubber boot; an optional carrying case is available.

Measuring Pressure with the PCL1200

With a PCL-PMA pressure module adaptor, the PCL1200 will work with all OMEGA PCL-PM pressure modules. See Specifications and "To Order" chart.

Specifications

(23 \pm 5°C unless otherwise noted)
Operating Temperature: -10 to 50°C (14 to 122°F)
Storage Temperature: -20 to 70°C (-4 to 158°F)
Stability: \pm 0.005% rdg/°C outside of 23 \pm 5°C (73 \pm 9°F)
Cold Junction Compensation (Thermocouple) Error: \pm 0.2°C (0.4°F)
Power Requirements: 6 Vdc
Batteries: 4 "AA", alkaline (included)
Dimensions: 221 H x 107 W x 58 mm D (8.7 x 4.2 x 2.3")
Weight: 863 g (30.5 oz)

MULTIFUNCTION CALIBRATOR



TYPE	RANGE		ACCURACY	
VOLTAGE				
Source	0.000 to 20.000 Vdc		±0.015% rdg + 2 mV	
Read, Isolated	0.000 to 30.000 Vdc		±0.015% rdg + 2 mV	
Read, Non-Isolated	0.000 to 20.000 Vdc		±0.015% rdg + 2 mV	
THERMOCOUPLE mV				
Read/Source	-10.000 to 75.000 mV		±0.02% rdg + 10 µV	
CURRENT				
Read	0.000 to 24.000 mA		±0.015% rdg + 2 µA	
FREQUENCY (1 TO 20V SELECTABLE AMPLITUDE)				
CPM, Read	2.0 to 600.0 CPM		±0.05% rdg (+1 LSD read)	
Hz, Read	1.0 to 1000.0 Hz		±0.05% rdg (+1 LSD read)	
kHz, Read	1.00 to 10.00 kHz		±0.05% rdg +1 LSD	
kHz, Source	1.00 to 10.00 kHz		±0.250% rdg	
RESISTANCE (Ω)				
Read	0.00 to 4000.0 Ω		400Ω range: ±0.025% rdg + 0.05Ω 4000Ω range: ±0.025% rdg + 0.5Ω	
Source	5.0 to 4000 Ω			
THERMOCOUPLE				
J	-200.0 to 1200.0°C	-328.0 to 2192.0°F	0.2°C	0.4°F
K	-200.0 to 1370.0°C	-328.0 to 2498.0°F	0.3°C	0.5°F
T	-200.0 to 400.0°C	-328.0 to 752.0°F	0.2°C	0.4°F
E	-200 to 950°C	-328.0 to 1742.0°F	0.2°C	0.4°F
R	0.0 to 1750.0°C	32.0 to 3182.0°F	1.2°C	2.2°F
S	0.0 to 1750.0°C	32.0 to 3182.0°F	1.2°C	2.2°F
B	600.0 to 1800.0°C	1112.0 to 3272.0°F	1.2°C	2.2°F
C	0.0 to 2316.0°C	32.0 to 4200.0°F	0.6°C	1.1°F
XK	-200.0 to 800.0°C	-328.0 to 1472.0°F	0.2°C	0.4°F
BP	0.0 to 2500.0°C	32.0 to 4532.0°F	0.9°C	1.6°F
L	-200.0 to 900.0°C	-328.0 to 1652.0°F	0.2°C	0.4°F
U	-200.0 to 400.0°C	-328.0 to 752.0°F	0.25°C	0.45°F
N	-200.0 to 1300.0°C	-328.0 to 2372.0°F	0.4°C	0.7°F
RTD/THERMISTOR				
Ni120 (672)	-80.0 to 260.0°C	-112.0 to 500.0°F	0.2°C	0.4°F
Pt100 (385)	-200.0 to 800.0°C	-328.0 to 1472.0°F	0.2°C	0.4°F
Pt100 (3926)	-200.0 to 630.0°C	-328.0 to 1166.0°F	0.2°C	0.4°F
Pt100 (3916)	-200.0 to 630.0°C	-328.0 to 1166.0°F	0.2°C	0.4°F
Pt200 (385)	-200.0 to 630.0°C	-328.0 to 1166.0°F	0.8°C	1.4°F
Pt500 (385)	-200.0 to 630.0°C	-328.0 to 1166.0°F	0.4°C	0.7°F
Pt1000 (385)	-200.0 to 630.0°C	-328.0 to 1166.0°F	0.2°C	0.4°F
Cu10	-100.0 to 260.0°C	-148.0 to 500.0°F	1.4°C	2.5°F
Cu50	-180.0 to 200.0°C	-292.0 to 392.0°F	0.4°C	0.7°F
Cu100	-180.0 to 200.0°C	-292.0 to 392.0°F	0.3°C	0.5°F
Pt385-10	-200.0 to 800.0°C	-328.0 to 1472.0°F	1.4°C	2.5°F
Pt385-50	-200.0 to 800.0°C	-328.0 to 1472.0°F	0.4°C	0.7°C
400 Series Thermistor	15.00 to 50.00°C	15.00 to 122.00°F	0.1°C	0.2°C

READBACK DISPLAY

The top half of the display is dedicated to readback from the device under test, or a pressure module.

MAIN DISPLAY

The lower half of the display is for all input and output combinations.

FUNCTION KEYS

Three software-controlled function keys; functions displayed over each button at bottom of display.

POWER ON/OFF

Turns power on/off. Auto shut-off button.

HOME KEY

HOME key displays main operating screen.

CLEAR ENTRY KEY

Allows clearing of entry.

NUMERIC KEYPAD


Rapid numeric entry of data values.

ENTER KEY

Accepts entries into memory and updates outputs.

CURRENT (mA)

Input/output for current.



PRESSURE MODULE COMMUNICATIONS PORT

Pressure modules connector; compatible with pressure modules (not shown). Pressure measurements from 1 inH₂O to 10,000 psi, module dependent.

ARROW KEYS

Arrow keys allow rapid movement of cursor and setting of output values.

COMPUTER COMMUNICATION CONNECTION

Mini-jack (stereo) serial communications connection. Allows full remote control.

VOLTAGE/Ω/Hz

Input/output for voltage/Ω/Hz.

THERMOCOUPLE

Input/output for thermocouple.

ISOLATED READBACK JACKS

Volts, mA, and mA with loop power.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

MODEL NO.	PRICE	DESCRIPTION		
PCL1200	\$1895	High-accuracy multifunction calibrator		
MODULES – MOST POPULAR RANGES*				
MODEL NO.	PRICE	PARAMETER RANGE GAUGE psig	ACCURACY	OVERPRESSURE
PCL-PM030G	\$795	0 to 30 (0 to 2 bar)	±0.025%	300%
PCL-PM050G	795	0 to 50 (0 to 3.5 bar)	±0.03%	300%
PCL-PM100G	795	0 to 100 (0 to 7 bar)	±0.025%	300%
PCL-PM300G	795	0 to 300 (0 to 20 bar)	±0.025%	200%
PCL-PM1KG	795	0 to 1000 (0 to 70 bar)	±0.05%	200%
PCL-PM3KG	795	0 to 3000 (0 to 200 bar)	±0.1%	200%
PCL-PM5KG	795	0 to 5000 (0 to 340 bar)	±0.1%	200%
PCL-PM015VAC	795	0 to -15 (0 to -1 mbar)	±0.025%, ±0.0025 psi	300%
PCL-PM015A	795	0 to 15 (0 to 1 bar) absolute	±0.025%, ±0.0025 psi	300%
PCL-PM030A	795	0 to 30 (0 to 2 bar) absolute	±0.025%	300%
PCL-PM015C	795	-15 to 15 (-1 to 1 bar)	±0.025%, ±0.0025 psi	300%
PCL-PM030C	795	-15 to 30 (-1 to 2 bar)	±0.025%, ±0.0025 psi	300%
PCL-PM030D	795	0 to 30 (0 to 2 bar) differential	±0.025%	300%

* See pressure module page A-32 for all ranges. One PCL-PMA adaptor required for use of pressure modules.

Note: Gauge, absolute and compound types are isolated and accept any media compatible with 316 SS. Vacuum and differential types are compatible with pressure media that are clean, dry, non-corrosive air or gas.

Comes complete with test leads, protective rubber boot, 1 Type K thermocouple with cable, 4 "AA" alkaline batteries, NIST certificate and operator's manual.

Ordering Example: PCL1200, high-accuracy multifunction calibrator, \$1895. For pressure applications, order one PCL-PMA (required) plus the modules required. **Example:** PCL-PMA, pressure module adaptor, PCL-PM030G, 0 to 30 psig pressure module, \$310 + 795 = \$1105.

ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
PCL-PMA	\$310	Pressure module adaptor (one required for pressure)
PCL-ACA	45	120 Vac adaptor

Recommended Reference Book: Instrumentation Fundamentals for Process Control, ME-1805, \$155.
Visit omega.com/bobi for Additional Books





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters