

## FINNED STRIP HEATERS

### For Fast Heat Transfer

OTF Series Starts at  
**\$82**



- ✓ Rugged, Reliable, Premium Quality
- ✓ 250 to 4150 W
- ✓ 1½" (3.8 cm) Strip [with Fins 2" (5 cm) Wide]
- ✓ Maximum Work Temperature from 225 to 565°F
- ✓ Available with Either Rust-Resisting Iron or Chrome Steel Sheath

### FEATURES


**Durability** is assured by rugged OMEGALUX® strip heater with lock-on aluminized steel fins

**Fast heat transfer** to air from large finned area.

**Large selection** of lengths, wattage and watt densities.

### UL Component Recognized

Finned elements (exclusive construction). High-quality, coiled nickel-chrome resistor wire is uniformly spaced over the width and length of the finned strip element, then embedded in high-grade refractory material which both insulates the wire and transfers heat rapidly. The refractory is then compressed to rock hardness and maximum density under tremendous hydraulic pressure to improve heat transfer from coil to sheath. Elements are oven baked at high temperatures to semi-vitrify and mature the refractory. Sheath material is either rust-resisting iron or chrome steel. Fins of aluminized steel are provided to improve that transfer to the air. Elements are individually replaceable.



### APPLICATION

- ✓ For mounting across air stream within forced air ducts
- ✓ For use in dryers, ovens and other process air heating equipment
- ✓ For comfort heating applications, principally ducts, load banks and humidity controls
- ✓ A wide range of air blast and convection requirements can be accommodated by the wide range of lengths, wattages and watt densities available

OTF-106/120, \$82, shown smaller than actual size.

**MOST POPULAR MODELS HIGHLIGHTED!**

### To Order (Specify Model Number)

Rust-Resisting Iron Sheath for Sheath Temperatures to 750°F Max.

Watts	W/in <sup>2</sup>	Dimension: Inches (cm)			Model No.	Price	Weight lb (kg)
		A	B	F			
250	10	10½ (27)	9½ (24)	6 (15)	OTF-102/*	\$82	2 (0.9)
350	15	10½ (27)	9½ (24)	6 (15)	OTF-103/*	82	2 (0.9)
600	25	10½ (27)	9½ (24)	6 (15)	OTF-106/*	82	2 (0.9)
500	17	12 (30)	11 (28)	7½ (19)	OTF-125/*	92	2 (0.9)
750	25	12 (30)	11 (28)	7½ (19)	OTF-127/*	92	2 (0.9)
250	8	12 (30)	11 (28)	7½ (19)	OTF-122/240	92	2 (0.9)
900	25	14 (36)	13 (33)	9½ (24)	OTF-149/*	103	2 (0.9)
500	15	14 (36)	13 (33)	9½ (24)	OTF-145/240	103	2 (0.9)
325	8	15¼ (39)	14¼ (36)	10¾ (27)	OTF-153/120	111	3 (1.4)
1000	25	15¼ (39)	14¼ (36)	10¾ (27)	OTF-151/*	111	3 (1.4)
500	10	17⅞ (46)	16⅞ (43)	13¾ (34)	OTF-185/*	122	3 (1.4)
1000	19	17⅞ (46)	16⅞ (43)	13¾ (34)	OTF-181/*	122	3 (1.4)
1300	25	17⅞ (46)	16⅞ (43)	13¾ (34)	OTF-182/*	122	3 (1.4)
1000	18	19½ (50)	18½ (47)	15 (38)	OTF-191/240	133	3 (1.4)
1500	25	19½ (50)	18½ (47)	15 (38)	OTF-192/*	133	3 (1.4)
1000	16	21 (53)	20 (51)	16½ (12)	OTF-211/240	137	3 (1.4)
1550	25	21 (53)	20 (51)	16½ (12)	OTF-212/240	137	3 (1.4)
750	10	23¾ (60)	22¾ (58)	19¼ (49)	OTF-247/240	155	4 (1.8)
1000	14	23¾ (60)	22¾ (58)	19¼ (49)	OTF-241/240	155	4 (1.8)
1800	25	23¾ (60)	22¾ (58)	19¼ (49)	OTF-242/240	155	4 (1.8)
1250	16	25½ (65)	24½ (62)	21 (53)	OTF-251/240	162	4 (1.8)
2000	26	25½ (65)	24½ (62)	21 (53)	OTF-252/240	162	4 (1.8)
700	9	26¾ (68)	25¾ (65)	22¼ (57)	OTF-267/*	169	4 (1.8)
1350	17	26¾ (68)	25¾ (65)	22¼ (57)	OTF-261/240	169	4 (1.8)
2000	24	26¾ (68)	25¾ (65)	22¼ (57)	OTF-262/240	169	4 (1.8)
1500	17	30½ (77)	29¾ (75)	25 (64)	OTF-301/240	190	4 (1.8)
2350	26	30½ (77)	29¾ (75)	25 (64)	OTF-302/240	190	4 (1.8)
1000	9	35⅞ (91)	34⅞ (89)	30⅞ (77)	OTF-361/240	220	5 (2.3)
1800	16	35⅞ (91)	34⅞ (89)	30⅞ (77)	OTF-363/240	220	5 (2.3)
2850	26	35⅞ (91)	34⅞ (89)	30⅞ (77)	OTF-362/240	220	5 (2.3)
2000	17	38½ (98)	37⅞ (89)	33 (84)	OTF-382/240	230	5 (2.3)
3100	26	38½ (98)	37⅞ (89)	33 (84)	OTF-383/*	230	5 (2.3)
3400	26	42½ (108)	41⅞ (106)	37 (94)	OTF-43/240	250	6 (2.7)

\* Specify voltage, insert "120" for 120 Vac or 240 for "240" Vac. Model numbers containing /120 or /240 are only available in that voltage.

† To determine maximum allowable watt density, see Figure C-10 (page 80).

Ordering Examples: OTF-127/120, finned strip heater 120 Vac, \$92.

OTF-102/240, finned strip heater 240 Vac, \$82.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters